

Automotive Relay

- General purpose automotive relay.
- Wide temperature range: -40°C to $+125^{\circ}\text{C}$.
- Standard ISO terminal foot print.
- Handles heavy automotive load; Inrush current 100A
- High current path fully welded – Reduces heat build up at full load.
- Made in North America.



Available Types

Type	Contact Form	Note
G8JN 1C7T R 12DC	SPDT	With Suppression Resistor
G8JN 1C7T D 12DC	SPDT	With Suppression Diode
G8JN 1C7T MF R 12DC	SPDT	With Mounting Bracket and Resistor
G8JN 1C6T F R 12DC	SPDT	Weatherproof with Resistor

Contact Data

Resistive load (max.)	35A(NO)/20A(NC)
Inrush current (max.)	100A
Contact Resistance	5m Ohm

Ratings/Specifications


Rated voltage	12 VDC	
Operating voltage (max.)	16 VDC	
Coil resistance	$72 \Omega \pm 15\%$	
Pull in voltage (cold start)	at $+23^{\circ}\text{C}$ (max.)	8.0 VDC
	at $+125^{\circ}\text{C}$ (max.)	11.0 VDC
Drop-out voltage at $+23^{\circ}\text{C}$ (min.)	1.0 VDC	
Duty cycle at rated load (16V at 80°C)	Up to 100%	
Operate time (at 23°C) (max.)	10 ms	
Release time (at 23°C) (max.)	4.0 ms	
Operating ambient temperature	-40°C to $+125^{\circ}\text{C}$	
Mechanical life (min.)	1,000,000 cycles	
Electrical life (resistive load) (min.)	100,000 cycles	
Weight	40g	

Application Examples

- Heated rear window
- ABS
- Head lamp
- Cooling fan
- HVAC blower motor
- Compressor coil
- Fuel pump
- Starter solenoid
- Horn

Dimensions

(All dimensions in mm)



ALSO AVAILABLE IN PCB TYPE

Cat. No. C-G8J-002 In the interest of product improvement, specifications are subject to change without notice.

OMRON

LEADERS IN ELECTRONIC COMPONENTS

OMRON Electronic Ltd.

1, Apsley Way,
Staples Corner,
London NW2 7HF
Phone:(020) 8450 4646 Fax:(020) 8450 8087