

# 70mm Compact fan



- With electronic protection against reverse polarity. The fan only operates when the polarity is correct. Impedance-protected against locked rotor and overloading.
- Fan of fibreglass reinforced plastic. PBT housing, PA impeller.
- Air exhaust over struts. Rotational direction CCW looking at rotor.
- Fitted with 3 pin molex connector (22-01-2035)
- Sensor signal for speed monitoring

Nominal data	Air flow @ free air	Air flow @ free air	Nominal voltage	Voltage range	Sound pressure level	Sintec sleeve bearings	Power input	Nominal speed	Temperature range	L10 Service life @ 40°C / @ t max
Type	m <sup>3</sup> /h	CFM	VDC	VDC	dB(A)	Yes	Watt	min <sup>-1</sup>	°C	Hours / Hours
712F/2L-005	28	16.5	12	8 ... 13.8	25	Yes	0.6	3,300	-20 ... +70	60,000 / 30,000

subject to alterations

## Dimensions

