

\*Varies from .62 to .81  
Depending on focus

TOOL  
DEV NO

**TOLERANCES**


APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

DIM.	TOL.	DIM.	TOL.
mm	mm/in	in	mm/in
NO PLACES	X	1/.04	
ONE PLACE	X,X	0.4/.016	X,X 0.8/.03
TWO PLACES	X,XX	0.15/.006	X,XX 0.38/.015
THREE PLACES	X,XXX		X,XXX 0.13/.005
ANGLES			

DESIGN UNITS  SI METRIC  US CUSTOMARY

RAW MATERIAL—COMMERCIAL STANDARD  
MICRO SWITCH STANDARDS APPLY  
DIMENSIONS ARE TO BE MET BEFORE  
PROTECTIVE COATINGS ARE APPLIED

**THIRD ANGLE PROJECTION**



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

REV	REVISION	REVISION NOTICE	CHANGED BY	CHECKED BY

**TITLE FELS1C OUTLINE DRAWING**

REPLACES  
**17-013 REV 1**

RELEASE NO.

**MATERIAL**

DRAWN **EJC** C-1851

**MICRO SWITCH**

SCALE **FULL**

QC  
REV

**DRAWING NUMBER**

CHECKED **CFR** 4 Nov 77

MARLBOROUGH, MA. U S A  
A DIVISION OF HONEYWELL

DO NOT SCALE  
PRINT

REV

1

**(M) FE LS1C**