






ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION,
WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED
WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC
TECHNOLOGY.

SPC-F0005.DWG



[illegible]

REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398



C:\Documents and Settings\jnash\Desktop\06R5629.tif



SPECIFICATIONS

- OPERATING CURRENT: 0.5A MAX.
- OPERATING TEMPERATURE: -25°C to +85°C
- DIELECTRIC WITHSTANDING VOLTAGE:
 - 500Volts AC Between Adjacent Terminal (UNMATE)
 - 300Volts AC Between Adjacent Terminal (MATE)
- INSULATION RESISTANCE:
 - 100Mohm min.(unmated); 10MOHM min.(mate)
- CONTACT PLATING: Gold Flash plated in contact area
- SHELL PLATING: Solderable Nickel Plated