
	ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY. SPC-F005.DWG	REVISIONS			DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398					
		DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
		1908	A	RELEASED	EO	6/7/06	YA	6/19/06	HO	6/19/06



RoHS
Compliant



Features:

- High intensity
- Standard T-1 diameter package
- General purpose LED
- Reliable and rugged

Specifications:

- Lead spacing is measured where the leads emerge from the package

Source Color	Chip Material	Lens Color
Yellow	GaAsP	Diffused

Absolute Maximum Rating at Ta=25°C


Parameter	MAX.	Unit
Power Dissipation	80	mW
Peak Forward Current (1/10 Duty Cycle, 0.1ms Pulse Width)	100	mA
Continuous Forward Current	30	mA
Derating Linear From 50°C	0.4	mA/°C
Reverse Voltage	5	V
Operating Temperature Range	-25°C to +80°C	
Storage Temperature Range	-40°C to +100°C	
Lead Soldering Temperature [4mm (0.157) From Body]	260°C for 5 seconds	

Electrical Optical Characteristics at Ta=25°C

Parameter	Symbol	Min.	Typ.	Max	Unit	Test Condition
Luminous Intensity	I _v		20		mcd	I _f =20mA (Note 1)
Viewing Angle	2θ _{1/2}		90		Deg	(Note 2)
Peak Emission Wavelength	λ _p		590		nm	I _f =20mA
Dominant Wavelength	λ _d		585		nm	I _f =20mA (Note 3)
Spectral Line Half-Width	Δλ		25		nm	I _f =20mA
Forward Voltage	V _f		1.9	2.5	V	I _f =20mA
Reverse Current	I _R	---	---	100	μA	V _R =5V

Notes:

- 1- Luminous intensity is measured with a light sensor and filter combination that approximates the CIE eye-response curve.
- 2- θ_{1/2} is the off-axis angle at which the luminous intensity is half the axial luminous intensity
- 3- The dominant wavelength (λ_d) is derived from the CIE chromaticity diagram and represents the single wavelength which defines the color of the device.



DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.	TOLERANCES: UNLESS OTHERWISE SPECIFIED, ±0.25 [±0.010]	DRAWN BY:	DATE:	DRAWING TITLE:			
		EKLAS ODISH	6/7/06	Standard LED, Round Lens, 3mm (T1), Yellow Emitting Color			
		CHECKED BY:	DATE:	SIZE	DWG. NO.	ELECTRONIC FILE	REV
		YILMAZ AKYONDEM	6/19/06	A	MV5374C	87K7094.DWG	A
		APPROVED BY:	DATE:	SCALE: NTS		U.O.M.: mm [INCHES]	SHEET: 1 OF 2

DRAWN BY:

DATE:

DRAWING TITLE:

EKLAS ODISH

6/7/06

Standard LED, Round Lens, 3mm (T1), Yellow Emitting Color

CHECKED BY:

DATE:

SIZE

DWG. NO.

ELECTRONIC FILE

REV

YILMAZ AKYONDEM

6/19/06

A MV5374C

87K7094.DWG

A

APPROVED BY:

DATE:

SCALE: NTS

U.O.M.: mm [INCHES]

SHEET: 1 OF 2

HISHAM ODISH

6/19/06

