

Standoffs Type A Female- / Female


- **Material** – Steel DIN 1.0718
- Brass DIN 2.0402
- Aluminum DIN 3.1645.51
- Stainless steel DIN 1.4305

- **Plating DIN 267**
 - zinc plated 5 µm (A2E)
 - yellow chromated 8 µm (A3G)
 - nickel plated 3 µm (E1E)
 - chromated

- **Tolerances**
 - Hex length DIN 7168 middle (in middle ±0,15 mm)
 - Outside length ca. ± 0,25 mm
 - Thread DIN 13 Part 13



M 3



Thread		Dimensions in mm				Steel zinc plated	Steel yellow chrom.	Order-No. Brass nickel plated	Brass nickel plated	Alu chromated	Steel stainless
G 1	G 2	L	Inch	I	A	SW 5,5	SW 5,5	SW 5,5	SW 5	SW 5,5	SW 5,5
M3	M3	3,0		3,0	-	5.03.031					
M3	M3	4,0		4,0	-	5.03.041					
M3	M3	5,0		5,0	-	5.03.051	5.03.054	5.03.053	5.03.055		5.03.059
M3	M3	5,5		5,5	-			5.03.057			
M3	M3	6,0		6,0	-	5.03.061	5.03.064	5.03.063	5.03.065		5.03.069
M3	M3	6,5		6,0	-	5.03.067					
M3	M3	7,0		7,0	-	5.03.071	5.03.072	5.03.073			5.03.079
M3	M3	7,5		7,5	-		5.03.074		5.03.075		
M3	M3	8,0		8,0	-	5.03.081	5.03.084	5.03.083	5.03.085		5.03.089
M3	M3	8,5		8,5	-	5.03.087	5.03.082				
M3	M3	9,0		9,0	-	5.03.091		5.03.093	5.03.095		5.03.099
M3	M3	9,5	3/8"	4,5	-				5.03.096		
M3	M3	10,0		10,0	-	5.03.101	5.03.104	5.03.103	5.03.105	5.03.108	5.03.109
M3	M3	11,0		5,5	-	5.03.111		5.03.113			
M3	M3	11,2		11,2	-	5.03.112					
M3	M3	12,0		6,0	-	5.03.121	5.03.124	5.03.123	5.03.125	5.03.128	
M3	M3	12,5		6,0	-	5.03.127		5.03.122			5.03.129
M3	M3	12,7	1/2"	6,0	-				5.03.126		
M3	M3	13,0		6,5	-	5.03.131		5.03.133			5.03.138
M3	M3	13,5		6,5	-	5.03.137	5.03.134	5.03.135			5.03.139
M3	M3	14,0		7,0	-	5.03.141	5.03.144	5.03.143	5.03.145		5.03.149
M3	M3	15,0		7,0	-	5.03.151	5.03.154	5.03.153	5.03.155	5.03.158	5.03.159
M3	M3	15,9	5/8"	7,0	-				5.03.156		
M3	M3	16,0		7,0	-	5.03.161	5.03.164	5.03.163	5.03.165		
M3	M3	17,0		7,0	-	5.03.171		5.03.173			5.03.179
M3	M3	17,5		7,0	-	5.03.172		5.03.177			
M3	M3	18,0		7,0	-	5.03.181	5.03.188	5.03.183	5.03.185		5.03.189
M3	M3	18,5		18,5	-			5.03.182			
M3	M3	18,5		7,0	-	5.03.187	5.03.184	5.03.186			
M3	M3	19,0		7,0	-	5.03.191		5.03.193			5.03.199
M3	M3	19,1	3/4"	7,0	-				5.03.196		
M3	M3	19,5		7,0	-			5.03.197			