

# Yellow ESD Caution Labels



**Features:**

- Label Type: Self Adhesive
- Label Size: 16x38mm
- Material: Gloss Paper with backing paper for all reel stock applications, suitable for automatic dispensing
- Adhesive: General purpose, strong permanent
- Colour: Yellow with black print
- Pack qty: 1,000 labels per reel
- Design: Industry standard design



<b>BACKING PAPER</b>	Honey Glassine 65 Yellow transparent glassine backing paper Backing paper for all reelstock applications suitable for automatic dispensing		
	<b>Test Method:</b>	<b>Value:</b>	<b>Units:</b>
Substance	ISO 536	60	g/m <sup>2</sup>
Caliper	ISO 534	53	microns
Tensile Strength MD	ISO 1924	6.3	kN/M
Tensile Strength CD	ISO 1924	2.4	kN/M
Transparency	DIN 53147	50	%
Warranty	Our recommendations are based on our most current knowledge and experience. As our products are used in conditions beyond our control, we cannot assume any liability for damage caused through their use.		
<b>ADHESIVE</b>	RP51 General purpose strong permanent. Acrylic, water borne. Good adhesion to all normal substrates, including non-polar surfaces, films and corrugated board. Good low temperature performance.		

<b>Product Code:</b>	<b>Description:</b>	<b>Size:</b>	<b>Additional Notes:</b>
1687868	Yellow ESD Caution Labels	16 x 38mm	Roll of 1,000 pieces (Ref: 055-0068)

**Important Notice:** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2011.



# Yellow ESD Caution Labels



	Test Method:	Value:	Units:
Tack min	FTM9	14	N
Shear Min	FTM8	1.0	h
PE-Looptack Min	modified FTM9	10	N
Labelling Temperature Min	-	0	°C
Service Temperature Min	-	-20	°C
Service Temperature Max	-	80	°C
Limitations	Not recommended for labelling highly curved surfaces.		
Additional Info	Approval: The research centre ISEGA has given the adhesive approval for direct contact with dry and moist non-fatty foods.		
Shelf Life	From the date of manufacture 4 years in +20 °C and RH 50%.		
Warranty	Our recommendations are based on our most current knowledge and experience. As our products are used in conditions beyond our control, we cannot assume any liability for damage caused through their use.		

<b>ROLL</b>	Raflabrite IL White woodfree machine coated SC midgloss face paper. Multipurpose label paper, suitable for Indigo digital offset printing.
-------------	--------------------------------------------------------------------------------------------------------------------------------------------------

	Test Method:	Value:	Units:
Substance	ISO 536	86	g/m <sup>2</sup>
Caliper	ISO 534	73	microns
Tensile Strength MD	ISO 1924	5.6	kN/M
Tensile Strength CD	ISO 1924	2.7	kN/M
Brightness	ISO 2470/1	88	%
Roughness	ISO 8791 / PPS10	1.1	microns
Opacity	ISO 2471	89	%
Stiffness MD	ISO/DP 5629/1	0.25	mNm
Stiffness CD	ISO/DP 5629/1	0.15	mNm
Printability	Optimized for the HP Indigo WS2000 and WS4000 digital printing presses. Pretesting recommended for conventional printing methods.		
Advantages	Stiffness of the paper offers good application characteristics for large labels. Good strength properties enables matrix stripping of difficult shapes.		
Shelf Life	Laminate one year if stored at room temperature (+20°C), RH 50% protected from light.		
Warranty	Our recommendations are based on our most current knowledge and experience. As our products are used in conditions beyond our control, we cannot assume any liability for damage caused through their use.		

<b>PRINTING INKS</b>	Water based printing inks.
----------------------	----------------------------

**Important Notice:** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2011.



# Yellow ESD Caution Labels



<p><b>FIRE FIGHTING MEASURES</b>          Extinguishing Media          Protective Equipment          Exposure Hazards</p>	<p>Not required. Waterspray, foam, dry chemical or carbon dioxide may be used on adjacent combustible materials.          Self contained breathing apparatus in severe fire conditions.          If involved in large fire, may decompose releasing irritant/toxic fumes.</p>
<p><b>ACCIDENTAL RELEASE MEASURES</b>          Personal Precautions          Environmental Precautions          Dealing with Spillages</p>	<p>Avoid contact with skin and eyes. Shut off leaks if possible without personal risk. Prevent large spillage from entering drains, ditches and rivers by the use of sand or earth. Inform local authorities/ Fire Service at once if this cannot be prevented. Contain and absorb spillage using earth, sand or other inert material. Transfer to suitable containers for disposal. When the spillage has been cleared, flush the contaminated area thoroughly with water.</p>
<p><b>PHYSICAL &amp; CHEMICAL PROPERTIES</b>          Appearance/Odour          Boiling Point/Range          Flash Point          Explosion Limits          Autoignition Temperature          Vapour Pressure          Density          Solubility in Water          Evaporation Rate          Viscosity          pH</p>	<p>Coloured liquids with a characteristic odour.          Approx. 100°C.          N/A.          N/A.          N/A.          Not determined.          Typically 1.05 - 1.40 at 20°C.          Completely miscible.          Similar to water.          Variable.          8.5 - 9.5.</p>
<p><b>STABILITY &amp; REACTIVITY</b>          Stability          Conditions and Materials to Avoid          Hazardous Products of Decomposition</p>	<p>Stable under normal conditions.          Do not allow to freeze.          Decomposition products may be irritant or toxic.</p>
<p><b>TOXICOLOGY INFORMATION</b>          Acute Toxicity          Skin          Eyes          Ingestion/Inhalation          Long Term Effects</p>	<p>Oral LD50 (rat) &gt; 2,000 mg./kg. calculated from toxicity information on constituent products.          Repeated or prolonged skin contact may cause drying and cracking.          Liquid may cause slight eye irritation.          No effects expected from inhalation at ambient temperature. Accidental ingestion of injurious quantities is unlikely. Action of stomach acids on some inks could release toxic gases.          No long term effects expected.</p>

**Important Notice:** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2011.



# Yellow ESD Caution Labels



<b>ECOLOGICAL INFORMATION</b>	
Mobility	Disperses rapidly in water. Viscosity of ink would prevent it from readily penetrating soil.
Persistence and Degradability	The resin components are readily biodegraded but, in general, the pigments are not.
Bio-accumulation	Information not available.
Ecotoxicity	Information not available.

**Important Notice:** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2011.

[www.element14.com](http://www.element14.com)

[www.farnell.com](http://www.farnell.com)

[www.newark.com](http://www.newark.com)

