



# 368 SERIES EDGE CARD CONNECTOR

.156" (3.96mm) Contact Spacing



## 368 SERIES ORDERING CODE

Example Part Number **368 - 006 - 540 - 201**



<b>Series</b> 368		
<b>Total Number of Contacts</b>	<b>Connector Style</b>	
004	End Module	
006	Centre Module	
<b>Contact Code</b>	<b>Description &amp; Tail Size</b>	<b>Tail Length "G"</b>
520	P.C. Tail .031 Square (0.79 Square)	.380 (9.65)
540	Wire Wrap .031 Square (0.79 Square)	.600(15.24)
<b>Mounting Option</b> 201		


## FEATURES

- .156 (3.96) Contact Spacing x .200 (5.08) Row Spacing
- Accepts .062 (1.57) Nominal Thickness P.C. Board
- High Profile Insulator Body, .630 (16.00)
- Press Fit Contact Termination Options include .031 (0.79) Square Wire Wrap & P.C. Tails
- Modular Design permits any Connector Length Assembly
- Accepts Between Contact and In-Contact Polarizing Keys


## SPECIFICATIONS

- ◆ Insulator Material: Polyphenylene Sulphide, UL 94V-0, Colour: Green
- ◆ Contact Material: Phosphor Bronze Alloy CA-510
- ◆ Contact Plating: Gold over Nickel for Entire Contact
- ◆ Current Rating: 5 Amperes Continuous
- ◆ For Additional Specifications, Refer to 317 Series

4 CONTACT END MODULE









6 CONTACT CENTRE MODULE



CARD SLOT ACCEPTS .054 (1.37) TO .070 (1.78) THICK P.C. BOARDS

FOR BETWEEN CONTACT POLARIZING KEY, SPECIFY P/N 368-240-318



RECOMMENDED HOLE PATTERN FOR PRESS FIT