

Date: 02 November 2004

Information Sheet No.: ZE0107

EVO-STIK CARPET ADHESIVE

A SOLVENT BORNE, SPRAYABLE ADHESIVE IN AN AEROSOL CAN

EVO-STIK CARPET ADHESIVE is a rapid drying solvent borne aerosol based adhesive that is quick and easy to apply. It is designed for bonding foam backed carpets, carpet tiles, under-felt and many other materials.

EVO-STIK CARPET ADHESIVE is easily applied direct from the can using the adjustable spray nozzle, provides a strong, flexible bond for many applications where a conventional adhesive would be too difficult to apply.

APPLICATIONS

- Adheres foam backed carpets, under-felt, and for spot fixing carpet tiles.
- It is Ideal for bonding all types of flexible foams, fabrics, felt, cork etc., to wood, metal, hardboard, glass, rigid plastics and many other materials.
- Bonds thin polyethylene or polypropylene sheets to other surfaces.

LIMITATIONS

- Do not use on plasticised (soft flexible) pvc or vinyl tiles, due to plasticiser migration.
- Not suitable for polystyrene and solvent sensitive surfaces.
- Do not use on asphalt, or bituminous materials.

APPLICATION

- Surfaces to be bonded must be clean, dry and free from grease, dust, polish and loose material.

Fixing Floor-coverings:

- Evo-Stik Carpet Adhesive should be applied directly from the can onto the surfaces to be bonded.
- Take care to avoid over-spray onto sensitive surfaces.
- Shake the can well before use. Use the adjustable nozzle to select the required spray

pattern. Hold the can 12 - 20 cm away from the surfaces to be sprayed and ensure an even coat is applied to both surfaces.

- Allow adhesive to become tacky (1- 3 minutes) and then press the two surfaces together firmly. Some very porous surfaces may require two coats and drying time may be longer.
- After use invert can and expel a small amount of propellant to clear nozzle
- Check that floor covering is bedded down securely after 2 hours.

Coverage: 500ml of adhesive covers an area of approximately 3.5m² in a single coat.

Drying times

The adhesive remains 'open' for 15 - 25 minutes, after drying. Check that floor-covering is bedded down securely after 2 hours.

SPECIAL INFORMATION

- This adhesive is one of the few that will bond thin polythene sheet to other surfaces with a reasonable bond.
- For less demanding bonds a single coat may be applied to one surface and when dry the other material can be bonded to it.

Date: 02 November 2004

Information Sheet No.: ZE0107

SHELF LIFE: Up to 12 months from the date of manufacture when stored as shown below:

STORAGE: Store under dry conditions between 5°C and 25°C.

COLOUR: Light amber

PACKAGING **Code:**
132801 500ml x12

HEALTH AND SAFETY: Available separately in file named as the packaging code above.

TYPICAL ADHESIVE CHARACTERISTICS

Physical form: Aerosol
Chemical type: Synthetic rubber/resin
Colour: Light amber, will darken if exposed to light.
Application temperature: Best between +15°C to +30°C. Do not use below +5°C or above + 40°C
Temperature resistance: -20°C to 45°C

Sales & Technical contacts at Bostik

	Telephone	Facsimile	Email addresses
Sales	01785 272700	01785 241818	customer.service@bostik.com
Technical advice	01785 272727	01785 272867	technical.service@bostik.com
Technical Data & COSHH (MSDS) sheets	01785 272827		gatehouse@bostik.com

This Product Data Sheet covers just one of a large range of products supplied by Bostik Limited. Full information on these products and advice on application is freely available from our fully trained staff throughout the country. In addition, specialist technical advice is available from our Technical Services Department. This Product Data Sheet supersedes all previous technical information on this product, and users of it are cautioned to ensure that it is the current issue. Destroy all previous Product Data Sheets, and if any doubt, contact Bostik Limited, quoting the code number in the top right hand corner on the front of this document. This leaflet is for general guidance only and may contain inappropriate information under particular conditions of use. The company cannot accept any responsibility for loss or damage that may result from the use of this information, due to the possibility of variations of processing or working conditions and of workmanship outside our control. Users are advised to confirm the suitability of this product by their own tests.
