

**ACT20M-CI-2CO-S**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-2083  
 www.weidmueller.com



The externally supplied ACT20M-CI-CO, MAS RPS/RPSH, MCZ CFC and WAS/WAZ 4/5 C signal converters/supply isolators can transmit, isolate and convert normalised DC current signals. They are optionally available in widths of 6 mm (ACT20M/MCZ), 12.5 mm (WAS/WAZ4) or 17.5 mm (WAS/WAZ5).

The input and output circuits are completely electrically isolated, as is the power supply. The input signal is converted into a DC current/voltage value (ACT20M, WAS/WAZ) or into a proportional frequency (MCZ CFC) between 0&ndash;1/4/8/16 kHz.&nbsp;

The WAVESERIES signal converters are available with a limiting frequency of either 10 Hz (WAS/WAZ4) or 20 kHz (WAS/WAZ5) so that they can process signals quickly.&nbsp;

The MAS/RPS/RPSH supply isolator can supply 2-wire sensors externally. They can also be used optionally to transmit the HART protocol (MAS RPSH).

The 24 VDC supply voltage can be cross-connected on the module side via the CH20M BUS profile (ACT20M series) or using the ZQV4N (MAS/MCZ) or ZQV 2,5N (WAS/WAZ) pluggable jumpers.&nbsp;

International approvals (such as ATEX Zone 2, UL C1D2 and FM Div2) permit use in explosion-risk zones.

**General ordering data**

Order No.	<a href="#">1175990000</a>
Type	ACT20M-CI-2CO-S
GTIN (EAN)	4032248969982
Qty.	1 pc(s).

**ACT20M-CI-2CO-S**

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com

**Technical data**

**Dimensions**

Length	114.3 mm	Width	6.1 mm
Height	112.5 mm		

**Temperatures**

Operating temperature	-25 °C...+70 °C	Ambient temperature (text)	-40 °C...+70°C
Storage temperature	-40 °C...+85 °C		

**Input**

Input frequency	100 Hz	Input current	0(4)...20 mA
-----------------	--------	---------------	--------------

**Output**

Cut-off frequency (-3 dB)	100 Hz	load impedance voltage	≥ 10 kΩ
Number of outputs	2	load impedance current	< 300 Ω
Output current	0(4)...20 mA		

**General data**

Accuracy	< 0.05 % of measuring range	Galvanic isolation	3-way isolator
Humidity	40°C / 93% rel. humidity, no condensation	Mounting rail	TS 35
Supply voltage	24 V DC ± 30 %	Temperature coefficient	≤ 0.01 % / °C
Type of connection	Screw connection		

**Insulation coordination**

EMC standards	EN 61326-1	Insulation voltage	2.5 kV <sub>eff</sub>
Pollution severity	2	Rated voltage	300 V <sub>eff</sub>
Standards	DIN EN 61010-1, DIN EN 60079, DIN EN 61326-1	Surge voltage category	II

**Ratings IECEx/ATEX**

Certificate No. (ATEX)	KEMA10ATEX0183X	Certificate No. (IECEx)	IECExKEM10.0090
------------------------	-----------------	-------------------------	-----------------

**Classifications**

ETIM 3.0	EC002479	ETIM 4.0	EC002653
eClass 6.0	27-21-01-20		

**Approvals**

Approvals	CE; CULUS; DETNORVER; FMEX; GERMLLOYD; IECExKEM; KEMAATEX
-----------	---

**ACT20M-CI-2CO-S**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-2083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Electric symbol**

