# **Clamp Meter**





### Safety Rating:

CAT II 600 V CAT III 300 V

### **Specifications**

Basic Functions	Range	Best Accuracy		
AC Current (A)	2 A / 20 A / 200 A / 400 A	± (1.5% + 5)		
AC Voltage (V)	2 V / 20 V / 200 V / 600 V	± (1.2% + 5)		
DC Voltage (V)	200 mV / 2 V / 20 V / 200 V / 600 V	± (0.8% + 1)		
Resistance (Ω)	200 $\Omega$ / 2 K $\Omega$ / 20 K $\Omega$ / 200 K $\Omega$ / 2 M $\Omega$ / 20 M $\Omega$	± (1% + 2)		
Temperature (°C)	-40°C to 1,000°C	± (1% + 3)		
Temperature (°F)	-40°F to 1,832°F	± (1% + 6)		
Features				
Display count	1,999			
Auto range	✓			
Jaw capacity	28 mm			
Diode	¥			
Auto power off	v			

www.element14.com www.farnell.com www.newark.com www.cpc.co.uk www.mcmelectronics.com



## **Clamp Meter**



### **Specifications**

Basic Functions	Range	Best Accuracy
Features		
Continuity buzzer		
Low battery indication		
Data hold	$\checkmark$	
Maximum mode		
Full icon display		
Input impedance for DCV	Around 10 MΩ	

#### **General Characteristics**

Power	1.5 V batteries (R03) × 2
LCD size	35.6 × 18 mm
Product colour	Orange and grey
Product net weight	220 g
Product size	210 × 75.6 × 30 mm
Standard accessories	Battery, test lead, carrying bag, point contact temperature probe
Standard individual packing	Gift box, English manual

#### **Part Number Table**

Description	Part Number
Clamp Meter, With Temperature	72-7222

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Famell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. TENMA<sup>™</sup> is the registered trademark of the Group. © Premier Famell plc 2011.

www.element14.com www.farnell.com www.newark.com www.cpc.co.uk www.mcmelectronics.com

