

VA-1DVIN-DVI EDID Emulator

The VA-1DVIN is an EDID emulator for DVI-D signals. The unit can capture an EDID setting in non-volatile memory from the output allowing convenient and reliable connection to the source.



VA-1DVIN FEATURES

- **Max. Data Rate** - 3.3Gbps.
- **Input/Output** - DVI-D signals on DVI-I connectors. Passes analog signals on the DVI-I connector without processing.
- **Control** - Capture button.
- **Ultra-Compact PicoTOOLS™** - 4 units can be rack mounted side by side in a 1U rack space with the optional RK-4PT rack adapter.

VA-1DVIN TECHNICAL SPECIFICATIONS

- **INPUT:**1 x DVI dual link, DVI 1.0, 1.2Vpp on a DVI Molex 24-pin female connector; DDC signal 5Vpp (TTL).
- **OUTPUT:**1 x DVI, dual Link, DVI 1.0, 1.2Vpp on a DVI Molex 24-pin female connector; DDC signal 5Vpp (TTL).
- **BANDWIDTH:**3.3Gbps.
- **CONTROLS:**Capture EDID button.
- **POWER SOURCE:**5V DC, 20mA.
- **DIMENSIONS:**6.22cm x 5.24cm x 2.41cm (2.45" x 2.06" x 0.95") W, D, H.
- **WEIGHT:**0.15kg (0.55lbs) approx.
- **ACCESSORIES:**Power supply.
- **OPTIONS:**RK-4PT 19" rack adapter.