


- Ball-Nosed Slot Drill
- Radius - Kopierfräser
- Radiusfrezen
- Fraises de finition bout hémisphérique
- Fresas con punta esférica
- Fresa Topo Esférico



## C530



- 1.1 1.2
- 1.3 3.1 3.2 3.3 4.1 4.2 5.1 5.2 6.1 6.2 6.3 7.1 7.2 7.3 8.1

d <sub>1</sub> Ø Inch	d <sub>1</sub> Ø mm	r Inch	R	d <sub>2</sub> Ø Inch	l <sub>2</sub> mm	l <sub>1</sub> mm	z	e-Code
1/16	1.59	1/32	0.79	6.35 - 1/4	2.5	48.5	2	C5301/16
	2.00		1.00	6	3	49	2	C5302.0
3/32	2.38	3/64	1.19	6.35 - 1/4	4.5	51	2	C5303/32
	2.50		1.25	6	4.5	51	2	C5302.5
	3.00		1.50	6	7	51	2	C5303.0
1/8	3.18	1/16	1.59	6.35 - 1/4	7.0	51	2	C5301/8
5/32	3.97	5/64	1.98	6.35 - 1/4	9.5	52.5	2	C5305/32
	4.00		2.00	6	9.5	52.5	2	C5304.0
3/16	4.76	3/32	2.38	6.35 - 1/4	9.5	52.5	2	C5303/16
	5.00		2.50	6	9.5	52.5	2	C5305.0
	6.00		3.00	6	11	56.5	2	C5306.0
1/4	6.35	1/8	3.18	6.35 - 1/4	11	56.5	2	C5301/4
	7.00		3.50	10	11	58.5	2	C5307.0
5/16	7.94	5/32	3.97	9.53 - 3/8	12.5	59.5	2	C5305/16
	8.00		4.00	10	12.5	59.5	2	C5308.0
3/8	9.53	3/16	4.76	9.53 - 3/8	14.5	60.5	2	C5303/8
	10.00		5.00	10	14.5	60.5	2	C53010.0
	12.00		6.00	12	19	66.5	2	C53012.0
	18.00		9.00	16	24	74	2	C53018.0
1/2	12.70	1/4	6.35	12.7 - 1/2	19	66.5	2	C5301/2
	14.00		7.00	12	22	68.5	2	C53014.0
	15.88	5/16	7.94	15.88 - 5/8	22	72	2	C5305/8
	16.00		8.00	16	22	72	2	C53016.0
3/4	18.00		9.00	16	24	74	2	C53018.0
	19.05	3/8	9.53	15.88 - 5/8	25.5	77	2	C5303/4
	20.00		10.00	25	25.5	77	2	C53020.0
7/8	22.00		11.00	25	25.5	100	2	C53022.0
	22.23	7/16	11.11	25.4 - 1.	25.5	100	2	C5307/8
	24.00		12.00	25	25.5	103	2	C53024.0
1	25.00		12.50	25	28.5	97	2	C53025.0
	25.40	1/2	12.70	25.4 - 1.	27	95	2	C5301
	26.00		13.00	25	28.5	97	2	C53026.0
	28.00		14.00	25	30	95	2	C53028.0
1.1/8	28.58	9/16	14.29	25.4 - 1.	30	95	2	C5301.1/8
	30.00		15.00	25	30	93.5	2	C53030.0
1.1/4	31.75	5/8	15.88	31.75 - 1.1/4	35	117.5	2	C5301.1/4X1.1/4
	32.00		16.00	25	36.5	100	2	C53032.0
1.3/8	34.93	11/16	17.46	31.75 - 1.1/4	39.5	111	2	C5301.3/8X1.1/4
1.1/2	38.10	3/4	19.05	31.75 - 1.1/4	43	114.5	2	C5301.1/2X1.1/4