


 Design Support

[Home](#) > [Support](#) > [Design Support](#) > [Design Resources](#) > [Evaluation Boards](#)
**Previously Viewed Products**
 Technical Documentation

**NCP3064SCBCKGEVB:NCP3064 SOIC8 BUCK DB**

[Clear List](#)
 Design Resources

 Design & Development Tools

 Evaluation Boards

 Conversion Services

 Evaluation Board Documents

 Custom Foundry Services

 Sample Kits

 Simulation Models

 Product Recommendation Tools

 Software

 Video

 Technical Support

### Evaluation Board Description

The NCP3064 device supports a buck configuration with a wide input voltage range from 3.0V to 40.0V. The NCP3064 is a low cost converter that supports a peak current of 1.5A with a maximum duty cycle of 85.7 percent. The ON/OFF function allows turn the device to low consumption mode.

Size: 41mm x 28mm x 14mm

### Features and Applications

#### Features

- ? Input Voltage Range from 3.0 V to 40 V
- ? Logic Level Shutdown Capability
- ? Low Power Standby Mode, Typical 100 uA
- ? Output Switch Current to 1.5 A
- ? Adjustable Output Voltage Range
- ? 150 kHz Frequency Operation
- ? Precision 2% Reference
- ? Internal Thermal Shutdown Protection
- ? CyclebyCycle Current Limiting
- ? NCV Prefix for Automotive and Other Applications Requiring Site and Control Changes
- ? These are PbFree Devices

### Evaluation Board Information

Evaluation Board	Status	Pb-free	Short Description	Parts Used	Action
NCP3064SCBCKGEVB	Active	<input checked="" type="checkbox"/> Pb-f <sub>r</sub>	NCP3064 SOIC8 BUCK DB	NCP3064DR2G	Contact Local Sales Office

### Technical Documents

Type	Document Title	Document ID/Size	Rev
Eval Board: BOM	NCP3064SCBCKGEVB Bill of Materials ROHS Compliant	NCP3064SCBCKGEVB_BOM_ROHS.PDF - 38.0 KB	2
Eval Board: Gerber	NCP3064SCBCKGEVB Gerber Layout Files (Zip Format)	NCP3064SCBCKGEVB_GERBER.ZIP - 31.0 KB	0
Eval Board: Schematic	NCP3064SCBCKGEVB Schematic	NCP3064SCBCKGEVB_SCHEMATIC.PDF - 131.0 KB	0
Eval Board: Test Procedure	NCP3064SCBCKGEVB Test Procedure	NCP3064SCBCKGEVB_TEST_PROCEDURE.PDF - 158.0 KB	0