

HIGH PERFORMANCE PTFE LUBRICANT



PRODUCT OVERVIEW

WD-40 Specialist High Performance PTFE Lubricant contains PTFE which provides excellent lubrication and protection whilst reducing friction and wear, extending the life of tools and equipment. This product can be used on metals, glass, vinyl, rubber and plastic.

FEATURES AND BENEFITS

- ⊕ Dual action Smart Straw applicator for wide area and precision spray applications
 - ⊕ For the use of metals, glass, vinyl, rubber and plastic
 - ⊕ Extends life of tools and equipment
 - ⊕ Reduces friction and wear
 - ⊕ Long lasting formula provides superior lubrication
 - ⊕ Withstands temperatures of -20°C to +100°C
- NSF H2 Registered #145377**



NARROW SPRAY



WIDE SPRAY

TYPICAL APPLICATIONS

Axles, Hydraulics, Hand & Power Tools, Cogs, Precision Tooling, Bushings, Conveyors, Sliding Tracks, Cranks, Wire Rope, Pulleys.

DIRECTIONS FOR USE

Shake Well. Apply by spraying directly on surface to be lubricated or protected.

TECHNICAL DATA

PROPERTY	HIGH PERFORMANCE SILICONE LUBRICANT
Appearance	Cloudy, deep yellow liquid
Odour	pleasant lemon odour
SG	0.75 - 0.78
Temperature range	Effective performance at temperatures from -20°C to +100°C
Solubility	Not miscible with water
NSF category	H2
Flammability	Classed as extremely flammable under current legislation
Compatibility	Safe to use on all metal and no-metal surfaces including glass, vinyl, rubber and plastic
Lubrication ASTM D-4172	Scar depth 0.38 mm
Extreme pressure lubrication ASTM 3233	1000 lb

PACKAGING SPECIFICATIONS

PRODUCT NUMBER	UNIT SIZE	CASE SIZE
44396	400ml	400ml x 12

