

# Pinless Moisture Meter

## **Non-invasive measurement**

Monitor moisture in wood and other building materials with virtually no surface damage

### **Features:**

- Relative pinless moisture reading for non-invasive measurement from 0.0 to 100.0 with 0.1 resolution
- Multifunction backlit triple LCD display
- Pinless measurement depth from 0.78" (20mm) to 1.6" (40mm) below the surface
- High frequency sensing technology
- Automatic Data Hold
- Two adjustable alarm levels with audible beeper and visual (flashing "RISK" or "WET") indicators
- Automatic calibration (in dry air) when meter is powered on
- Low battery indication
- Auto Power off
- Dimensions: 9.25x2.5x1.1" (235x63x28mm)  
Weight: 7.7oz (218g)
- Complete with 3 AA batteries and pouch case



Measures relative moisture of various building materials including wood, particle board, carpeting, and ceiling tiles using non-invasive Pinless Technology

### **Ordering Information:**

M0257.....Non-Contact Pinless Moisture Meter