





| REVISIONS |                    |
|-----------|--------------------|
| ISS       | DESCRIPTION \ DATE |
| 1         |                    |

BNC2 58D

RoHS COMPLIANT



RECOMMENDED  
CABLE STRIPPING DIM'S



1. CRIMPED FERRULE  
HEX CRIMP SIZE .213"
2. CRIMPED CONTACT PIN  
HEX CRIMP SIZE .068"

|                                     |  |                 |                                                                                                                                                |            |             |            |
|-------------------------------------|--|-----------------|------------------------------------------------------------------------------------------------------------------------------------------------|------------|-------------|------------|
| <b>CONNECTORCO</b>                  |  | APRD: <b>TS</b> | UNLESS OTHERWISE SPECIFIED TOLERANCES<br>0.5-6 = ±0.2<br>>6-30 = ±0.4<br>>30-120 = ±0.6<br>>120-318 = ±1.1<br>>318-1000 = ±1.6<br>ANGLES = ±5° |            |             |            |
|                                     |  | CHKD: <b>CH</b> |                                                                                                                                                |            |             |            |
|                                     |  | DR: <b>DS</b>   |                                                                                                                                                |            |             |            |
| TITLE: BNC MALE CRIMP<br>(FOR RG58) |  | DATE: 10/28/10" | UNIT: mm                                                                                                                                       |            |             |            |
| PART NO: B002D058-96                |  | SHEET: .        |                                                                                                                                                | SCALE: 3/1 |             |            |
| DRAWING NO: 50013-016               |  |                 |                                                                                                                                                | NO.        | DESCRIPTION | MATERIAL   |
|                                     |  |                 |                                                                                                                                                | 1          | BODY        | ZINC ALLOY |
|                                     |  |                 |                                                                                                                                                | 2          | INSULATOR   | DELIRIN    |
|                                     |  |                 |                                                                                                                                                | 3          | SPRING      | SK-5       |
|                                     |  |                 |                                                                                                                                                | 4          | WASHER      | STEEL      |
|                                     |  |                 |                                                                                                                                                | 5          | SHELL       | ZINC ALLOY |
|                                     |  |                 |                                                                                                                                                | 6          | CONTACT PIN | BRASS      |
|                                     |  |                 |                                                                                                                                                | 7          | FERRULE     | BRASS      |
|                                     |  |                 |                                                                                                                                                |            |             | NICKEL     |
|                                     |  |                 |                                                                                                                                                |            |             | GOLD       |
|                                     |  |                 |                                                                                                                                                |            |             | NICKEL     |
|                                     |  |                 |                                                                                                                                                |            |             | NICKEL     |
|                                     |  |                 |                                                                                                                                                |            |             | WHITE      |
|                                     |  |                 |                                                                                                                                                |            |             | NICKEL     |
|                                     |  |                 |                                                                                                                                                |            |             | FINISH     |