

FEATURES

- Metabo S-automatic torque limiting clutch
- Spindle lock
- Fully closed guide plate for secure support
- Clearly visible cutting indicator
- Safety lock switch to prevent unintentional start of the machine
- Angle adjustment of the sawing blade to the guide plate can be aligned for maximum cutting precision
- Angle-precise bevel cuts up to 45°
- Lubrication system for long service life of the gearbox
- Optimum sawing dust ejection
- External dust extraction outlet
- With carbide thin circular saw blade
- Guide rail available as accessory

The KSA P 18
Cordless Circular Saw
– for sawing without being
connected to the mains –
Please see page 75



KS 54

KSE 55 Plus

	1010 Watt Circular Saw KS 54	1200 Watt Electronic Circular Saw KSE 55 Plus
Special advantages		
■ Vario Tacho Constamatic (VTC) full-wave electronics		•
■ Thumbwheel for preselection of speed		•
■ Electronic soft start		•
■ Overload protection		•
Comparable specifications		
Torque	4 Nm	5 Nm
Carbide-tipped circular saw blades	10 teeth	10 teeth
Maximum cutting depth at 90°	54 mm	55 mm
Maximum cutting depth at 45°	38 mm	39 mm
Adjustable cutting depth	0 - 54 mm	0 - 55 mm
Saw blade diameter	160 mm	160 mm
Speeds at no load	6,000/min	2,000 - 5,200/min
Rated input power	1,010 W	1,200 W
Output power	630 W	680 W
Speed at rated load	4,200/min	5,000/min
Cutting speed at rated load	35 m/s	42 m/s
Weight (excluding mains lead)	3.4 kg	3.5 kg
Standard equipment	Carbide-tipped thin circular sawing blade, ripping fence, hexagonal spanner	Carbide-tipped thin circular sawing blade, ripping fence, hexagonal spanner
Type	KS 54	KSE 55 Plus
Order no.	6.00540	6.00541