



## 4000 Staticide® Acrylic Floor Finish

### Low Cost + High Performance = Value

Staticide® Acrylic Floor Finish offers high-tech static protection at a reasonable price. This economical formula leaves a durable, glossy finish that can last up to twelve months, making it a popular choice for budget-minded companies with industrial areas where static control is essential.

Easy to apply and maintain, Staticide® Acrylic Floor Finish leaves floors with a surface resistivity of  $10^8$  -  $10^9$  ohms per square, complying with ANSI/ESD S20.20 guidelines. This water-based formula is UL listed for slip resistance, RoHS compliant, biodegradable, non-flammable, and free of formaldehyde, phthalates, alkalis, acids, and ammonia.

As ACL's original ESD floor finish, Staticide® Acrylic continues to be an ideal choice for production areas, warehousing, shipping, laboratories, and electronic repair facilities.

**Directions:** Clean floor and apply two thin coats of floor finish with a dedicated rayon mop. Wait one hour between coats. Consult application procedure for details and precise instructions.

**Maintenance:** Sweep or damp mop daily to remove dirt. Periodically clean with a 1:1 dilution of water and floor finish. Apply a thin top coat of floor finish every 4 – 6 weeks. For heavy cleaning, use the 4100 Restorer Cleaner. Consult maintenance procedure for details and precise instructions.

*Product #40001; 4 gallons per case*

*Product #40005; 5-gallon pail*

*Product #40002; 54-gallon drum*

- ❖ **Coverage: 1,500 - 2,000 square feet per gallon**
- ❖ **Non-toxic; biodegradable**
- ❖ **Non-volatile solids: 20 ± 5%**
- ❖ **Strip cycle: 6-12 months**
- ❖ **Suitable to use on vinyl, linoleum, and ceramic tiles**
- ❖ **Surface resistivity:  $10^8$  –  $10^9$  ohms per square (average)**
- ❖ **Low V.O.C.**
- ❖ **Water-based polyurethane**

