

USB Serial Adapter GXMU-1200

Quick and painless! That is a brief description of the process of installing and using the GoldX® PlusSeries® USB to Serial adapter. Just plug it in, load the software and go! Perfect for connecting your serial port based peripherals to the USB port. Use it for connecting modems, PDA's, PLC's, transcription devices and other serial items to the new laptop and desktop computers without serial ports or connect more devices than you have serial ports.

Features:

- Flexible cable
- Premium quality
- Gold connectors
- Ergonomic molding for easy connections
- Industry standard color coded for easy installation
- Foil and braid shielding to reduce EMI/RFI interference
- Designed for high speed transmissions for optimal performance
- 24 Karat Warranty





Specifications:

- RS-232C standard compliant
- Powered by the USB bus
- DB 9 male connector

Operating Systems:

- Windows Vista (All versions)
- Windows Server 2003
- Windows 2000 Professional
- Windows 2000 Server Family
- Windows XP Home
- Windows XP Professional



Hardware Requirements:

- Pentium II class processor or higher
- One available USB port

© Copyright 2007 Jo-Dan International, Inc. all rights reserved. Plus Series®, PowerCore®, QuickConnect®, Share Plus®, and GoldX® Products are registered trademarks of Jo-Dan International, Inc. All other trademarks and registered trademarks are the property of their respective owners. Designed in USA. Made in China. One or more of the following patents may apply: D494,935, D494,934, D494,932, D493,453, 6,755,676, D490,702, 6,736,658, 6,726,509, 6,716,047, D485,752, D484,044, D481,629, D481,628, 6,607,408, D478,001, D478,000, D468,635, 6,479,607, D465,223, 6,454,584, D462,612, D452,427, D452,426, D451,888, D451,480, D450,303, D448,736, D444,772, D443,862, D443,593, D442,919, D442,556, D442,555, 5,788,521, 5,658,158, 5,334,033, 5,292,257. D503,882; 6,843,684; 6,854,989; 6,872,086; D506,386; 6,905,374; D509,797; 6,991,483; D513,976; 7,004,787; 7,028,114; D519,925; D522,507; 7,258,572. Other patents pending.