

SUBMINIATURE JACKS & PLUGS 150/3150 SERIES TRS/TTM



Sub-miniature Jacks & Plugs

Sub-miniature concentric twinax/triax connectors increase packing density up to 246%. They are designed for high density applications where digital, video pair or baseband noise-free guarded circuits are required. The 3-lug, 4-lug, and threaded versions improve mechanical stability and provide “error-free” redundant data bus capabilities. The wrench crimp version accommodates cables with other jacket diameters up to .215" and the tool crimp versions up to .250".

<p>PL155-29 Shown</p> <p>CABLE PLUG WRENCH CRIMP</p> <p>3-lug 4-lug Threaded</p> <p>PL155-[△] PL155FL-[△] PL3155-[△]</p>	<p>BJ159-29 Shown</p> <p>BULKHEAD JACK REAR MOUNT, WRENCH CRIMP</p> <p>3-lug 4-lug Threaded</p> <p>BJ159-[△] BJ159FL-[△] BJ3159-[△]</p> <p>Mounting Hole: D4.125</p>
<p>PL155AC-207 Shown</p> <p>CABLE PLUG TOOL CRIMP</p> <p>3-lug 4-lug Threaded</p> <p>PL155AC-[△] PL155ACFL-[△] PL3155AC-[△]</p>	<p>BJ159AC Shown</p> <p>BULKHEAD JACK REAR MOUNT, TOOL CRIMP</p> <p>3-lug 4-lug Threaded</p> <p>BJ159AC-[△] BJ159ACFL-[△] BJ3159AC-[△]</p> <p>Mounting Hole: D4.125</p>
<p>PLR3155AC-201 Shown</p> <p>RIGHT ANGLE CABLE PLUG TOOL CRIMP</p> <p>3-lug 4-lug Threaded</p> <p>PLR155AC-[△] PLR155ACFL-[△] PLR3155AC-[△]</p>	<p>CJ150-29 Shown</p> <p>CABLE JACK WRENCH CRIMP</p> <p>3-lug 4-lug Threaded</p> <p>CJ150-[△] CJ150FL-[△] CJ3150-[△]</p>
<p>PLR3155AC-201 Shown</p> <p>RIGHT ANGLE CABLE JACK TOOL CRIMP</p> <p>3-lug 4-lug Threaded</p> <p>PLR155AC-[△] PLR155ACFL-[△] PLR3155AC-[△]</p>	<p>CJ150AC-207 Shown</p> <p>CABLE JACK TOOL CRIMP</p> <p>3-lug 4-lug Threaded</p> <p>CJ150AC-[△] CJ150ACFL-[△] CJ3150AC-[△]</p>

[△]Refers to Cable Group Table see pages 82-124. "D" mounting holes see page 63.