


## Locknuts



**LN-Z Series** locknuts provide a method of securing a threaded entry component into a piece of equipment.

**Threadforms:** Metric, NPT, NPSM, ISO Pipe (BSP), PG, ET  
**Materials:** Brass, 316 Stainless Steel, Aluminium, Steel, Nylon 6  
**Plating:** Nickel, Zinc, other on application  
**CE Conformity:** Please refer to *European Directives & CE Marking*  
**Part Number:** Please refer to *Part Numbering System*

### Dimensions of Metric and NPT Versions (Metallic)

	Hex A/F	Hex A/C	Thickness		Hex A/F	Hex A/C	Thickness
<b>M16</b>	20.0	23.0	3.0	<b>½" NPT</b>	27.0	31.0	3.0
<b>M20</b>	24.0	26.7	3.0	<b>¾" NPT</b>	30.5	35.0	3.5
<b>M25</b>	30.0	33.5	3.5	<b>1" NPT</b>	37.6	43.4	5.0
<b>M32</b>	36.0	39.0	4.0	<b>1¼" NPT</b>	52.0	60.0	5.5
<b>M40</b>	46.0	50.0	4.5	<b>1½" NPT</b>	60.0	69.0	6.0
<b>M50</b>	60.0	69.0	5.5	<b>2" NPT</b>	75.0	86.2	7.0
<b>M63</b>	75.0	86.2	7.0	<b>2½" NPT</b>	80.0	92.0	9.0
<b>M75</b>	90.2	103.7	7.0	<b>3" NPT</b>	106.4	122.3	9.0
<b>M80x2.0</b>	90.2	103.7	8.0	<b>3½" NPT</b>	114.3	131.5	10.0
<b>M85x2.0</b>	106.4	122.3	8.0	<b>4" NPT</b>	127.0	146.1	10.0
<b>M90x2.0</b>	106.4	122.3	8.0				
<b>M100x2.0</b>	114.3	131.5	9.0				

### Dimensions of Metric Versions (Nylon)

	Hex A/F	Hex A/C	Thickness
<b>M16</b>	19.0	22.0	6.8
<b>M20</b>	23.0	26.8	8.0
<b>M25</b>	28.0	32.1	9.0
<b>M32</b>	36.5	42.2	9.0
<b>M40</b>	45.9	50.9	10.0
<b>M50</b>	60.0	65.1	10.0
<b>M63</b>	74.0	82.0	10.8

For full material specifications and options please refer to *Material Specifications*.