

## Metallized Polypropylene (PP) Capacitors in PCM 5 mm

### Special Features

- High volume/capacitance ratio
- Self-healing
- Increased pulse duty from 250 VDC rated voltage
- Very low dissipation factor
- Negative capacitance change versus temperature
- Very low dielectric absorption
- According to RoHS 2002/95/EC

### Typical Applications

For high frequency applications e.g.

- Sample and hold
- Timing
- Oscillating circuits
- High frequency coupling and decoupling

### Construction


#### Dielectric:

Polypropylene (PP) film

#### Capacitor electrodes:

Vacuum-deposited

#### Internal construction:



#### Encapsulation:

Solvent-resistant, flame-retardant plastic case with epoxy resin seal, UL 94 V-0

#### Terminations:

Tinned wire.

#### Marking:

Colour: Red. Marking: Black. Epoxy resin seal: Red

### Electrical Data

#### Capacitance range:

1000 pF to 0.33 μF (E12-values on request)

#### Rated voltages:

63 VDC, 100 VDC, 250 VDC, 400 VDC, 630 VDC, 1000 VDC

#### Capacitance tolerances:

± 20%, ±10%, ±5%

#### Operating temperature range:

-55° C to +100° C

#### Test specifications:

In accordance with IEC 60384-16 and EN 131 200

#### Climatic test category:

55/085/56 in accordance with IEC

#### Insulation resistance at +20° C:

≥ 3 × 10<sup>4</sup> MΩ

(mean value: 1 × 10<sup>5</sup> MΩ)

Measuring voltage:

U<sub>r</sub> = 63 V: U<sub>test</sub> = 50 V/1 min.

U<sub>r</sub> ≥ 100 V: U<sub>test</sub> = 100 V/1 min.

#### Test voltage:

1.6 U<sub>r</sub>, 2 sec.

#### Maximum pulse rise time:

Capacitance pF/μF	max. pulse rise time V/μsec					
	63 VDC	100 VDC	250 VDC	400 VDC	630 VDC	1000 VDC
1000 ... 2200	-	-	-	300	400	500
3300 ... 6800	-	-	-	300	400	500
0.01 ... 0.022	100	100	250	300	400	500
0.033 ... 0.068	100	100	250	300	400	-
0.1 ... 0.22	100	100	250	-	-	-
0.33	100	100	250	-	-	-

for pulses equal to the rated voltage

### Mechanical Tests

#### Pull test on leads:

10 N in direction of leads according to IEC 60068-2-21

#### Vibration:

6 hours at 10 ... 2000 Hz and 0.75 mm displacement amplitude or 10 g in accordance with IEC 60068-2-6

#### Low air density:

1kPa = 10 mbar in accordance with IEC 60068-2-13

#### Bump test:

4000 bumps at 390 m/sec<sup>2</sup> in accordance with IEC 60068-2-29

#### Dielectric absorption:

0.05 %

#### Dissipation factors at +20° C: tan δ

at f	C ≤ 0.1 μF	0.1 μF < C ≤ 0.33 μF
1 kHz	≤ 0.5 × 10 <sup>-3</sup>	≤ 0.5 × 10 <sup>-3</sup>
10 kHz	≤ 0.8 × 10 <sup>-3</sup>	≤ 0.8 × 10 <sup>-3</sup>
100 kHz	≤ 3.0 × 10 <sup>-3</sup>	-

#### Voltage derating:

A voltage derating factor of 1.35 % per K must be applied from +85° C for DC voltages and from +75° C for AC voltages

#### Reliability:

Operational life > 300 000 hours

Failure rate < 2 fit (0.5 × U<sub>r</sub> and 40° C)

### Packing

Available taped and reeled.

Detailed taping information and graphs at the end of the catalogue.

For further details and graphs please refer to Technical Information.

## Continuation

### General Data

Capacitance	63 VDC/40 VAC*					100 VDC/63 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
0.01 $\mu$ F	3	7.5	7.2	5	MKP2C021001B00_____	3	7.5	7.2	5	MKP2D021001B00_____
0.015 "	3	7.5	7.2	5	MKP2C021501B00_____	3	7.5	7.2	5	MKP2D021501B00_____
0.022 "	3	7.5	7.2	5	MKP2C022201B00_____	3	7.5	7.2	5	MKP2D022201B00_____
0.033 "	3	7.5	7.2	5	MKP2C023301B00_____	3	7.5	7.2	5	MKP2D023301B00_____
0.047 "	3.5	8.5	7.2	5	MKP2C024701C00_____	3.5	8.5	7.2	5	MKP2D024701C00_____
0.068 "	4.5	9.5	7.2	5	MKP2C026801E00_____	4.5	9.5	7.2	5	MKP2D026801E00_____
0.1 $\mu$ F	5	10	7.2	5	MKP2C031001F00_____	5	10	7.2	5	MKP2D031001F00_____
0.15 "	5.5	11.5	7.2	5	MKP2C031501H00_____	5.5	11.5	7.2	5	MKP2D031501H00_____
0.22 "	7.2	13	7.2	5	MKP2C032201K00_____	7.2	13	7.2	5	MKP2D032201K00_____
0.33 "	8.5	14	7.2	5	MKP2C033301M00_____	8.5	14	7.2	5	MKP2D033301M00_____


  

Capacitance	250 VDC/160 VAC*					400 VDC/200 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
1000 pF						3	7.5	7.2	5	MKP2G011001B00_____
1500 "						3	7.5	7.2	5	MKP2G011501B00_____
2200 "						3	7.5	7.2	5	MKP2G012201B00_____
3300 "						3	7.5	7.2	5	MKP2G013301B00_____
4700 "						3	7.5	7.2	5	MKP2G014701B00_____
6800 "						3	7.5	7.2	5	MKP2G016801B00_____
0.01 $\mu$ F	3	7.5	7.2	5	MKP2F021001B00_____	3.5	8.5	7.2	5	MKP2G021001C00_____
0.015 "	3	7.5	7.2	5	MKP2F021501B00_____	3.5	8.5	7.2	5	MKP2G021501C00_____
0.022 "	3	7.5	7.2	5	MKP2F022201B00_____	4.5	9.5	7.2	5	MKP2G022201E00_____
0.033 "	3	7.5	7.2	5	MKP2F023301B00_____	5.5	11.5	7.2	5	MKP2G023301H00_____
0.047 "	3.5	8.5	7.2	5	MKP2F024701C00_____	7.2	13	7.2	5	MKP2G024701K00_____
0.068 "	4.5	9.5	7.2	5	MKP2F026801E00_____	7.2	13	7.2	5	MKP2G026801K00_____
0.1 $\mu$ F	5	10	7.2	5	MKP2F031001F00_____					
0.15 "	7.2	13	7.2	5	MKP2F031501K00_____					
0.22 "	7.2	13	7.2	5	MKP2F032201K00_____					
0.33 "	8.5	14	7.2	5	MKP2F033301M00_____					

\* AC voltage:  $f \leq 400$  Hz;  $1.4 \times U_{rms} + UDC \leq U_r$

\*\* PCM = Printed circuit module = lead spacing.

Dims. in mm.



#### Part number completion:

Tolerance: 20 % = M

10 % = K

5 % = J

Packing: bulk = S

Lead length: 6-2 = SD

Taped version see page 127.

Rights reserved to amend design data without prior notification.

Continuation page 38

## Continuation

### General Data

Capacitance	630 VDC/250 VAC*					1000 VDC/250 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
1000 pF	3	7.5	7.2	5	MKP2J011001B00_____	3	7.5	7.2	5	MKP2O111001B00_____
1500 "	3	7.5	7.2	5	MKP2J011501B00_____	3	7.5	7.2	5	MKP2O111501B00_____
2200 "	3	7.5	7.2	5	MKP2J012201B00_____	3	7.5	7.2	5	MKP2O112201B00_____
3300 "	3	7.5	7.2	5	MKP2J013301B00_____	3.5	8.5	7.2	5	MKP2O113301C00_____
4700 "	3	7.5	7.2	5	MKP2J014701B00_____	4.5	9.5	7.2	5	MKP2O114701E00_____
6800 "	3.5	8.5	7.2	5	MKP2J016801C00_____	5	10	7.2	5	MKP2O116801F00_____
0.01 µF	4.5	9.5	7.2	5	MKP2J021001E00_____	7.2	13	7.2	5	MKP2O121001K00_____
0.015 "	5	10	7.2	5	MKP2J021501F00_____					
0.022 "	5.5	11.5	7.2	5	MKP2J022201H00_____					
0.033 "	7.2	13	7.2	5	MKP2J023301K00_____					
0.047 "	8.5	14	7.2	5	MKP2J024701M00_____					

\* AC voltage:  $f \leq 400 \text{ Hz}$ ;  $1.4 \times U_{\text{rms}} + \text{UDC} \leq U_r$

\*\* PCM = Printed circuit module = lead spacing.

Dims. in mm.

Part number completion:

Tolerance: 20 % = M

10 % = K

5 % = J


Packing: bulk = S

Lead length: 6-2 = SD

Taped version see page 127.

Rights reserved to amend design data without prior notification.

Permissible AC voltage in relation to frequency at 10° C internal temperature rise (general guide).



## Recommendation for Processing and Application of Through-Hole Capacitors

### Soldering Process

A preheating of through-hole WIMA capacitors is allowed for temperatures  $T_{\max} < 100^{\circ}\text{C}$ . In practice a preheating duration of  $t < 5$  min. has been proven to be best.


#### Single wave soldering

Soldering bath temperature:  $T < 260^{\circ}\text{C}$   
Immersion time:  $t < 5$  sec

#### Double wave soldering

Soldering bath temperature:  $T < 260^{\circ}\text{C}$   
Immersion time:  $2 \times t < 3$  sec

Due to different soldering processes and heat requirements the graphs are to be regarded as a recommendation only.



## WIMA Quality and Environmental Philosophy

### ISO 9001:2000 Certification

ISO 9001:2000 is an international basic standard of quality assurance systems for all branches of industry. The approval according to ISO 9001:2000 of our factories by the VDE inspectorate certifies that organisation, equipment and monitoring of quality assurance in our factories correspond to internationally recognized standards.

### WIMA WPCS

The WIMA Process Control System (WPCS) is a quality surveillance and optimization system developed by WIMA. WPCS is a major part of the quality-oriented WIMA production. Points of application of WPCS during production process:

- incoming material inspection
- metallization
- film inspection
- schoopage
- pre-healing
- lead attachment
- cast resin preparation/encapsulation
- 100% final inspection
- AQL check

### WIMA Environmental Policy

All WIMA capacitors, irrespective of whether through-hole devices or SMD, are made of environmentally friendly materials. Neither during manufacture nor in the product itself any toxic substances are used, e.g.

- Lead
- PCB
- CFC
- Hydrocarbon chloride
- Chromium 6+
- PBB/PBDE
- Arsenic
- Cadmium
- Mercury
- etc.

We merely use pure, recyclable materials for packing our components, such as:

- carton
- cardboard
- adhesive tape made of paper
- polystyrene

We almost completely refrain from using packing materials such as:

- foamed polystyrene (Styropor®)
- adhesive tapes made of plastic
- metal clips

### RoHS Compliance

According to the RoHS Directive 2002/95/EC certain hazardous substances like e.g. lead, cadmium, mercury must not be used any longer in electronic equipment as of July 1st, 2006. For the sake of the environment WIMA has refrained from using such substances since years already.



WIMA Kondensatoren sind bleifrei konform RoHS 2002/95/EG

WIMA capacitors are lead free in accordance with RoHS 2002/95/EC

Tape for lead-free WIMA capacitors

### DIN EN ISO 14001:2005

WIMA's environmental management has been established in accordance with the guidelines of DIN EN ISO 14001:2005. The certification has been granted in June 2006.

# Typical Dimensions for Taping Configuration




Diagram 1:  
PCM 2.5/5/7.5mm

Diagram 2: PCM 10/15 mm

Diagram 3: PCM 22.5 and 27.5\*mm

\*PCM 27.5 taping possible with two feed holes between components

Designation	Symbol	Dimensions for Radial Taping						
		PCM 2.5 taping	PCM 5 taping	PCM 7.5 taping	PCM 10 taping*	PCM 15 taping*	PCM 22.5 taping	PCM 27.5 taping
Carrier tape width	W	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5
Hold-down tape width	W <sub>0</sub>	6.0 for hot-sealing adhesive tape	6.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape
Hole position	W <sub>1</sub>	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5
Hold-down tape position	W <sub>2</sub>	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.
Feed hole diameter	D <sub>0</sub>	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2
Pitch of component	P	12.7 ±1.0	12.7 ±1.0	12.7 ±1.0	25.4 ±1.0	25.4 ±1.0	38.1 ±1.5	38.1 ±1.5 or 50.8 ±1.5
Feed hole pitch	P <sub>0</sub>	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch
Feed hole centre to lead	P <sub>1</sub>	5.1 ±0.5	3.85 ±0.7	2.6 ±0.7	7.7 ±0.7	5.2 ±0.7	7.8 ±0.7	5.3 ±0.7
Hole centre to component centre	P <sub>2</sub>	6.35 ±1.3	6.35 ±1.3	6.35 ±1.3	12.7 ±1.3	12.7 ±1.3	19.05 ±1.3	19.05 ±1.3
Feed hole centre to bottom edge of the component	H	16.5 ±0.3 18.5 ±0.5	16.5 ±0.3 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5
Feed hole centre to top edge of the component	H <sub>1</sub>	H+H <sub>component</sub> < H <sub>1</sub> 32.25 max.	H+H <sub>component</sub> < H <sub>1</sub> 32.25 max.	H+H <sub>component</sub> < H <sub>1</sub> 24.5 to 31.5	H+H <sub>component</sub> < H <sub>1</sub> 25.0 to 31.5	H+H <sub>component</sub> < H <sub>1</sub> 26.0 to 37.0	H+H <sub>component</sub> < H <sub>1</sub> 30.0 to 43.0	H+H <sub>component</sub> < H <sub>1</sub> 35.0 to 45.0
Lead spacing at upper edge of carrier tape	F	2.5 ±0.5	5.0 <sup>+0.8</sup> <sub>-0.2</sub>	7.5 ±0.8	10.0 ±0.8	15 ±0.8	22.5 ±0.8	27.5 ±0.8
Lead diameter	d	0.4 ±0.05	0.5 ±0.05	0.5 ±0.05 or 0.6 <sup>+0.06</sup> <sub>-0.05</sub>	0.5 ±0.05 or 0.6 <sup>+0.06</sup> <sub>-0.05</sub>	0.8 <sup>+0.08</sup> <sub>-0.05</sub>	0.8 <sup>+0.08</sup> <sub>-0.05</sub>	0.8 <sup>+0.08</sup> <sub>-0.05</sub>
Component alignment	Δh	± 2.0 max.	± 2.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.
Total tape thickness	t	0.7 ±0.2	0.7 ±0.2	0.7 ±0.2	0.7 ±0.2	0.7 ±0.2	0.7 ±0.2	0.7 ±0.2
Package (see also page 128)	ROLL/AMMO			AMMO				
	REEL	φ 360 max. φ 30 ±1	B 52 ±2 58 ±2 } depending on comp. dimensions	REEL	φ 360 max. φ 30 ±1	52 ±2 58 ±2 or 66 ±2	REEL	φ 500 max. φ 25 ±1
Unit	see details page 130.							

Dims in mm.

\* Diameter of leads see General Data.

\* PCM 10 and PCM 15 can be crimped to PCM 7.5.

Position of components according to PCM 7.5 (sketch 11). P<sub>0</sub> = 12.7 or 15.0 is possible

Please clarify customer-specific deviations with the manufacturer.

# Packing Quantities for Bulk Capacitors and TPS\*



PCM	Size				pcs. per packaging unit bulk			pcs. per packaging unit/TPS*	
	W	H	L	Codes	Mini <b>M</b>	Standard <b>S</b>	Maxi <b>G</b>	Mini <b>X</b>	Standard <b>Y</b>
<b>2.5 mm</b>	2.5	7	4.6	<b>0B</b>	1000	5000	10 000	-	-
	3	7.5	4.6	<b>0C</b>	1000	5000	10 000	-	-
	3.8	8.5	4.6	<b>0D</b>	1000	5000	10 000	-	-
	4.6	9	4.6	<b>0E</b>	1000	5000	10 000	-	-
	5.5	10	4.6	<b>0F</b>	1000	5000	10 000	-	-
<b>5 mm</b>	2.5	6.5	7.2	<b>1A</b>	2000	5000	10 000	-	-
	3	7.5	7.2	<b>1B</b>	1000	5000	-	-	-
	3.5	8.5	7.2	<b>1C</b>	1000	5000	-	-	-
	4.5	6	7.2	<b>1D</b>	1000	6000	-	-	-
	4.5	9.5	7.2	<b>1E</b>	1000	4000	-	-	-
	5	10	7.2	<b>1F</b>	1000	3500	-	-	-
	5.5	7	7.2	<b>1G</b>	1000	4000	-	-	-
	5.5	11.5	7.2	<b>1H</b>	500	2500	-	-	-
	6.5	8	7.2	<b>1I</b>	1000	2500	-	-	-
	7.2	8.5	7.2	<b>1J</b>	500	2500	-	-	-
	7.2	13	7.2	<b>1K</b>	500	2000	-	-	-
	8.5	10	7.2	<b>1L</b>	500	2000	-	-	-
	8.5	14	7.2	<b>1M</b>	500	1500	-	-	-
11	16	7.2	<b>1N</b>	250	1000	-	-	-	
<b>7.5 mm</b>	2.5	7	10	<b>2A</b>	1000	5000	-	-	-
	3	8.5	10	<b>2B</b>	1000	5000	-	-	-
	4	9	10	<b>2C</b>	1000	4000	-	-	-
	4.5	9.5	10.3	<b>2D</b>	1000	3500	-	-	-
	5	10.5	10.3	<b>2E</b>	1000	3000	-	-	-
	5.7	12.5	10.3	<b>2F</b>	500	2000	-	-	-
	7.2	12.5	10.3	<b>2G</b>	500	1500	-	-	-
<b>10 mm</b>	3	9	13	<b>3A</b>	1000	3000	-	-	-
	4	8.5	13.5	<b>3A</b>	500	3000	-	-	-
	4	9	13	<b>3C</b>	1000	3000	-	-	-
	4	9.5	13	<b>3D</b>	1000	3000	-	-	-
	5	10	13.5	<b>3B</b>	500	2000	-	-	-
	5	11	13	<b>3F</b>	1000	3000	-	-	-
	6	12	13	<b>3G</b>	800	2400	-	-	-
	6	12.5	13	<b>3H</b>	800	2400	-	-	-
8	12	13	<b>3I</b>	500	2000	-	-	-	
<b>15 mm</b>	5	11	18	<b>4B</b>	800	2400	-	-	-
	5	13	19	<b>4C</b>	200	1000	-	-	-
	6	12.5	18	<b>4C</b>	500	2000	-	-	-
	6	14	19	<b>4D</b>	250	1000	-	-	-
	7	14	18	<b>4D</b>	400	1600	-	-	-
	7	15	19	<b>4E</b>	250	1000	-	-	-
	8	15	18	<b>4F</b>	400	1200	-	-	-
	8	17	19	<b>4F</b>	100	500	-	-	-
	9	14	18	<b>4H</b>	400	1200	-	-	-
	9	16	18	<b>4J</b>	300	900	-	-	-
	10	18	19	<b>4G</b>	100	500	-	-	-
11	14	18	<b>4M</b>	300	1000	-	-	-	
<b>22.5 mm</b>	5	14	26.5	<b>5A</b>	300	1200	-	-	-
	6	15	26.5	<b>5B</b>	250	1000	-	-	-
	7	16.5	26.5	<b>5D</b>	190	760	-	-	-
	8	20	28	<b>5H</b>	125	500	-	-	-
	8.5	18.5	26.5	<b>5F</b>	125	500	-	-	-
	10	22	28	<b>5I</b>	-	-	-	90	540
	10.5	19	26.5	<b>5G</b>	-	-	-	170	680
	10.5	20.5	26.5	<b>5H</b>	-	-	-	170	680
	11	21	26.5	<b>5I</b>	-	-	-	170	680
	12	24	28	<b>5J</b>	-	-	-	75	450
<b>27.5 mm</b>	9	19	31.5	<b>6A</b>	-	-	-	160	640
	11	21	31.5	<b>6B</b>	-	-	-	136	544
	13	24	31.5	<b>6D</b>	-	-	-	112	448
	13	25	33	<b>6K</b>	-	-	-	56	336
	15	26	31.5	<b>6F</b>	-	-	-	96	384
	15	26	33	<b>6L</b>	-	-	-	48	288
	17	29	31.5	<b>6G</b>	-	-	-	88	176
	17	34.5	31.5	<b>6I</b>	-	-	-	88	176
	20	32	33	<b>6M</b>	-	-	-	36	216
	20	39.5	31.5	<b>6J</b>	-	-	-	36	144
<b>37.5 mm</b>	9	19	41.5	<b>7A</b>	-	-	-	60	480
	11	22	41.5	<b>7B</b>	-	-	-	51	408
	13	24	41.5	<b>7C</b>	-	-	-	84	252
	15	26	41.5	<b>7D</b>	-	-	-	72	144
	17	29	41.5	<b>7E</b>	-	-	-	66	132
	19	32	41.5	<b>7F</b>	-	-	-	54	108
	20	39.5	41.5	<b>7G</b>	-	-	-	27	108
	24	45.5	41.5	<b>7H</b>	-	-	-	21	84



## Packing Units for Taped Capacitors with Radial Leads

PCM	Size				ROLL		REEL				AMMO			
					H16.5	H18.5	ø 360		ø 500		340 x 340		490 x 370	
	W	H	L	Codes	N	O	F	I	H	J	A	C	B	D
<b>2.5 mm</b>	2.5	7	4.6	<b>0B</b>	2200		2500				2800			
	3	7.5	4.6	<b>0C</b>	2000		2300				2300			
	3.8	8.5	4.6	<b>0D</b>	1500		1800				1800			
	4.6	9	4.6	<b>0E</b>	1200		1500				1500			
	5.5	10	4.6	<b>0F</b>	900		1200				1200			
<b>5 mm</b>	2.5	6.5	7.2	<b>1A</b>	2200		2500				2800			
	3	7.5	7.2	<b>1B</b>	2000		2300				2300			
	3.5	8.5	7.2	<b>1C</b>	1600		2000				2000			
	4.5	6	7.2	<b>1D</b>	1300		1500				1500			
	4.5	9.5	7.2	<b>1E</b>	1300		1500				1500			
	5	10	7.2	<b>1F</b>	1100		1400				1400			
	5.5	7	7.2	<b>1G</b>	1000		1200				1200			
	5.5	11.5	7.2	<b>1H</b>	1000		1200				1200			
	6.5	8	7.2	<b>1I</b>	800		1000				1000			
	7.2	8.5	7.2	<b>1J</b>	700		1000				1000			
	7.2	13	7.2	<b>1K</b>	700		950				1000			
	8.5	10	7.2	<b>1L</b>	600		800				800			
	8.5	14	7.2	<b>1M</b>	600		800				800			
11	16	7.2	<b>1N</b>	500		700				700				
<b>7.5 mm</b>	2.5	7	10	<b>2A</b>			2500		4400		2500			
	3	8.5	10	<b>2B</b>			2200		4300		2300		4150	
	4	9	10	<b>2C</b>			1700		3200		1700		3100	
	4.5	9.5	10.3	<b>2D</b>			1500		2900		1400		2800	
	5	10.5	10.3	<b>2E</b>			1300		2500		1300			
	5.7	12.5	10.3	<b>2F</b>			1000		2200		1100			
	7.2	12.5	10.3	<b>2G</b>			900		1800		1000			
<b>10 mm</b>	3	9	13	<b>3A</b>			1100		2200				1900	
	4	8.5	13.5	<b>FA</b>			900		1600				1450	
	4	9	13	<b>3C</b>			900		1600				1450	
	4	9.5	13	<b>3D</b>			900		1600				1400	
	5	10	13.5	<b>FB</b>			700		1300				1200	
	5	11	13	<b>3F</b>			700		1300				1200	
	6	12	13	<b>3G</b>			550		1100				1000	
	6	12.5	13	<b>3H</b>			550		1100				1000	
8	12	13	<b>3I</b>			400		800				740		
<b>15 mm</b>	5	11	18	<b>4B</b>			600		1200				1150	
	5	13	19	<b>FC</b>			600		1200				1200	
	6	12.5	18	<b>4C</b>			500		1000				1000	
	6	14	19	<b>FD</b>			500		1000				1000	
	7	14	18	<b>4D</b>			450		900				850	
	7	15	19	<b>FE</b>			450		900				850	
	8	15	18	<b>4F</b>			400		800				740	
	8	17	19	<b>FF</b>			400		800				740	
	9	14	18	<b>4H</b>			350		700				650	
	9	16	18	<b>4J</b>			350		700				650	
	10	18	19	<b>FG</b>			300		650				590	
11	14	18	<b>4M</b>			300		600				540		
<b>22.5 mm</b>	5	14	26.5	<b>5A</b>					800				770	
	6	15	26.5	<b>5B</b>					700				640	
	7	16.5	26.5	<b>5D</b>					600				550	
	8	20	28	<b>FH</b>					500				480	
	8.5	18.5	26.5	<b>5F</b>					480				450	
	10	22	28	<b>FI</b>					420				380	
	10.5	19	26.5	<b>5G</b>					400				360	
	10.5	20.5	26.5	<b>5H</b>					400				360	
	11	21	26.5	<b>5I</b>					380				350	
	12	24	28	<b>FJ</b>					350				310	
<b>27.5 mm</b>	9	19	31.5	<b>6A</b>					460/340*				420	
	11	21	31.5	<b>6B</b>					380/280*				350	
	13	24	31.5	<b>6D</b>					300				290	
	15	26	31.5	<b>6F</b>					270				250	

\* for 2-inch transport pitches.

Samples and pre-production needs 1 packing unit minimum.

■ Moulded versions.

Rights reserved to amend design data without prior notification.



A WIMA part number consists of 18 digits and is composed as follows:

- Field 1 - 4: Type description
- Field 5 - 6: Rated voltage
- Field 7 - 10: Capacitance
- Field 11 - 12: Size and PCM
- Field 13 - 14: Special features (e.g. Snubber versions)
- Field 15: Capacitance tolerance
- Field 16: Packing
- Field 17 - 18: Lead length (untaped)

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18
<b>M</b>	<b>K</b>	<b>S</b>	<b>2</b>	<b>C</b>	<b>0</b>	<b>2</b>	<b>1</b>	<b>0</b>	<b>0</b>	<b>1</b>	<b>A</b>	<b>0</b>	<b>0</b>	<b>M</b>	<b>S</b>	<b>S</b>	<b>D</b>
MKS 2				63 VDC		0.01 µF			2.5x6.5x7.2			-		20%	bulk	6 -2	

<p><b>Type description:</b></p> <p>SMD-PET = SMDT  SMD-PPS = SMDI  FKP 02 = FKP0  MKS 02 = MKS0  FKS 2 = FKS2  FKP 2 = FKP2  MKS 2 = MKS2  MKP 2 = MKP2  FKS 3 = FKS3  FKP 3 = FKP3  MKS 4 = MKS4  MKP 4 = MKP4  MKP 10 = MKP1  FKP 4 = FKP4  FKP 1 = FKP1  MKP-X2 = MKX2  MKP-X2 R = MKXR  MKP-Y2 = MKY2  MP 3-X2 = MPX2  MP 3-X1 = MPX1  MP 3-Y2 = MPY2  MP 3R-Y2 = MPRY  Snubber MKP = SNMP  Snubber FKP = SNFP  GTO MKP = GTOM  DC-LINK MKP 4 = DCP4  DC-LINK MKP C = DCPC  DC-LINK HC = DCH_  SuperCap C = SCSC  SuperCap MC = SMC  SuperCap R = SCSR  SuperCap MR = SCMR</p>	<p><b>Rated voltage:</b></p> <p>2.5 VDC = A1  4 VDC = A2  14 VDC = A3  28 VDC = A4  40 VDC = A5  5 VDC = A6  50 VDC = B0  63 VDC = C0  100 VDC = D0  160 VDC = E0  250 VDC = F0  400 VDC = G0  450 VDC = H0  600 VDC = I0  630 VDC = J0  700 VDC = K0  800 VDC = L0  850 VDC = M0  900 VDC = N0  1000 VDC = O1  1100 VDC = P0  1200 VDC = Q0  1250 VDC = R0  1500 VDC = S0  1600 VDC = T0  2000 VDC = U0  2500 VDC = V0  3000 VDC = W0  4000 VDC = X0  6000 VDC = Y0  250 VAC = 0W  275 VAC = 1W  300 VAC = 2W  400 VAC = 3W  440 VAC = 4W  500 VAC = 5W</p>	<p><b>Capacitance:</b></p> <p>22 pF = 0022  47 pF = 0047  100 pF = 0100  150 pF = 0150  220 pF = 0220  330 pF = 0330  470 pF = 0470  680 pF = 0680  1000 pF = 1100  1500 pF = 1150  2200 pF = 1220  3300 pF = 1330  4700 pF = 1470  6800 pF = 1680  0.01 µF = 2100  0.022 µF = 2220  0.047 µF = 2470  0.1 µF = 3100  0.22 µF = 3220  0.47 µF = 3470  1 µF = 4100  2.2 µF = 4220  4.7 µF = 4470  10 µF = 5100  22 µF = 5220  47 µF = 5470  100 µF = 6100  220 µF = 6220  1 F = A010  2.5 F = A025  50 F = A500  100 F = B100  110 F = B110  600 F = B600  1200 F = C120  ...</p>	<p><b>Size:</b></p> <p>4.8x3.3x3 Size 1812 = X1  4.8x3.3x4 Size 1812 = X2  5.7x5.1x3.5 Size 2220 = Y1  5.7x5.1x4.5 Size 2220 = Y2  7.2x6.1x3 Size 2824 = T1  7.2x6.1x5 Size 2824 = T2  10.2x7.6x5 Size 4030 = K1  12.7x10.2x6 Size 5040 = V1  15.3x13.7x7 Size 6054 = Q1  2.5x7x4.6 PCM 2.5 = 0B  3x7.5x4.6 PCM 2.5 = 0C  2.5x6.5x7.2 PCM 5 = 1A  3x7.5x7.2 PCM 5 = 1B  2.5x7x10 PCM 7.5 = 2A  3x8.5x10 PCM 7.5 = 2B  3x9x13 PCM 10 = 3A  4x9x13 PCM 10 = 3C  5x11x18 PCM 15 = 4B  6x12.5x18 PCM 15 = 4C  5x14x26.5 PCM 22.5 = 5A  6x15x26.5 PCM 22.5 = 5B  9x19x31.5 PCM 27.5 = 6A  11x21x31.5 PCM 27.5 = 6B  9x19x41.5 PCM 37.5 = 7A  11x22x41.5 PCM 37.5 = 7B  94x49x182 DCH_ = H0  94x77x182 DCH_ = H1  ...</p>	<p><b>Tolerance:</b></p> <p>20% = M  10% = K  5% = J  2.5% = H  1% = E  ...</p> <p><b>Packing:</b></p> <p>AMMO H16.5 340x340 = A  AMMO H16.5 490x370 = B  AMMO H18.5 340x340 = C  AMMO H18.5 490x370 = D  REEL H16.5 360 = F  REEL H16.5 500 = H  REEL H18.5 360 = I  REEL H18.5 500 = J  ROLL H16.5 = N  ROLL H18.5 = O  BLISTER W12 180 = P  BLISTER W12 330 = Q  BLISTER W16 330 = R  BLISTER W24 330 = T  Bulk Mini = M  Bulk Standard = S  Bulk Maxi = G  TPS Mini = X  TPS Standard = Y  ...</p>	
<p><b>Special features:</b></p> <p>Standard = 00  Version A1 = 1A  Version A1.1.1 = 1B  Version A1.2 = 1C  ...</p>					<p><b>Lead length (untaped)</b></p> <p>3.5 ±0.5 = C9  6 -2 = SD  16 ±1 = P1  ...</p>

The data on this page is not complete and serves only to explain the part number system. Part number information is listed on the pages of the respective WIMA range.