

K90DWN2-V1-F 29/Sep 2010 PAGE 1 OF 14

K90DWN2-V1-F

Product

Standard LCD Module 800 x RGB x 480 Dots 9 inch 16.7M colors TFT display Wide temperature With white LED backlight With resistive touch screen

Kentec Electronics (Displays) Limited URL: <u>http://www.kentec.com.hk</u> E-mail: <u>t.liang@kentec.com.hk</u>; <u>mf.zou@kentec.com.hk</u>



K90DWN2-V1-F 29/Sep 2010 PAGE 2 OF 14

CONTENTS

Page No.

1.	DOCUMENT REVISION HISTORY	3
2.	GENERAL DESCRIPTION	4
3.	MECHANICAL SPECIFICATIONS	5-6
4.	INTERFACE SIGNALS	7
5.	ABSOLUTE MAXIMUM RATINGS	8
6.	ELECTRICAL SPECIFICATIONS	8
7.	OPTICAL CHARACTERISTICS	9
8.	TIMING CHARACTERISTICS	10
9.	RELIABILITY TEST ITEM	12
10.	SUGGESTIONS FOR USING LCD MODULES	13
12.	PACKING(REFERENCE ONLY)	14



K90DWN2-V1-F

29/Sep 2010

PAGE 3 OF 14

1. Document	revision his	tory :		
DOCUMENT REVISION	DATE	DESCRIPTION	PREPARED BY	APPROVED BY
01 02	2010.09.29 2010.12.30		MF Zou MF Zou	В1



2. General Description


NO.	Item	Unit	Specification	Remark
1	Screen Size	inch	9(Diagonal)	
2	Display Resolution	Dot	800RGB(W)x480(H)	
3	Overall Dimension	mm	211.1(W)x126.5(H)x8.8 (D)	Note 1
4	Active Area	mm	198.0(W)x111.7(H)	
5	Pixel Pitch	mm	0.2327(W)x0.2327(H)	
6	Color Configuration	-	Tri-Gate	
7	Color Depth	-	16.7M Color	Note 2
8	NTSC Ratio	%	50	
9	Display Mode	-	Normally White	
10	Panel Surface Treatment	-	Anti-Glare, 3H	
11	Weight	g	TBD	
12	Panel Power Consumption	mW	TBD	
13	Backlight Power Consumption	W	2.2(typ.)	
14	Viewing Direction		6 o'clock(Gray inversion)	


Note 1: Not include controller board and FPC.

Note 2: Full color display depends on 24-bit data signal.



3. Mechanical Specifications







K90DWN2-V1-F 29/Sep 2010

PAGE 7 OF 14

4. Interface signals

	C	Table 2: Pin assignment	
Pin No.	Symbol	Description	
1	GND	Ground for digital circuit	
2	VDD	Power supply for digital circuit (VDD = 3.3 V).	
3	AVDD	Power supply for analog circuit (AVDD $= 5V$).	
4	RESET	External reset, active low.	
5	CS	Chip select, active low.	
6	RS	Command/data select.	
7	WR	Write control.	
8	RD	Read control.	
9-24	[DB0-DB15]	16bit data bus	
25	NC	NO CONNECT	
26	GND	Ground for digital circuit	
27-29	NC	NO CONNECT	
30	GND	Ground for digital circuit	
31-32	AGND	Ground for analog circuit	
33-34	AVDD	Power supply for analog circuit (AVDD $= 5V$).	
35,36	NC	NO CONNECT	
37	YU		
38	XL	Touch panel terminal	
39	YD		
40	XR		

5. Absolute Maximum Ratings

5.1 Electrical Maximum Ratings – for IC Only

Table 3: Electrical Maximum Ratings - for IC

Parameter	Symbol	Min.	Max.	Unit	Note
Supply voltage	VCC	-0.3	5.0	V	1
LED forward current	If		30	mA	
LED reverse	Vr		5.0	V	

Note:

1.VCC, GND must be maintained.

2. The modules may be destroyed if they are used beyond the absolute maximum ratings.

5.2 Environmental Condition

Table 4						
Item	Operat tempera (Top	iture	Storage temperature (Tstg) (Note 1)		Remark	
	Min.	Max.	Min.	Max.		
Ambient temperature	-20°C	+70°C	-30°C	+80°C	Dry	
Humidity (Note 1)	80% max. RH for Ta $\leq 40^{\circ}$ CNo< 50% RH for 40°C < Ta \leq Maximum operating temperaturecondensati					

Note 1: Product cannot sustain at extreme storage conditions for long time.

6. Electrical Specifications

Typical Electrical Characteristics

At Ta = 25 °C, VCC=IOVCC= 3.3V, GND=0V.

		Table 5				
Parameter	Symbol	Conditions	Min.	Тур.	Max.	Unit
Supply voltage (logic)	VDD-GND		3	3.3	3.6	V
Supply voltage (analog)	AVDD-GND		4.8	5.0	5.2	V
Input signal voltage	VIH		0.8VDD	-	VDD	V
input signal voltage	VIL		0	-	0.2VDD	V
Supply current (Logic & LCD)	IDD	VDD=3.3V	-	15	19	mA
Supply current (Analog & LED)	IA	AVDD=5.0V	-	T.B.D.	T.B.D.	V



K90DWN2-V1-F 29/Sep 2010

PAGE 9 OF 14

7. Optical Characteristics

Table 6: Optical specifications								
Itama		Symbol	Condition	Condition Specifications			Unit	
Items		Symbol	Condition	Min.	Тур.	Max.	Omt	
Luminand	ce	Lw		200	250	-	cd/m^2	
Contrast Ra	atio	CR		400	500	-	-	
Response T	ime	$T_R + T_F$		-	25	50	ms	Note
Chromaticity	White	X_{W}		(0.26)	(0.31)	(0.36)	-	
Chromaticity	w mie	Y_W		(0.28)	(0.33)	(0.38)	-	
Viewing angle	Hor.	$\phi 1 + \phi 2$	Center	120	140	-	dag	
viewing angle	Ver.	$\theta 1 + \theta 2$	CR=10	100	120	-	deg.	

Note 1: Definition of Contrast Ratio (CR):

The contrast ratio can be calculated by the following expression.

Contrast Ratio (CR) = L63 / L0


L63: Luminance of gray level 63

L0: Luminance of gray level 0

CR = CR (10)

CR (X) is corresponding to the Contrast Ratio of the point X at Figure in Note 5.

Note 2: Definition of Response Time (TR, TF):





Note 3: Viewing Angle




Figure 4



The above "Viewing Angle" is the measuring position with Largest Contrast Ratio; not for good image quality. View Direction for good image quality is 6 O'clock. Module maker can increase the "Viewing Angle" by applying Wide View Film.

Note 4: Measurement Set-Up:

The LCD module should be stabilized at a given temperature for 20 minutes to avoid abrupt temperature change during measuring. In order to stabilize the luminance, the measurement should be executed after lighting Backlight for 20 minutes in a windless room.





Figure 5

8. AC Characteristics and Signal timing


8.1 Please refer SSD1963 datasheet.





PAGE 11 OF 14

8.2 Horizontal input timing.



8.3 Timing

Item	Symbol		Values			Remark	
Item	Symbol	Min.	Тур.	Max.	Unit	Keinai K	
Horizontal Display Area	thd	-	800	-	DCLK		
DCLK Frequency	fclk	26.4	33.3	46.8	MHz		
One Horizontal Line	th	862	1056	1200	DCLK		
HS Pulse Width	thpw	1	-	40	DCLK		
HS Blanking	thb	46	46	46	DCLK		
HS Front Porch	thfp	16	21	354	DCLK		
Vertical Display Area	tvd	-	480	-	TH		
VS Period Time	tv	510	525	650	TH		
VS Pulse Width	tvpw	1	-	20	TH		
VS Blanking	tvb	23	23	23	TH		
VS Front Porch	tvfp	7	22	147	TH		



		9. Kenability Test Item	
	Test Item	Test Condition	Remark
1	High temperature storage	70 ; 240H	
2	Low temperature storage	-20 ; 240H	
3	High temperature High humidity	50 , 80%RH; 240H	Operation
4	High temperature operation	60 ; 240H	
5	Low temperature operation	-10 ; 240H	
6	Temperature Shock	-20 ? 60 ; 100cycle, 1Hrs/cycle	Non-operation
7	Electrostatic Discharge	Contact ± 4kV, Class B Air ± 8kV, Class B	
8	Image sticking	25 ,4H	
9	Vibration	Frequency range : 10~55Hz Stoke : 1.5mm Sweep : 10~55~10Hz 2 Hours for each direction of X,Y,Z (total 6 Hours)	Non-operation JIS C7021, A-10 Condiction A : 15 minutes
10	Mechanical shock	100G, 6ms, $\pm X$, $\pm Y$, $\pm Z$, 3 times for each direction	Non-operation JIS C7021, A-10 Condiction C
11	Vibration (with carton)	Random vibration : 0.015G ² /Hz from 2~200Hz -6dB/Octave from 200~500Hz	ICE 68-34
12	Drop (with carton)	Height : 60cm 1 corner, 3 edges, 6 surfaces	
13	Pressure	5 kg, 5 sec	

9. Reliability Test Item



10. Suggestions for using LCD modules

10.1 Handling of LCM

- 1. The LCD screen is made of glass. Don't give excessive external shock, or drop from a high place.
- 2. If the LCD screen is damaged and the liquid crystal leaks out, do not lick and swallow. When the liquid is attach to your hand, skin, cloth etc, wash it off by using soap and water thoroughly and immediately.
- 3. Don't apply excessive force on the surface of the LCM.
- 4. If the surface is contaminated ,clean it with soft cloth. If the LCM is severely contaminated , use Isopropyl alcohol/Ethyl alcohol to clean. Other solvents may damage the polarizer . The following solvents is especially prohibited: water , ketone Aromatic solvents etc.
- 5. Exercise care to minimize corrosion of the electrode. Corrosion of the electrodes is accelerated by water droplets, moisture condensation or a current flow in a high-humidity environment.
- 6. Install the LCD Module by using the mounting holes. When mounting the LCD module make sure it is free of twisting, warping and distortion. In particular, do not forcibly pull or bend the I/O cable or the backlight cable.

7. Don't disassemble the LCM.

- 8. To prevent destruction of the elements by static electricity, be careful to maintain an optimum work environment.
 - Be sure to ground the body when handling the LCD modules.
 - Tools required for assembling, such as soldering irons, must be properly grounded.
 - To reduce the amount of static electricity generated, do not conduct assembling and other work under dry conditions.
 - The LCD module is coated with a film to protect the display surface. Exercise care when peeling off this protective film since static electricity may be generated.

9. Do not alter, modify or change the the shape of the tab on the metal frame.

10. Do not make extra holes on the printed circuit board, modify its shape or change the positions of components to be attached.

- 11. Do not damage or modify the pattern writing on the printed circuit board.
- 12. Absolutely do not modify the zebra rubber strip (conductive rubber) or heat seal connector
- 13. Except for soldering the interface, do not make any alterations or modifications with a soldering iron.
- 14. Do not drop, bend or twist LCM.

10.2 Storage

- 1. Store in an ambient temperature of 5 to 45 °C, and in a relative humidity of 40% to 60%. Don't expose to sunlight or fluorescent light.
- 2. Storage in a clean environment, free from dust, active gas, and solvent.
- 3. Store in antistatic container.

11. Packing Method TBD

- END -