



Description

The Redington Model 732 provides a DC Hour Meter with an operating range of 10-80VDC. Models are available in the standard industry housings, 3-Hole Round, Flush-Rectangular, Flush-Round and 2-Hole Rectangular. Models 732-0002 and 732-0004 fit a panel opening of 1.45" X 0.95" [36.8mm X 24.1mm]. The Flush-Round Model 732-0003 and 3-Hole Model 732-0001 fit a panel opening of 2.0" [50.6mm]. Its quartz time base insures accurate long-term time keeping. The Totally Sealed case protects against the environment and provides years of reliable service. The 3-Hole Round housing is NEMA 4X,12 rated when mounted with optional gasket.

Features

- Operating voltage 10-80VDC
- Totally sealed
- UL/CSA Recognized, CE Compliant
- 6 Figure, 99999.9
- Quartz accuracy

Options

- Wire leads
- 3-hole mount gasket kit (part# 5003-007S) (for NEMA 4X, 12 rating)

Specifications

Figures: 6 - digits, 0.125" [3.2mm] 99999.9
 Hours - white on black
 Tenths - red on white

Reset: Non-reset

Voltage: 10-80VDC

Power: 0.3 watts @ 12VDC

Mounting: Clip or mounting holes

Termination: ¼" [6.3mm] spade terminals

Weight: 2.0 oz [57 g]

Accuracy: ± 0.02 over entire range

Case Material: Black polymer

Agency Approvals: UL/CSA Recognized, CE Compliant

Environmental: Totally sealed (all models)

Front Panel: Model: 732-0001, NEMA 4X, 12 rated with optional gasket (part# 5003-007S)

Temperature: -40°F to +185°F [-40°C to + 85°C]

Vibration: 10-75 Hz @ 1 to 8g's

Models Description

732-0001	3-Hole Round,	10-80VDC,	¼" [6.3mm] spade terminals,	hours & 1/10's
732-0002	Flush-Rectangular,	10-80VDC,	¼" [6.3mm] spade terminals,	hours & 1/10's
732-0003	Flush-Round,	10-80VDC,	¼" [6.3mm] spade terminals,	hours & 1/10's
732-0004	2-Hole Rectangular,	10-80VDC,	¼" [6.3mm] spade terminals,	hours & 1/10's
5003-007S	NEMA 4X, 12 Gasket kit and hardware for 3-Hole Round model (732-0001)			

* All items are normally in factory stock.

[17.5]

[38.1]

[12.5]

Outdoor power equipment

Utility Vehicles