



SAFETY DATA SHEET

ROOF AND GUTTER SEALANT

Page 1
Issued: 9/3/10
Revision No: 4

1. IDENTIFICATION OF THE SUBSTANCE / MIXTURE AND OF THE COMPANY / UNDERTAKING

Product name: ROOF AND GUTTER SEALANT
Product code: ROOF
Company name: EVERBUILD BUILDING PRODUCTS LTD
SITE 41, KNOWSTHORPE WAY
CROSS GREEN INDUSTRIAL ESTATE
LEEDS
WEST YORKSHIRE
LS9OSW
ENGLAND
Tel: 0044 113 240 3456
Fax: 0044 113 240 0024
Emergency tel: 0044 113 240 3456 (office hours only)
Email: pault@everbuild.co.uk

2. HAZARDS IDENTIFICATION

Workplace exposure limit: This substance does not have a workplace exposure limit.
PBT: This substance is not identified as a PBT substance.
Directive 1999/45/EC: This does not meet the criteria for classification as dangerous in accordance with Directive 1999/45/EC.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous ingredients: LOW BOILING POINT HYDROGEN TREATED NAPHTHA - NAPHTHA (PETROLEUM), HYDRODESULPHURIZED HEAVY 1-10%
EINECS: 265-185-4 CAS: 64742-82-1
[T] R46; [Xn] R65; [-] R10; [N] R51/53
• DISTILLATES, PETROLEUM, HYDROTREATED, MIDDLE 1-10%
CAS: 64742-46-7
[Xn] R65

4. FIRST AID MEASURES

Skin contact: Wash immediately with plenty of soap and water.
Eye contact: Bathe the eye with running water for 15 minutes.
Ingestion: Wash out mouth with water. Do not induce vomiting. Consult a doctor.
Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

5. FIRE-FIGHTING MEASURES

Extinguishing media: Dry chemical powder. Carbon dioxide. Alcohol or polymer foam. Water spray.

[cont...]

SAFETY DATA SHEET
ROOF AND GUTTER SEALANT

Exposure hazards: In combustion emits toxic fumes.

Protection of fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions: Refer to section 8 of SDS for personal protection details.

Environmental precautions: Do not discharge into drains or rivers.

Clean-up procedures: Absorb into dry earth or sand.

7. HANDLING AND STORAGE

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area. Smoking is forbidden.

Storage conditions: Store in cool, well ventilated area. Keep container tightly closed. Store in original containers between +5 and +25`C. Storage outside these paramaters will dramatically reduce shelf life and invalidates all product warrenties.

Suitable packaging: Must only be kept in original packaging.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Engineering measures: Ensure there is sufficient ventilation of the area.

Respiratory protection: Respiratory protection not required. in normal use. Gas/vapour filter, type A: organic vapours (EN141). must be worn if vapour concentration is above OES or if ventilation is poor

Hand protection: Protective gloves.

Eye protection: Safety glasses.

Skin protection: Protective clothing.

9. PHYSICAL AND CHEMICAL PROPERTIES

State: Paste

Colour: Black

Odour: Characteristic odour

Evaporation rate: Moderate

Solubility in water: Not miscible

Also soluble in: Most organic solvents.

Viscosity: Highly viscous

Flash point°C: >60

Vapour pressure: n.d

Relative density: ~1.8

pH: n/a

VOC g/l: 2

10. STABILITY AND REACTIVITY

Stability: Stable under normal conditions.

Conditions to avoid: Heat.

Materials to avoid: Strong oxidising agents. Strong acids.

Haz. decomp. products: In combustion emits toxic fumes.

11. TOXICOLOGICAL INFORMATION**11. TOXICOLOGICAL INFORMATION (SYMPTOMS)**

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be soreness and redness of the mouth and throat.

12. ECOLOGICAL INFORMATION

Mobility: Readily absorbed into soil.

Persistence and degradability: No data available.

Bioaccumulative potential: No data available.

PBT identification: This substance is not identified as a PBT substance.

13. DISPOSAL CONSIDERATIONS

Disposal operations: Dispose of according to local or national legislation

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

14. TRANSPORT INFORMATION**ADR / RID**

UN no: Not Classified.

IMDG / IMO

UN no: Not Classified.

IATA / ICAO

UN no: Not Classified.

15. REGULATORY INFORMATION (CHIP)

Hazard symbols: No significant hazard.

Note: The regulatory information given above only indicates the principal regulations specifically applicable to the product described in the safety data sheet. The user's attention is drawn to the possible existence of additional provisions which complete these regulations. Refer to all applicable national, international and local regulations or provisions.

SAFETY DATA SHEET
ROOF AND GUTTER SEALANT

16. OTHER INFORMATION

Other information: This safety data sheet is prepared in accordance with Regulation (EC) No 1907/2006.

* indicates text in the SDS which has changed since the last revision.

Risk phrases used in s.3: R46: May cause heritable genetic damage.

R65: Harmful: may cause lung damage if swallowed.

R10: Flammable.

R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.