

MATERIAL SAFETY DATA SHEET

MAY BE USED TO COMPLY WITH OSHA'S
HAZARD COMMUNICATION STANDARD
29CFR 1910.1200

Static Control Components,
P.O. BOX 152
Sanford North Carolina 27331

Emergency telephone number 1-800-356-2728
telephone number 1-919-774-3808

DATE PREPARED 8/26/2004 SIGNATURE OF PREPARER (OPTIONAL)

SECTION 1 CHEMICAL PRODUCT / NAME

Product/Chemical Name: Samsung ML-1710 / 1750

CAS Number: Mixture

Other Designations: N/A

General Use: Laser Printer

SECTION 2 COMPOSITION / INFORMATION ON INGREDIENTS

Ingredient Name:	CAS NUMBER	%	OSHA PEL	ACGIH TLV	OTHER LIMITS
					Toner is regulated under OSHA as particulate not otherwise regulated:
Polyester	25038-59-9	88 - 92			
Polypropylene	9003-07-0	2 - 4			
Carbon Black	1333-86-4	3 - 6			
Additive	31714-55-3	2			

NDA = NO DATA AVAILABLE

N/A = NOT APPLICABLE

SECTION 3 HAZARDOUS IDENTIFICATION

Primary Entry Routes:	Inhalation	HMIS H 1 F 1 R 0 PPE Sec.8
Target Organs:	N/A	
Acute Effects:	N/A	
Inhalation:	Slight irritation of respiratory tract.	
Eye:	Dust may cause irritation by mechanical abrasion.	
Skin:	Slight irritation.	
Ingestion:	None known.	
Carcinogenicity:	N/A	
Medical Conditions Aggravated By Long-Term Exposure:	Accumulation of dust in the respiratory system may cause congestion.	
Chronic Effects:	If these materials are used in a manner that could generate airborne particles (dust), it is recommended that the dust be treated as a NUISANCE PARTICULATE according to the American Conference of Government Industrial Hygienists (ACGIH)(TLV=10mg/m3).	

SECTION 4 FIRST AID MEASURES

Inhalation:	Remove to fresh air. Treat any irritation symptomatically. Call a physician if condition persists.
Eye Contact:	In case of contact immediately flush with plenty of low pressure water for at least 15 minutes. Remove any contact lenses to ensure thorough flushing.
Skin Contact:	Wash well with soap and running water.
Ingestion:	Give water to drink. <i>After first aid, get appropriate in-plant paramedic or community medical support if serious sign and symptoms persist.</i>
Note to Physicians:	N/A
Special Precautions / procedures:	N/A

Section 5 FIRE FIGHTING MEASURES

Flash Point:	N/A
Flash Point Method:	N/A
Burning Rate:	N/A
Auto Ignition Temperature:	> 360 C
LEL:	N/A
UEL:	N/A
Flammability Classification:	1 Slight (HMIS, NFPA)
Extinguishing Media:	Water spray, foam, carbon dioxide.
Unusual Fire or explosion hazards:	May form flammable dust-air mixture.
Hazardous combustion products:	Carbon monoxide, carbon dioxide, nitrogen oxide and smoke. Under certain conditions some aliphatic aldehydes and carboxylic acids may form.
Fire- Fighting Instructions:	Do not release runoff from fire control methods to sewers or waterways.
Fire-Fighting Equipment:	Because fire may produce toxic thermal decomposition products, wear a self-contained breathing apparatus (SCBA) with full facepiece operated in pressure-demand or positive-pressure mode.

SECTION 6 ACCIDENTAL RELEASE MEASURES

Spill / Leak Procedures:	
Small Spills:	Scoop into container for disposal, suction up remaining material with high efficiency vacuum cleaner.
Large Spills:	Scoop into container for disposal, suction up remaining material with high efficiency vacuum cleaner.
Containment:	For large spills, avoid suspending particles, collect for later disposal. Do not release into sewers or waterways.
Cleanup:	No special requirements.
REGULATORY REQUIREMENT :	N/A

SECTION 7 HANDLING AND STORAGE

Handling Precautions:	Keep containers closed at all times. Avoid creating dust. Keep away from ignition sources.
Storage Requirements:	Store in a cool, dry location. (Below 40 C / 100 F)
Regulatory Requirements:	N/A

SECTION 8 EXPOSURE CONTROLS / PERSONAL PROTECTION

Engineering Controls:	
Ventilation:	Provide general or local exhaust ventilation systems to maintain airborne concentrations below OSHA PELs (sec.2). Local exhaust ventilation is preferred because it prevents contaminant dispersion into the work area by controlling it at its source.
Administrative Controls:	
Respiratory Protection:	Seek professional advise prior to respirator selection and use. Follow OSHA respirator regulations (29 CFR 1910.134) and, if necessary, wear a MSHA/NIOSH-approved respirator. select respirator based on its suitability to provide adequate worker protection for given working conditions, level of airborne contamination, and presence of sufficient oxygen. For emergency or nonroutine operation (cleaning spills, reactor vessels, or storage tanks), wear an SCBA. <i>Warning! Air-purified respirators do not protect workers in oxygen-deficient atmospheres.</i>
Protective Clothing/Equipment:	Wear chemically protective gloves, boots, aprons, and gauntlets to prevent prolonged or repeated skin contact. Wear protective eyeglasses or chemical safety goggles, per OSHA eye-and face-protection regulations (29CFR 1910.133). Contact lenses are not eye protective devices. appropriate protection must be worn instead of, or in conjunction with contact lenses.
Safety Stations:	Make emergency eyewash stations and washing facilities available in work area.
Contaminated Equipment:	Separate contaminated work clothing from street clothes. Launder before re-use. Remove this material from your shoes and clean personal protective equipment.
Comments:	Never eat, drink, or smoke in work areas. Practice good personal hygiene after using this material, especially before eating, drinking using the toilet, or applying cosmetics

SECTION 9 PHYSICAL AND CHEMICAL PROPERTIES

Physical State:		Water Solubility:	Insoluble
Appearance and Odor:	Black, free flowing powder, slight odor.	Other Solubilities:	N/A
Odor Threshold:	N/A	Boiling Point:	N/A
Vapor Pressure:	N/A	Freezing/Melting Point:	120 C (Melting Point)
Vapor Density(Air=1):	Heavier than air.	Viscosity:	N/A
Formula Weight:	N/A	Refractive Index:	N/A
Density:	N/A	Surface Tension:	N/A
Specific Gravity:	(H ₂ O=1, at 4 ^o C): 1.1	%Volatile:	N/A
pH:	N/A	Evaporation Rate:	N/A

SECTION 10 STABILITY AND REACTIVITY

STABILITY:	Stable product.
POLYMERIZATION:	N/A
CHEMICAL INCOMPATIBILITIES:	N/A
CONDITIONS TO AVOID:	N/A
HAZARDOUS DECOMPOSITION PRODUCTS:	May include nitrogen and carbon oxides.

SECTION 11 TOXICOLOGICAL INFORMATION

Eye Effects:	N/A	Toxicity Data: *	
Skin Effects:	N/A	Acute Inhalation Effects:	N/A
		Acute Oral Effects:	N/A
		Chronic Effects:	N/A
		Carcinogenicity:	N/A
		Mutagenicity:	Ames Test - Negative
		Teratogenicity:	N/A

*See NIOSH, RTECS for additional toxicity data.

SECTION 12 ECOLOGICAL INFORMATION

Ecotoxicity:	N/A
Environmental Fate:	N/A
Environmental Degradation:	N/A
Soil Absorption / Mobility:	N/A

SECTION 13 DISPOSAL CONSIDERATIONS

Disposal:	Waste material may be incinerated under conditions which meet all federal, state and local environmental regulations.
Disposal Regulatory Requirements:	N/A
Container Cleaning and Disposal:	N/A

SECTION 14 TRANSPORT INFORMATION

DOT Transportation Data (49 CFR 172.101):	Not specifically listed		
Shipping Name:	N/A	Packaging Authorizations	Quantity Limitations
Shipping Symbol:	N/A	a) Exceptions:	N/A
Hazard Class:	N/A	b) Non-bulk Packaging:	N/A
ID No.:	N/A	c) Bulk Packaging:	N/A
Packing Group:	N/A		Vessel Stowage Requirements
Label:	N/A		a) vessel stowage:
Special Provisions	N/A		b) Other:

SECTION 15 REGULATORY INFORMATION**EPA Regulations:**

RCRA Hazardous Waste Number: (40 CFR 261.33) Not Listed
RCRA Hazardous Waste Classification: (40 CFR 261): Not classified
CERCLA Hazardous Substance (40 CFR 302.4) listed/unlisted specific per RCRA, sec. 3001;
CWA sec.311 (b)(4);
CWA, Sec. 307(a),CAA,Sec.112
CERCLA Reportable Quantity(RQ): Not listed
SARA 311/312 Codes: N/A
SARA Toxic Chemical (40 CFR 372.65): Not listed
SARA EHS (Extremely Hazardous Substance) (40 CFR 355): Not listed, Threshold Planning Quantity (TPQ)

OSHA Regulations:

Air Contaminant (29 CFR 1910.1000< Table Z-1-A): Particulates not otherwise regulated.

State Regulations: Check your states regulations that may specifically list copy machine toner.

SECTION 16 OTHER INFORMATION

Prepared By: N/A
Revision Notes: N/A
Additional Hazard Rating System: N/A

THIS INFORMATION IN THIS MSDS WAS OBTAINED FROM SOURCES WHICH WE BELIEVE ARE RELIABLE. HOWEVER, THE INFORMATION IS PROVIDED WITHOUT ANY WARRANTY EXPRESS OR IMPLIED, REGARDING IT'S CORRECTNESS.
THE CONDITIONS OR METHODS OF HANDLING, STORAGE, USE AND DISPOSAL OF THE PRODUCT ARE BEYOND OUR CONTROL AND MAY BE BEYOND OUR KNOWLEDGE.
FOR THIS AND OTHER REASONS, WE DO NOT ASSUME RESPONSIBILITY AND EXPRESSLY DISCLAIM LIABILITY FOR LOSS, DAMAGE OR EXPENSE ARISING OUT OF OR IN ANY WAY CONNECTED WITH THE HANDLING, STORAGE, USE OR DISPOSAL OF THE PRODUCT.