



TEXACO  
MATERIAL SAFETY DATA SHEET

NOTE: Read and understand Material Safety Data Sheet before handling or disposing of product.

1. CHEMICAL PRODUCT AND COMPANY IDENTIFICATION

MATERIAL IDENTITY

Product Code and Name:

02319 MERO PA 68

Chemical Name and/or Family or Description:

Industrial Oils

Manufacturer's Name and Address:

TEXACO LUBRICANTS COMPANY

A DIVISION OF TEXACO REFINING AND MARKETING INC.

P.O. Box 4427

Houston, TX 77210-4427

Telephone Numbers:

Transportation Emergency-Company : (914) 831-3400

CHEMTREC : (800) 424-9300

Health Emergency -Company : (914) 831-3400

General MSDS Assistance : (914) 838-7204

Technical Information -Fuels : (914) 838-7336

-Chemical : (512) 459-6543

-Lubricant/: (800) 782-7852

Antifreezes

-Additives : (713) 235-6278

-Solvents : (800) 876-3738

2. COMPOSITION/INFORMATION ON INGREDIENTS

THE CRITERIA FOR LISTING COMPONENTS IN THE COMPOSITION SECTION IS AS FOLLOWS: CARCINOGENS ARE LISTED WHEN PRESENT AT 0.1 % OR GREATER; COMPONENTS WHICH ARE OTHERWISE HAZARDOUS ACCORDING TO OSHA ARE LISTED WHEN PRESENT AT 1.0 % OR GREATER; NON-HAZARDOUS COMPONENTS ARE LISTED AT 3.0 % OR GREATER. THIS IS NOT INTENDED TO BE A COMPLETE COMPOSITIONAL DISCLOSURE. REFER TO SECTION 14 FOR APPLICABLE STATES' RIGHT TO KNOW AND OTHER REGULATORY INFORMATION.

Product and/or Component(s) Carcinogenic According to:

OSHA IARC NTP OTHER NONE

- - - - X

Composition: (Sequence Number and Chemical Name)

Seq.	Chemical Name	CAS Number	Range in %
01	# Severely solvent refined, solvent-dewaxed heavy paraffinic petroleum distillates	64742-65-0	65.00-79.99
02	# Lubricating oils (petroleum), C > 25, hydro-treated bright stock-based	72623-83-7	20.00-34.99

PRODUCT IS NON-HAZARDOUS ACCORDING TO OSHA (1910.1200).

# COMPONENT, BY DEFINITION, IS CONSIDERED HAZARDOUS ACCORDING TO OSHA BECAUSE IT CARRIES THE PERMISSIBLE EXPOSURE LIMIT (PEL) FOR MINERAL OIL MIST.

Exposure Limits referenced by Sequence Number in the Composition Section

Seq.	Limit
01	5 mg/m3 TWA-OSHA (MINERAL OIL MIST)
01	5 mg/m3 TWA-ACGIH (MINERAL OIL MIST)
01	10 mg/m3 STEL ACGIH (MINERAL OIL MIST)
02	5.0 mg/m3 TWA-OSHA (MINERAL OIL MIST)
02	5.0 mg/m3 TWA-ACGIH (MINERAL OIL MIST)
02	10.0 mg/m3 STEL ACGIH (MINERAL OIL MIST)

3. HAZARD IDENTIFICATION

EMERGENCY OVERVIEW

Appearance:

Dark red liquid

Odor:

Not determined

PAGE: 1

N.D. - NOT DETERMINED  
< - LESS THAN

N.A. - NOT APPLICABLE  
> - GREATER THAN

N.T. - NOT TESTED

PRODUCT CODE: 00702  
NAME: REGAL R&D 68

Date Issued: 12-08-95  
Supersedes: 07-31-95



### 3. HAZARD IDENTIFICATION (CONT)

HMIS		NFPA	
Health: 0	Reactivity: 0	Health: 0	Reactivity: 0
Flammability: 1	Special: -	Flammability: 1	Special: -

#### POTENTIAL HEALTH EFFECTS

	EYE	SKIN	INHALATION	INGESTION
Primary Route of Exposure:	X	X	X	-

#### EFFECTS OF OVEREXPOSURE

##### Acute:

##### Eyes:

May cause minimal irritation, experienced as temporary discomfort.

##### Skin:

Brief contact is not irritating. Prolonged contact, as with clothing wetted with material, may cause defatting of skin or irritation, seen as local redness with possible mild discomfort.

Other than the potential skin irritation effects noted above, acute (short term) adverse effects are not expected from brief skin contact; see other effects, below, and Section 11 for information regarding potential long term effects.

##### Inhalation:

Vapors or mist, in excess of permissible concentrations, or in unusually high concentrations generated from spraying, heating the material or as from exposure in poorly ventilated areas or confined spaces, may cause irritation of the nose and throat, headache, nausea, and drowsiness.

##### Ingestion:

If more than several mouthfuls are swallowed, abdominal discomfort, nausea, and diarrhea may occur.

##### Sensitization Properties:

Unknown.

##### Chronic:

No adverse effects have been documented in humans as a result of chronic exposure. Section 11 may contain applicable animal data.

##### Medical Conditions Aggravated by Exposure:

Because of its defatting properties, prolonged and repeated skin contact may aggravate an existing dermatitis (skin condition).

##### Other Remarks:

Material from high pressure equipment, pinhole leaks, or high pressure line failure can penetrate the skin and, if not properly treated, can cause severe injury, including disfigurement, loss of function, or even require amputation of the affected area. To prevent such serious injury, immediate medical attention should be sought even if the injection injury appears to be minor.

### 4. FIRST AID MEASURES

##### Eyes:

Flush eyes with plenty of water for several minutes. Get medical attention if eye irritation persists.

##### Skin:

Wash skin with plenty of soap and water for several minutes. Get medical attention if skin irritation develops or persists.

##### Ingestion:

If more than several mouthfuls of this material are swallowed, give two glasses of water (16 oz.). Get medical attention.

##### Inhalation:

If irritation, headache, nausea, or drowsiness occurs, remove to fresh air. Get medical attention if breathing becomes difficult or respiratory irritation persists.

PAGE: 2

N.D. - NOT DETERMINED  
< - LESS THAN

N.A. - NOT APPLICABLE  
> - GREATER THAN

N.T. - NOT TESTED

#### 4. FIRST AID MEASURES (CONT)

**Other Instructions:**

Remove and dry-clean or launder clothing soaked or soiled with this material before reuse. Dry cleaning of contaminated clothing may be more effective than normal laundering. Inform individuals responsible for cleaning of potential hazards associated with handling contaminated clothing.

#### 5. FIRE-FIGHTING MEASURES

**Ignition Temperature - AIT (degrees F):**

Not determined.

**Flash Point (degrees F):**

400 (COC)

**Flammable Limits (%):**

Lower: Not determined.

Upper: Not determined.

**Recommended Fire Extinguishing Agents And Special Procedures:**

Use water spray, dry chemical, foam, or carbon dioxide to extinguish flames. Use water spray to cool fire-exposed containers. Water or foam may cause frothing.

**Unusual or Explosive Hazards:**

None

**Special Protective Equipment for Firefighters:**

No special equipment or procedures required.

#### 6. ACCIDENTAL RELEASE MEASURES (Transportation Spills: CHEMTREC (800)424-9300)

**Procedures in Case of Accidental Release, Breakage or Leakage:**

Ventilate area. Avoid breathing vapor. Wear appropriate personal protective equipment, including appropriate respiratory protection. Contain spill if possible. Wipe up or absorb on suitable material and shovel up. Prevent entry into sewers and waterways. Avoid contact with skin, eyes or clothing.

If more than 5,208,333 pounds of product is spilled, then report spill according to SARA 304 and/or CERCLA 102(a) requirements, unless product qualifies for the petroleum exemption (CERCLA Section 101(14)).

#### 7. HANDLING AND STORAGE

**Precautions to be Taken in****Handling:**

Minimum feasible handling temperatures should be maintained.

**Storage:**

Periods of exposure to high temperatures should be minimized. Water contamination should be avoided.

#### 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

**Protective Equipment (Type)****Eye/Face Protection:**

Safety glasses, chemical type goggles, or face shield recommended to prevent eye contact.

**Skin Protection:**

Workers should wash exposed skin several times daily with soap and water. Soiled work clothing should be laundered or dry-cleaned.

**Respiratory Protection:**

Airborne concentrations should be kept to lowest levels possible. If vapor, mist or dust is generated and the occupational exposure limit of the product, or any component of the product, is exceeded, use appropriate NIOSH or MSHA approved air purifying or air supplied respirator after determining the airborne concentration of the contaminant. Air supplied respirators should always be worn when airborne concentration of the contaminant or oxygen content is unknown.

PAGE: 3

N.D. - NOT DETERMINED  
< - LESS THAN

N.A. - NOT APPLICABLE  
> - GREATER THAN

N.T. - NOT TESTED

PRODUCT CODE: 00702  
NAME: REGAL R&O 68

Date Issued: 12-08-95  
Supersedes: 07-31-95



## 8. EXPOSURE CONTROLS/PERSONAL PROTECTION (CONT)

### Respiratory Protection:

Airborne concentrations should be kept to lowest levels possible. If vapor, mist or dust is generated and the occupational exposure limit of the product, or any component of the product, is exceeded, use appropriate NIOSH or MSHA approved air purifying or air supplied respirator after determining the airborne concentration of the contaminant. Air supplied respirators should always be worn when airborne concentration of the contaminant or oxygen content is unknown.

### Ventilation:

Adequate to meet component occupational exposure limits (see Section 2).

### Exposure Limit for Total Product:

None established for product; refer to Section 2 for component exposure limits.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

### Appearance:

Light pale liquid

### Odor:

Mild odor

### Boiling Point (degrees F):

Not determined.

### Melting/Freezing point (degrees F):

Not applicable.

### Specific Gravity (water=1):

.8805

### pH of undiluted product:

Not applicable.

### Vapor Pressure:

Not determined.

### Viscosity:

67 cSt at 40.0 C

### VOC Content:

7 g/L

### Vapor Density (air=1):

Not determined.

### Solubility in Water (%):

Not determined.

Other: None

## 10. STABILITY AND REACTIVITY

### This Material Reacts Violently With:

(If Others is checked below, see comments for details)

Air	Water	Heat	Strong Oxidizers	Others	None of These
			X		

### Comments:

None

### Products Evolved When Subjected to Heat or Combustion:

Toxic levels of carbon monoxide, carbon dioxide, irritating aldehydes and ketones.

Hazardous Polymerizations: DO NOT OCCUR

PAGE: 4

N.D. - NOT DETERMINED  
< - LESS THAN

N.A. - NOT APPLICABLE  
> - GREATER THAN

N.T. - NOT TESTED

PRODUCT CODE: 02319  
NAME: MEROPA 68

Date Issued: 12-08-95  
Supersedes: 09-15-95



#### 11. TOXICOLOGICAL INFORMATION (CONT)

**Eyes:**

(Draize) Believed to be < 15.00 /110 (rabbit) no appreciable effect

**Sensitization:**

Not determined.

**Other:**

None

#### 12. DISPOSAL CONSIDERATIONS

**Waste Disposal Methods**

This product has been evaluated for RCRA characteristics and does not meet the criteria of a hazardous waste if discarded in its purchased form. Under RCRA, it is the responsibility of the user of the product to determine at the time of disposal, whether the product meets RCRA criteria for hazardous waste. This is because product uses, transformations, mixtures, processes, etc. may render the resulting materials hazardous.

**Remarks**

None

#### 13. TRANSPORT INFORMATION

**Transportation**

**DOT:**

Proper Shipping Name:

Not regulated

**IMDG:**

Proper Shipping Name:

Not evaluated

**ICAO:**

Proper Shipping Name:

Not evaluated

**TDG:**

Proper Shipping Name:

Not evaluated

#### 14. REGULATORY INFORMATION

**Federal Regulations:**

**SARA Title III:**

**Section 302/304 Extremely Hazardous Substances**

Seq. Chemical Name CAS Number Range in %

None

**Section 302/304 Extremely Hazardous Substances (CONT)**

Seq. TPQ RQ

None

**Section 311 Hazardous Categorization:**

Acute Chronic Fire Pressure Reactive N/A

- - - - - X

**Section 313 Toxic Chemical**

Chemical Name CAS Number Concentration

None

**CERCLA 102(a)/DOT Hazardous Substances: (+ indicates DOT Hazardous Substance)**

Seq. Chemical Name CAS Number Range in %

O1+ Toluene 108-88-3 0.01-0.09

**CERCLA/DOT Hazardous Substances (Sequence Numbers and RQ's):**

Seq. RQ

O1+ 1000

**TSCA Inventory Status:**

This product, or its components, are listed on or are exempt from the Toxic Substance Control Act (TSCA) Chemical Substance Inventory.

PAGE: 5

N.D. - NOT DETERMINED  
< - LESS THAN

N.A. - NOT APPLICABLE  
> - GREATER THAN

N.T. - NOT TESTED

PRODUCT CODE: 00702  
NAME: REGAL R&D 68

Date Issued: 12-08-95  
Supersedes: 07-31-95



#### 14. REGULATORY INFORMATION (CONT)

CERCLA 102(a)/DOT Hazardous Substances: (+ indicates DOT Hazardous Substance)

Seq. Chemical Name CAS Number Range in %  
None

CERCLA/DOT Hazardous Substances (Sequence Numbers and RQ's):

Seq. RQ  
None

##### TSCA Inventory Status:

This product, or its components, are listed on or are exempt from the Toxic Substance Control Act (TSCA) Chemical Substance Inventory.

Other:  
None.

##### State Regulations:

###### California Proposition 65:

The following detectable components of this product are substances, or belong to classes of substances, known to the State of California to cause cancer and/or reproductive toxicity.

Chemical Name CAS Number  
None

##### States Right-to-know Regulations:

Chemical Name State Right-to-know  
None

State list: CT (Connecticut), FL (Florida), IL (Illinois), MI (Michigan),  
LA (Louisiana), MA (Massachusetts), NJ (New Jersey),  
PA (Pennsylvania), RI (Rhode Island)

##### International Regulations:

WHMIS Classification:  
Not regulated

Canada Inventory Status:  
Not determined.

EINECS Inventory Status:  
Not determined.

Australia Inventory Status:  
Not determined.

Japan Inventory Status:  
Not determined.

#### 15. ENVIRONMENTAL INFORMATION

Aquatic Toxicity:  
Not determined.

Mobility:  
Not determined.

Persistence and Biodegradability:  
Not determined.

Potential to Bioaccumulate:  
Not evaluated.

Remarks:  
Not evaluated.

#### 16. OTHER INFORMATION

None

THE INFORMATION CONTAINED HEREIN IS BELIEVED TO BE ACCURATE. IT IS PROVIDED

PAGE: 6

N.D. - NOT DETERMINED  
< - LESS THAN

N.A. - NOT APPLICABLE  
> - GREATER THAN

N.T. - NOT TESTED



PRODUCT CODE: 02319  
NAME: MEROPA 68

Date Issued: 12-08-95  
Supersedes: 09-15-95

16. OTHER INFORMATION (CONT)

ARE ENCOURAGED AND REQUESTED TO ADVISE THOSE WHO MAY COME IN CONTACT WITH SUCH PRODUCTS OF THE INFORMATION CONTAINED HEREIN.

TO DETERMINE APPLICABILITY OR EFFECT OF ANY LAW OR REGULATION WITH RESPECT TO THE PRODUCT, USER SHOULD CONSULT HIS LEGAL ADVISOR OR THE APPROPRIATE GOVERNMENT AGENCY. TEXACO DOES NOT UNDERTAKE TO FURNISH ADVICE ON SUCH MATTERS.

Since the last mailing for this customer code, the following sections have been revised:  
11, 13, 14, 16, 17.

Date: 12-08-95      New    ☒    Revised, Supersedes: 09-15-95  
Date printed: 02-07-96

Inquiries regarding MSDS should be directed to:  
Texaco Inc.  
Manager, Product Safety  
P.O. Box 509  
Beacon, N.Y. 12508

PLEASE SEE NEXT PAGE FOR PRODUCT LABEL

PAGE: 7

N.D. - NOT DETERMINED  
< - LESS THAN

N.A. - NOT APPLICABLE  
> - GREATER THAN

N.T. - NOT TESTED



PRODUCT CODE: 00702  
NAME: REGAL R&O 68

Date Issued: 12-08-95  
Supersedes: 07-31-95



17. PRODUCT LABEL

Label Date: 12-08-95

READ AND UNDERSTAND MATERIAL SAFETY DATA SHEET BEFORE HANDLING OR DISPOSING OF PRODUCT. THIS LABEL COMPLIES WITH THE REQUIREMENTS OF THE OSHA HAZARD COMMUNICATION STANDARD (29 CFR 1910.1200) FOR USE IN THE WORKPLACE. THIS LABEL IS NOT INTENDED TO BE USED WITH PACKAGING INTENDED FOR SALE TO CONSUMERS AND MAY NOT CONFORM WITH THE REQUIREMENTS OF THE CONSUMER PRODUCT SAFETY ACT OR OTHER RELATED REGULATORY REQUIREMENTS.

00702 REGAL R&O 68

**WARNING STATEMENT**  
NONE CONSIDERED NECESSARY

**PRECAUTIONARY MEASURES**

- Avoid prolonged breathing of vapor, mist, or gas.
- Workers should wash exposed skin several times daily with soap and water.

**FIRST AID**

**Eye Contact:**

Flush eyes with plenty of water for several minutes. Get medical attention if eye irritation persists.

**Skin Contact:**

Wash skin with plenty of soap and water for several minutes. Get medical attention if skin irritation develops or persists.

**Ingestion:**

If more than several mouthfuls of this material are swallowed, give two glasses of water (16 oz.). Get medical attention.

**Inhalation:**

If irritation, headache, nausea, or drowsiness occurs, remove to fresh air. Get medical attention if breathing becomes difficult or respiratory irritation persists.

**Note to Physician:**

High pressure injection of material can cause severe injury. Failure to debride the wound of all residual material can result in disfigurement, loss of function, or may require amputation of the affected area.

**FIRE**

In case of fire, use water spray, dry chemical, foam or carbon dioxide. Water may cause frothing. Use water spray to cool fire-exposed containers.

**Chemical Name**

**CAS Number**

**Range in %**

# Severely solvent refined, solvent-dewaxed heavy paraffinic petroleum distillates

64742-65-0 95.00-99.99

PRODUCT IS NON-HAZARDOUS ACCORDING TO OSHA (1910.1200).

# COMPONENT, BY DEFINITION, IS CONSIDERED HAZARDOUS ACCORDING TO OSHA BECAUSE IT CARRIES THE PERMISSIBLE EXPOSURE LIMIT (PEL) FOR MINERAL OIL MIST.

**Pennsylvania Special Hazardous Substance(s)**  
None

**CAS Number**

**Range in %**

**HMIS**

Health: 0 Reactivity: 0  
Flammability: 1 Special : -

**NFPA**

Health: 0 Reactivity: 0  
Flammability: 1 Special : -

**Transportation**

**DOT:**

**Proper Shipping Name:**  
Not regulated

**CAUTION:** Misuse of empty containers can be hazardous. Empty containers can be hazardous if used to store toxic, flammable, or reactive materials. Cutting or welding of empty containers might cause fire, explosion or toxic fumes from residues. Do not pressurize or expose to open flame or heat. Keep container closed and drum bungs in place.

PAGE: 8

N.D. - NOT DETERMINED  
< - LESS THAN

N.A. - NOT APPLICABLE  
> - GREATER THAN

N.T. - NOT TESTED



PRODUCT CODE: 02319  
NAME: MEROPA 68

Date Issued: 12-08-95  
Supersedes: 09-15-95



17. PRODUCT LABEL (CONT)

Label Date: 12-08-95

Manufacturer's Name and Address:

TEXACO LUBRICANTS COMPANY  
A DIVISION OF TEXACO REFINING AND MARKETING INC.  
P.O. Box 4427  
Houston, TX 77210-4427

TRANSPORTATION EMERGENCY      Company:      (914) 831-3400  
CHEMTREC:      (800) 424-9300

HEALTH EMERGENCY                      Company:      (914) 831-3400