

# Vyna-Plush



- Economical yet effective scraper doormat
- Slip and stain resistant PVC backing
- Available in 4 attractive colours

#### Technical Specifications:

- Pile height: 4mm
- Total weight: 2.6 kg/m<sup>2</sup>
- Pile material is 100% polypropylene
- Product height: 7mm

Dimensions (m.)	Weight Kg	Packaging Dimensions (cm.)	Packaging Type	Packaging Volume (m.)	Packaging Quantity	Colour	Part Code
0.6 x 0.9	2	17.5 x 17.5 x 75	Box	0.02	1	Black/Steel	VP010601
						Black/Red	VP010301
						Black/Blue	VP010201
						Black/Brown	VP010501
0.9 x 1.2	2	17.5 x 17.5 x 105	Box	0.02	1	Black/Steel	VP010602
						Black/Red	VP010302
						Black/Blue	VP010202
						Black/Brown	VP010502
0.9 x 1.5	2	17.5 x 17.5 x 105	Box	0.02	1	Black/Steel	VP010603
						Black/Red	VP010303
						Black/Blue	VP010203
						Black/Brown	VP010503
1.2 x 1.8	2	23 x 23 x 124	Box	0.02	1	Black/Steel	VP010604
						Black/Red	VP010304
						Black/Blue	VP010204
						Black/Brown	VP010504

#### Technical Features:

Manufacturing Process  
Surface Aspect  
Pile material  
Primary Backing  
Machine gauge  
Backing  
Pile Height  
Total Height

#### According to:

ISO 2424 / BS 5557

ISO 2424 / BS 5557

DIN 61151 / BS 5557

ISO 2424

ISO 1766 / BS 4223 Clause 10

ISO 1765 / BS 4051

Vuilvang

Cutpile

100% PA

Collback TM80

5/32" COC

PVC US

4.0 mm

.16 in

7.0 mm

.28 in

Continued on next page

Pile Weight	400 g/m2	11.8 oz/yd2 (+/-7,5%)
Total Weight	ISO 8543 / BS 4223 Clause 7	2660 g/m2 78.4 oz/yd2 (+/-7,5%)
Number of tufts	ISO 1763 / BS 4223 Clause 6	65500 1/m2 55000 1/yd2

Performances:

Walking test	EN 1815 / ISO TR 6356 / DD68	< 2 KV
Dimensional Stability	EN 986 / ISO 2551 / DIN 54318	Voldoet aan de norm(pass)
Electrical resistivity	IBM/ ICL	-
Electrical resistivity vertical	DIN 54345	-
Electrical resistivity horizontal	DIN 54345	-
Sound Insulation	ISO 140-8 / BS 3638	>= 19dB
Thermal retention	ISO 8302 / DIN 52612	-
Soiling (dry / wet)	EN 1289	4.5

Colour fastness:

To light	ISO 105 B02 / DIN 54004/ BS 1006 5
To water	ISO 105 E01 / DIN 54006/ BS 1006 5
To seawater	ISO 105 E02 / DIN 54007/ BS1006 -
To shampoo	BS 1006 5
To rubbing dry	ISO 105 X12/ DIN 54021/BS1006 4
Wet	4

Flammability rating:

NBS Flooring Radiant	ASTM E648/DIN 4102/NEN 1775	-
Pill (Tablet) test	ISO 6925 = ASTM D2829/ BS 6307	-
Hot Metal Nut	BS 4790/BS 5287	Low radius
UK Radiant panel test	BS 476 (7)	-
Austrian radiant panel test Oenorm	3810 / Oenorm 3800 (1)	-
Kleinbrenner	DIN 54332 / NEN 1775 (1)	Ta (B2)/T3
Panneau radiant	NF P-92-506	-

Gut certificate no. 20249

European Overall Classification EN 1307 2LC1

Strapazierwert DIN 66095 (2)  Gering  Normal  Stark  Extrem

Komfortwert DIN 66095 (2)  Einfach  Gut  Hoch  Luxurious

End of document