


LENGTH CODE CHART		
CABLE# & LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED
CA-RSPNMAXXX	WHERE XXX = LENGTH IN FEET	CA-RSPNMA010 (10 FEET)
CA-RSPNMANXX	WHERE NXX = LENGTH IN INCHES	CA-RSPNMAN16 (16 INCHES)
CA-RSPNMAXXX	WHERE MXX = LENGTH IN METERS	CA-RSPNMA07 (7 METERS)
CA-RSPNMAXMX	WHERE XMX = LENGTH IN DECIMEL METERS	CA-RSPNMA3M5 (3.5 METERS)

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY
2. CABLE ASSEMBLY SHALL RECIEVE INSERTION LOSS TEST#TP-0027
3. CABLE ASSEMBLY SHALL WITHSTAND PULL TEST OF 40lbs WITHOUT ANY SEPERATION OR ELECTRICAL FAILURE
4. CABLE SHALL BE RoHS COMPLIANT
5. CABLE SHALL BE INDIVIDUALLY PACKAGED IN HEAT SEALED POLY BAG WITH APPROP. LABEL (REF. DRAWING #F950)
6. CENTER PIN OF CONNECTORS TO BE CRIMPED ONTO CABLE INNER CONDUCTOR

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES <u>OVERALL CABLE LENGTH TOLERANCE</u> ≤ 12 [305] = +1 [25]/-0 >12 [305] ≤ 60 [1524] = +2 [51] /-0 >60 [1524] ≤ 120 [3048] = +4/-0 >120 [3048] U+2264300 [7620] = +6/-0 >300 [76290] = +5%/-0					SIZE A	TITLE: FABRICATION: CA-195R SERIES RP-SMA PLUG TO N-MALE ASSEMBLY with HEATSHRINK				
	B	HL-ECN-0037	05/11/09	Change Tol. for Heatshrink from ±.06" & ±.15mm						
	REV	ECN No.	DATE	DESCRIPTION		DRAWN BY	A. Vajanyi	08/19/08	DRAWING No.	REV
						ORIGINATOR	P. Pesa	08/07/08	F958	B
 Website: www.L-com.com Tel: 1-800-343-1455 Copyright © 2009 L-com, Inc. All rights reserved.				APPROVAL	M. Audus	08/27/08	PART No.	CA-RSPNMA	VAR.	
				SCALE 1:1	SHEET 1/1	MATERIAL Noted	FILE No.	F958-01		