

Ratchet Ring Spanners

BRITool



Ratcheting ring spanners are designed for use in areas where access is restricted. The ratchet is reversed simply by turning the wrench over. The bi-hexagon ring form is broached for accuracy to ensure a perfect non slip fit. The wrench body is nickel and chrome plated to prevent corrosion and extend tool life.

Metric

Size (mm)	Number	Order Code	Price Each
7 x 8	RBB78	137-7963	
9 x 10	RBB910	137-7964	
11 x 12	RBB1112	141-7905	
13 x 14	RBB1314	137-7965	
15 x 17	RBB1517	141-7906	
16 x 18	RBB1618	141-7907	
19 x 21	RBB1921	137-7967	

AF

495311

AF (in)	Number	Order Code	Price Each
1/4 x 5/16	RBB2531	141-7908	
3/8 x 7/16	RBB3743	141-7909	
7/16 x 1/2	RBB4350	141-7910	
1/2 x 9/16	RBB5056	141-7911	
9/16 x 5/8	RBB5662	137-7968	
5/8 x 11/16	RBB6268	141-7912	
3/4 x 7/8	RBB7587	141-7913	