


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS		DOC. NO.	SPC-F005	*	Effective:	12/21/98	*	DCP No:	680
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE	
904	A	RELEASED	JMM	3/19/01	JC	5/7/01	DJC	5/11/01	



**Specifications**

- Display: 18mm (0.7") LCD, 5 digits w/annunciator
- Measuring Capacity: 11.022 lb.
- Resolution: 0.002 lb.
- Min. Display Weight: 0.006 lb.
- Accuracy (23°C ±5°C): ±(3% + 1 digit)
- After internal calibration is completed*
- Spec. tested environment: RF Field Strength less than 3 V/M and frequency less than 30MHz*
- Sampling Time: Approx. 0.8 Second
- Tare Control: Full Capacity
- Transducer: Load Cell
- Cabinet Size: 240mm x 185mm x 50MM
- Platform Size: 185mm x 185mm
- Power Supply: Six 1.5VAA (UM-3) batteries or or 9V DC adapter. (Not included)
- Power Consumption: Approx. DC 27mA.
- Includes operating manual

DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL. THE USER ASSUMES ALL LIABILITY WHATSOEVER IN CONNECTION THEREWITH. INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	Jeff McVicker	DATE:	3/19/01
CHECKED BY:	JOHN COLE	DATE:	5/7/01
APPROVED BY:	Daniel Carey	DATE:	5/11/01



DRAWING TITLE: Digital Scale

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	72-6787	17C6514.dwg	A
SCALE:	NTS	U.O.M.: Millimeters	SHEET: 1 OF 1