

Bench Drilling Machine



CDP151B



Bench drilling machine. Features front mounted no volt release safety switch, emergency stop switch, safety cut on belt guard depth gauge, chuck and guard. 230V.

Model	CDP151B
Drilling Capacity	13 mm
Spindle Taper	33JT
No. of Speeds	5
Spindle Speed	460 - 2480 rpm
Table Size (W x D)	198 x 193 mm
Table Tilt	90°
Motor	0.30 kW

494101

Description	Order Code	Price Each
CDP151B bench drill 230V	145-5476 ●	