

Main

Product or component type	Communication card
Range compatibility	Altivar 312
Communication port protocol	DeviceNet
Electrical connection	1 connector RJ45, Modbus 1 removable screw terminal block for inputs/outputs 5-way screw connector, DeviceNet
Transmission rate	125 kbps, 250 kbps or 500 kbps
Number of addresses	1...63

Complementary

Input/Output number	AI2 and AI3: 2 analog input LI1...LI3: 3 logic input R2: 1 relay output
Communication service	Periodic variables ATV 312 native profile (CiA 402) 100 and 101 Communication monitoring can be inhibited No auto device replacement Periodic variables ODVA AC drive type profile 20, 21, 70 and 71 Periodic exchange mode on inputs : polled, change of state, cyclic Periodic exchange mode on outputs : polled
Display type	1 dual colour LED for MNS (status)
Product weight	0.2 kg

Environment

RoHS EUR status	Compliant
RoHS EUR conformity date	0939

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.