



Features:


- Protects electronics from moisture and static damage
- Opaque and light tight ensuring the inside item can not be seen from outside
- Firm lamination and hot sealing offers superior resistance of vapour and oxygen
- Surface resistance of 10^8 - $10^{11}\Omega$
- Applicable to pack electronic products which are sensitive to moisture and static, such as PC board, IC integrated circuit, CD drivers, HD etc.
- Flexible structure & easy to vacuum seal

Additional Notes:

We recommend that all of our moisture barrier bags be used within 2 years from the date of manufacture. Store this product in its original packaging in a climate-controlled environment where temperature ranges from 21°C -23°C and relative humidity is 45 - 50%.



Aluminized Polyester
Dissipative Nylon
Cast Polyethylene



Standard Construction:

Our moisture barrier bags are constructed in 3 layers. The bag features an anti static metallized polyester outer layer and an anti static inner layer. In between are layers of polyethylene, nylon and an aluminium foil shield.

Configuration(s):

Bags are offered in a 3-seal configuration, with our standard flexographically printed artwork.



Standard Bag Artwork:

Our moisture barrier bags are produced with the following sample artwork as standard. For further information on bespoke/printed orders, please contact one of our sales team. Please note there is a MOQ of 20,000 bags on all printed bags. Note: All of our moisture barrier bags are batch coded for QC traceability.

Important Notice: This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2011.

Moisture Barrier Bag_ANT018MBB



Test Conditions:

The following results were taken under the following environmental test conditions:

Temperature: 21.3°C / Humidity: 45.1%

Technical Parameters:

Item:	Test Standard:	Result:
Film Composition	N/A	PET-AL/NY/CPE
Metal Layer Resistance	ASTMD-257	<0.1 Ω
Inner and Outer Resistance	ASTMD-257	$10^8 - 10^{11} \Omega$
EMI Shielding	MIL-B-81705-C	>60db
Static Shielding - Capacitance Probe	EIA541 (Voltage Difference)	<10V
Moisture Vapour Transmission (at 90%RH, 23°C)	ASTMF1249-2005	0.0006 gm/100sq.in/24hrs
Tensile Strength	ASTM D882	MD/TD >24lbs/in
Puncture Resistance	ASTM F1306-90(2002)	Inner to Outer: 54.7N Outer to Inner: 51.3N
Tear Strength	ASTM D1004	MD >3lbs/in TD >3.8lbs/in
Heat Seal Temperature	-	250-375 F
Heat Seal Time	-	0.5-3.5 sec
Heat Seal Pressure	-	30-70 PSI
Seal Strength	GB/96-04-10	>3kg/cm
Contact Corrosivity	FTMS 101C Method 3005	No visible spots detected

Test Conclusion: (Date of Issue: 2009-08-16)

The anti-static moisture barrier bag is tested accordant with the relevant test standard and requirements.

Test Item:	Test Method:	Measured Equipment(s):	MDL:
Lead (Pb)	IEC 62321:2008 Ed.1 Sec.8	ICP-OES	2mg/kg
Cadmium (Cd)	IEC 62321:2008 Ed.1 Sec.8	ICP-OES	2mg/kg
Mercury (Hg)	IEC 62321:2008 Ed.1 Sec.7	ICP-OES	2mg/kg
Hexavalent Chromium (Cr(VI))	IEC 62321:2008 Ed.1 Annex C	UV-Vis	2mg/kg
Polybrominated Biphenyls (PBBs)	IEC 62321:2008 Ed.1 Annex A	GC-MS	5mg/kg
Polybrominated Diphenyl Ethers (PBDEs)	IEC 62321:2008 Ed.1 Annex A	GC-MS	5mg/kg

Product Code:	Description:	Size (inches):	Size (mm):	Additional Notes:
1503138	Moisture Barrier Bag 3.6Mil	10 x 24	254 x 610	Pack of 100 (Ref:018-0401)

Important Notice: This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2011.

www.element14.com

www.farnell.com

www.newark.com

