


11

OKW
GEHÄUSE
SYSTEME

www.okw.com



NEW PRODUCTS



PROGRAMME

Enclosures & Accessories

Supplement 2011





FORWARD-LOOKING

SYSTEM VARIETY

This range has been continuously extended over the years: for us, innovation is our passion.

If you also want to go with the times, or even better, if you want to be one step ahead, then OKW is just right for you.

In the following we should like to present our product enhancements and innovations, and make suggestions concerning our current services as well as new materials, e.g. BIO plastic.

Highlights

- INTERFACE-TERMINAL (4-7)
- DIATEC (8-9)
- MINITEC DROP/EDGE (10-11)
- WALLTEC (12)
- SMART-CASE (13)
- ART-CASE (13)



INDIVIDUAL

TO MEET YOUR NEEDS

Contribute your own wishes and suggestions and thus create individuality and a personal touch!

Through attractive services tailored to your needs, OKW Gehäusesysteme offers you the means to make your product something special.

Put our flexibility to the test!

Service

- individual printing
- special surfaces
- company colour
- graphic overlay
- membrane keyboard
- interfaces
- EMC protected
- spec. material properties
- fully assembled
- corporate design
- sales wrapping



ENVIRONMENT-FRIENDLY



BIO-PLASTIC

Show that you are responsible and environmentally aware with an enclosure made of BIOGRADE® C 7500.

In many applications BIOGRADE® C 7500 can replace the fossil plastics used up to now. For this reason, OKW Gehäusesysteme also offers numerous standard cases made of this material.

In this way you can help to save fossil raw materials and reduce dependence on petroleum.

BIOGRADE®

- CO₂-neutral
- made from renewable raw materials (cotton, wood)
- technically compostable and biologically degradable
- similar properties to ABS
- individual colouring



STERILE

ROWACARE

- permanent protection against bacteria, viruses and fungi
- natural prophylaxis
- complies with JIS Z 2801
- with an admixture of only 2 %, a > 99.9 % reduction in germs can be achieved after 5-6 hours
- material properties remain practically unchanged

ANTIMICROBIAL

Besides use in the medical sector, the antimicrobial materials and products are also ideal for equipment and cases that are used by different persons or are even held in the hand.

The compound used on request by OKW Gehäusesysteme consists of a ASA material in off-white.



INTERFACE-TERMINAL MOBILE

Order data on pages 14-15



EXCITING AND VERSATILE



THE PRODUCT

The growing demand in the field of data visualisation calls for innovative products tailor-made to meet the requirements of today's users.

The new INTERFACE-TERMINAL meets all of the requirements of a modern man-machine interface. Here the user himself decides whether he would like to use the device as a mobile or as a stationary unit.

APPLICATIONS

Unique variety of applications:
Mobile – desk-top – wall mounted

Peripheral and interface equipment.
Office applications. Communications technology.

Safety engineering. Biometrics.

Medical and laboratory technology.
Health sector.

Automation. Measuring/regulating/
controlling.


Protection class IP 54

With sealings (accessories).

Max. size of PCB (L x W in mm)

	bottom	cover	station
S	124 x 162	120 x 176	84 x 95
M	154 x 196	150 x 210	112 x 126
L	180 x 257	180 x 256	143 x 155

(cutouts of pillars not taken into consideration)



detailed drawings see our website
www.okw.com



CONTACT-FRIENDLY

Max. display sizes

- S 6.4" / 16 cm
- M 8.4" / 21 cm
- L 10.4" / 26 cm

The INTERFACE TERMINAL offers sufficient space for large-area touch screen displays. It is thus ideal for making operation as pleasant as possible for the user, for the processes can be displayed interactively on a touch screen display. The great advantage is its simple intuitive operation and a perfect navigation experience.

MOBILE

Maximum mobility and independence.

With/without battery compartment (5 x AA), accessible from the outside, incl. protection against incorrect polarity as well as anti-rotation device.

User-friendly design with attractive flat styling in the handle area. Finger recesses on the underside ensure a secure grip.

Available with either flat or high bottom part for individual installation configuration, interfaces, cable inputs and outputs etc.

CHARGING / TRANSMITTING

Easy transmission of data and charging current. Contacts as accessories.

Case available either to hang in position (desktop application) or NEW: base with snap-in mechanism for secure desktop and wall mounted applications. A flat wall suspension element as a base or for contacts is now also available.

Operating panel can be mounted either vertically or horizontally.

The base offers adequate space for the electronics.



INTERFACE-TERMINAL DESK-TOP

Order data on pages 14-15



EASY TO OPERATE



ERGONOMIC

Operating panel inclined by 20°. Ergonomically ideal for operating and reading – whether vertically or horizontally mounted.



The rubber feet included in the scope of delivery give the desktop units stability.

BASE-MOUNTED VARIANTS

Individual desktop cases can be assembled from different components to match the component configuration.

Case also available screwed to the base (desk). Assembly screws hidden on the underside.

Alternatively, the case snaps into base (desk/wall). If required, unit can be secured by latch lock.


Protection class IP 54

With sealings (accessories).


Max. size of PCB (L x W in mm)

	bottom	cover	station
S	124 x 162	120 x 176	84 x 95
M	154 x 196	150 x 210	112 x 126
L	180 x 257	180 x 256	143 x 155

(cutouts of pillars not taken into consideration)




detailed drawings see our website
www.okw.com



INTERFACE PROFESSIONAL

Rational wall mounting

The case can be mounted on the wall as a closed unit.



EFFICIENT

Unique "interface" between a stationary and a mobile component.

Assembly can be significantly simplified by predefined, snap-in interfaces.

You can also benefit from the ease of assembly when equipping and connecting up the interfaces; plug-in connectors also prevent wiring errors whenever servicing is required.

WALL MOUNTING

Direct wall mounting. The ergonomically inclined base offers plenty of space for connectors, electronics as well as wiring.

Separate wall suspension element for low-profile wall mounting, suitable for cases without base. The wall suspension element is prepared for contacts (accessories) for transmitting data and current.





PERFECT DIALOGUE



THE PRODUCT

You can hardly present your communication or network systems in a more attractive way.

The DIATEC is an attractive eye-catcher in your direct living and working environment. But this innovative range of cases also offers many functional benefits.

All details are designed to match each other perfectly. Depending on requirements, different equipment options and connections are possible.

YOUR ADVANTAGE

Modern, flat enclosure design, ideal for table top and wall mounting applications.

Plain, recessed area on the bottom part for installation and protection of interfaces, screwed cable glands, plug-in connections etc.


Easy, flush wall mounting.

Recessed operating area for the protection of the membrane keyboards and operating elements.

Protection class IP 40

Max. size of PCB (L x W in mm)

	bottom part	top part
XS	120 x 115	127 x 115
S	120 x 180	120 x 180
M	180 x 180	180 x 180
L	240 x 180	240 x 180






S/M/L

NEW
XS



S/M/L



S/M/L



PRESTIGIOUS

Design DIATEC XS

Two-piece case, consisting of top and bottom part, screwed together. Integrated battery holder for 2 x 1.5 V AA batteries. Pre-shaped flush-mounting box contoured in the bottom part.

DIATEC S, M, L

Four-piece case, consisting of top and bottom part as well as two covers for concealing the assembly screws. If required, the snap-on covers can be locked to prevent unauthorised access. Integrated battery compartment for 2 x 1.5 V AA batteries or 1 x 9 V flat battery.

SPEZIAL FOR S/M/L

Separate slot-in panels can be used as interior partitions, for example to guard the electronics when changing batteries. This allows the complete pre-assembly of the electronics unit. The technician on site only has to mount the unit on the wall and connect up the relevant leads. Connection can be effected from the left and/or from the right-hand side. The actual case does not have to be opened to do this, only the snap-on side trims.

Hinged lid in case colour or transparent for covering the dialogue zone as accessory.

APPLICATIONS

Systems for data collection on the job.

Access and security controls.

Peripheral equipment for computers, data system engineering.

Measuring and controlling.

Medical field and laboratory technology.





PRACTICAL MOBILE CASE DESIGNS



THE PRODUCT

The new MINITEC cases convince their users thanks to their mini-dimensions and maxi-benefits.

Whether round your neck or round your wrist, MINITEC cases are your loyal companions and are always within easy reach. They are so small and light that they also fit into any trouser pocket.

Whether with orange, green, blue or volcano-coloured intermediate rings or one coloured, these MINITEC cases are the right enclosures for today's personal electronics.

ENCLOSURE DESIGNS

You have a choice between an organic "MINITEC DROP" shape or a more technical "MINITEC EDGE" design.

Different intermediate rings and accessories offer the necessary flexibility for individual use.

Protection class IP 41

MINITEC DROP (sizes S and M) with intermediate ring in TPE.

Max. size of PCB (L x W in mm)


MINITEC DROP bottom part

S 35 x 27

M 51 x 38

L 57 x 45

(cutouts of pillars not taken into consideration)





THE PERFECT COMPANION

Protection class IP 41

MINITEC EDGE (size M)
with intermediate ring in TPE.

Max. size of PCB (L x W in mm)

MINITEC EDGE bottom part

S 36 x 24

M 51 x 34

L 53 x 40

(cutouts of pillars not taken into consideration)



YOUR ADVANTAGE

Modern, flat styling.

Easy to wear, e.g. round your neck,
or as a bracelet with wrist strap,
on a key ring or on a belt (EL).

TPE ring for a pleasant touch sensation
and as impact protection.

Also available in infra-red light-permeable material.

Recessed operating area for the
protection of the membrane keyboard
or decorative foil. MINITEC Edge also
without recessed operating area.

APPLICATIONS

Many different types of remote
control systems.

Specially made for clinic and social
fields as well as in the household
and in industry, e.g. emergency
systems, monitoring and alarm
equipment, radio remote control etc.



detailed drawings see our website
www.okw.com





MEASURING, CONTROLLING, REGULATING



THE PRODUCT

The robust range of wall mounted cases with freely accessible terminal compartment for easy component mounting and wiring.

The cases with a transparent case cover have an easy-to-operate closure system ensuring comfortable opening and closing.

These cases are particularly suitable for use in heating, air conditioning and ventilation technology, measurement and control technology, for machine and industrial controllers etc.

YOUR ADVANTAGE

Available either with or without transparent cover to protect the display and operating elements. Opening either to the right or to the left.

Alternatively available with front cover / front panel attachment (accessory).

Screw bosses and guides for the vertical and horizontal installation of printed circuit boards and mounting plates.


Direct wall mounting or external wall mounting brackets (accessory). Optional DIN rail mounting kit (accessory).

Protection class IP 65

With transparent enclosure cover or front lid.

Sizes (W x H x D1/D2 in mm)

W x H	D1	D2
166/188 x 160	80, 108	106, 134
213/235 x 185	90	119
257/280 x 219	122	156
296/320 x 260	95	129
363/390 x 316	134	167



detailed drawings see our website
www.okw.com

SMART-CASE

Order data on page 19



GOOD TO HOLD



NEW VERSIONS

SMART-CASE in ABS, black, RAL 9005 (M, L, XL) with black cable gland.

SMART-CASE M, closed version, without battery holder.

Sizes (L x W x H in mm)

SMART-CASE	
XS	58 x 35.6 x 19
M	96 x 47 x 24
L	140 x 62.7 x 30.5
XL	168 x 74.4 x 35.4

ART-CASE

Order data on page 18



GEOMETRIC PERFECTION




WALL MOUNTING

Wall suspension element in the colour black, RAL 9005 – to colour-match the lid (ART CASE ROUND & OVAL) and all bases for practical wall mounting of the ART CASES in black. Machining lid/base necessary.

Sizes (L x W x H in mm)

ART-CASE ROUND	110 x 110 x 30/38/41
ART-CASE SQUARE	110 x 110 x 38
ART-CASE OVAL	160 x 110 x 30/38/41
ART-CASE EDGE	160 x 110 x 38

SYSTEM COMPONENTS



YOUR APPLICATION / MINIMUM COMPONENTS REQUIRED

Mobile with battery compartment
5 x AA.

① ② ①

Mobile without battery compartment.

① ③ ①

Mobile with station
and battery compartment 5 x AA.
Contacts as accessory.

① ② ⑥ ①

Mobile with station
without battery compartment.

① ③ ⑥ ①

Mobile with battery compartment
5 x AA and wall suspension element
as base. Also ideal for flat wall
applications.

Contacts as accessory.

① ② ⑫ ①

Mobile without battery compart-
ment and wall suspension element
as base. Also ideal for flat wall
applications.

① ③ ⑫ ①

Desk-top / Wall

Case snaps into base. If required, unit
can be secured by latch lock.

① ④ ⑦ ①

Desk-top

Case screwed to base.

① ⑤ ①

INTERFACE-TERMINAL

Enclosure (for the difference between vers. I and II see front design options)
ABS (UL 94 HB), off-white RAL 9002, dim. in mm (L x W x H)

		Part-No. INTERFACE-TERMINAL S		Part-No. INTERFACE-TERMINAL M		Part-No. INTERFACE-TERMINAL L	
		I	II	I	II	I	II
① Bottom part	flat	B 40 42 707 (135 x 190 x 24.5)	B 40 42 717 (135 x 190 x 24.5)	B 40 44 707 (165 x 225 x 25.5)	B 40 44 717 (165 x 225 x 25.5)	B 40 46 707 (195 x 275 x 26.5)	B 40 46 717 (195 x 275 x 26.5)
	high	B 40 42 757 (135 x 190 x 34.5)	B 40 42 767 (135 x 190 x 34.5)	B 40 44 757 (165 x 225 x 35.5)	B 40 44 767 (165 x 225 x 35.5)	B 40 46 757 (195 x 275 x 36.5)	B 40 46 767 (195 x 275 x 36.5)

End piece for bottom part required, depending on the application

ABS (UL 94 HB), off-white RAL 9002, dim. in mm (L x W x H)


	S	M	L
② Battery compartment and lid, contacts tin-plated 5 x AA	B 41 42 047	B 41 44 047	B 41 46 047
③ Bottom panel with handle recess	B 41 42 167	B 41 44 167	B 41 46 167
④ Bottom panel with snap-in strips	B 41 42 257	B 41 44 257	B 41 46 257
⑤ Base (desk-top) with covers, for combinations with open bottom part ① (for screw-type connection*)	B 40 42 827 (123 x 123 x 53)	B 40 44 827 (153 x 153 x 63)	B 40 46 827 (183 x 183 x 73)
⑥ Base (station for mobile case) with base covers, for combinations ① with ② or ③ (for hanging in position / snap-in connection*)	B 40 42 837 123 x 123 x 60	B 40 44 837 153 x 153 x 70	B 40 46 837 (183 x 183 x 80)
⑦ Base (desk-top/wall) with clips and latch-lock, for combination ① with ④ (snap-in connection)	B 40 42 847 (123 x 123 x 53)	B 40 44 847 (153 x 153 x 63)	B 40 46 847 (183 x 183 x 73)
⑫ Wall suspension element with snap-in connection, for combinations ① with ② or ③, not suitable for case with base	B 41 42 247	B 41 44 247	B 41 46 247

Front design

		suitable for bottom part S		suitable for bottom part M		suitable for bottom part L	
		I	II	I	II	I	II
⑧ Cover ABS (UL 94 HB), off-white RAL 9002	outside dim. in mm max. dim. keypad in mm	B 40 42 407 135 x 190 x 12 123 x 162	—	B 40 44 407 165 x 225 x 12 153 x 197	—	B 40 46 407 195 x 275 x 12 183 x 247	—
⑨ Front panel Al, matt anodised	outside dim. in mm	B 41 42 106 131.5 x 186.5 x 2	—	B 41 44 106 161.5 x 221.5 x 2	—	B 41 46 106 191.5 x 271.5 x 2	—
⑩ Front panel ABS (UL 94 HB) off-white RAL 9002	outside dim. in mm max. dim. keypad in mm	—	B 41 42 107 131.7 x 186.7 x 3	—	B 41 44 107 161.7 x 221.7 x 3	—	B 41 46 107 191.7 x 271.7 x 3
⑪ Glass panel without printing*	outside dim. in mm	—	B 41 42 203 128.7 x 183.7 x 4	—	B 41 44 203 158.7 x 218.7 x 4	—	B 41 46 203 188.7 x 268.7 x 4

INTERFACE-TERMINAL ACCESSORIES

Article	S	M	L
⑬ Contact, male for ⑥, 6-pole* ¹	A 91 78 007	A 91 78 007	A 91 78 007
Contact, female for ② or ③, 6-pole* ¹	A 91 78 008	A 91 78 008	A 91 78 008
⑭ Sealing, bottom part - front	B 41 42 005	B 41 44 005	B 41 46 005
⑮ Sealing, bottom part - base/bottom panel/battery comp.	B 41 42 006	B 41 44 006	B 41 46 006
⑮ Sealing, base - base cover (⑥)	B 41 42 006	B 41 44 006	B 41 46 006



*¹ holes required, for assembly instruction please refer to our website

*² snap-in installation advisable for wall mounted use and for use of contacts (accessories).

*³ kit with adhesive foil and mounting frame; display window with individual printing adapted to your visible display cutout as well as to cover the area of adhesive foil, on demand



DIATEC

Enclosure	Size	Outside dim. in mm			Equipment (dim. in mm) max. dim. keypad	Material	Part-No.	
		L	W	H			off-white RAL 9002	lava NCS S 7502-B
	XS* ¹ NEW	155	150	37		ABS (UL 94 HB)	A 90 92 107	A 90 92 108
	S* ²	200	210	48	127.60 x 119.70	ABS (UL 94 HB)	A 90 93 107	A 90 93 108
	M* ²	200	270	48	127.60 x 179.60	ABS (UL 94 HB)	A 90 94 107	A 90 94 108
	L* ² NEW	200	330	48		ABS (UL 94 HB)	A 90 95 107	A 90 95 108

DIATEC ACCESSORIES

Article	For DIATEC	Version / Application	ABS, case colour* ³	Part-No.	
				PC, translucent* ⁴	PC, clear* ⁴
① Hinged lid	S, L (off-white)* ⁵	2 mounting holes ø 4.2 mm necessary, 1 set	A 91 93 127	A 91 93 121	A 91 93 131
	S, L (lava)* ⁵	2 mounting holes ø 4.2 mm necessary, 1 set	A 91 93 128	A 91 93 122	A 91 93 132
	M (off-white)	2 mounting holes ø 4.2 mm necessary, 1 set	A 91 94 127	A 91 94 121	A 91 94 131
	M (lava)	2 mounting holes ø 4.2 mm necessary, 1 set	A 91 94 128	A 91 94 122	A 91 94 132

Article	For DIATEC	Version / Application	Part-No.
② Slot-in panel	S, M, L	ABS, off-white, 156 x 30 x 3 mm, 1 pc	A 91 94 007
③ Set of battery clips NEW	XS	nickel-plated for 2 x 1.5 V mignon cells (AA)	A 91 90 015
	S, M, L	tin-plated for 2 x 1.5 V mignon cells (AA)	A 91 90 002
④ Plug-in contact	S, M, L	for one 9 V flat battery (PP3), 1 pc	A 91 60 003
⑤ Non-slip pads	XS	transparent, self-adhesive, ensure reliable desk-top positioning, 1 pair	A 92 07 150
	S, M, L	transparent, self-adhesive, ensure reliable desk-top positioning, 1 pair	A 92 12 330
⑥ Self-tapping screw	XS, S, M, L	ø 3 x 6 mm (PZ1), for mounting PCBs, 1 pc	A 03 06 031
⑦ Torx screwdriver T10 NEW	XS	Torx 10, with ergonomic handle, for assembling enclosure	A 03 99 T10



UNIVERSAL ACCESSORIES

Self-tapping screw	Version / Application	Part-No.
	ø 3 x 8 mm (Torx 10), stainless steel, 1 pc As an alternative to A 03 08 031 (self-tapping screw ø 3 x 8 mm with cross recess PZ1) for PCB mounting – for information on which screw diameter matches which OKW case, please refer to www.okw.com . Or as a substitute for case assembly DIATEC XS (2 pcs. required).	NEW A 03 08 132

*¹ Supply: 1 bottom and top part each, assembly kit.

Assembly of bottom and top part with 2 Torx T10 self-tapping screws, stainless steel.

*² Supply: 1 bottom and top part each, 1 trim left and right side incl. 2 locking elements, assembly kit.

Assembly of top and bottom part with 4 self-tapping screws (PZ2), snap-on side trims. If required, the trims can also be locked, thus preventing unauthorised access.

*³ in the relevant case colour

*⁴ fasteners from the assembly set in the case colour in question

*⁵ hinged lid for covering the dialogue area of the DIATEC S or for partially covering the dialogue area of the DIATEC L (half side)

MINITEC DROP

Bottom and top part	Size	Outside in mm			Equipment (dim. in mm) max. dim. keypad	Part-No.		PMMA*2 black
		L	W	H		ABS (UL 94 HB) off-white	lava	
	S	51	32	13	38.60 x 18.15	B 90 02 907	B 90 02 908	B 90 02 906
	M	70	44	16	52.55 x 23.70	B 90 04 907	B 90 04 908	B 90 04 906
	L	84	53	19	63.95 x 30.10	B 90 06 907	B 90 06 908	B 90 06 906

Intermediate ring	Material	Colour				S			S
							M	L	
	TPE	 lava, NCS S 7502-B				B 90 02 302	B 90 04 302	B 90 06 302	B 90 02 352
	TPE	 orange, NCS S 1070-Y40R				B 90 02 303	B 90 04 303	B 90 06 303	B 90 02 353
	TPE	 green, NCS S 1070-G60Y				B 90 02 304	B 90 04 304	B 90 06 304	B 90 02 354
	TPE	 blue, NCS S 1060-B				B 90 02 305	B 90 04 305	B 90 06 305	B 90 02 355
	PMMA*2	 black, RAL 9005				B 90 02 306	B 90 04 306	B 90 06 306	B 90 02 356
	TPE	 off-white, RAL 9002				B 90 02 307	B 90 04 307	B 90 06 307	B 90 02 357
	TPE	 volcano, NCS S 5502-G				B 90 02 308	B 90 04 308	B 90 06 308	B 90 02 358
	ABS	 black, RAL 9005				B 90 02 309	B 90 04 309	B 90 06 309	B 90 02 359

MINITEC EGDE

Bottom and top part	Size	Outside dim. in mm			Equipment (dim. in mm)	Part-No.		PMMA*2 black
		L	W	H	max. dim. keypad	ABS (UL 94 HB) off-white	lava	
	S	52	32	15	34.90 x 19.85	B 90 02 807	B 90 02 808	B 90 02 806
		52	32	15	without recess	B 90 02 857	B 90 02 858	B 90 02 856
	M	68	42	18	45.00 x 27.85	B 90 04 807	B 90 04 808	B 90 04 806
		68	42	18	without recess	B 90 04 857	B 90 04 858	B 90 04 856
	L	78	48	20	51.60 x 31.95	B 90 06 807	B 90 06 808	B 90 06 806
		78	48	20	without recess	B 90 06 857	B 90 06 858	B 90 06 856
	NEW	78	48	24	51.50 x 29.70	B 90 06 817	B 90 06 818	B 90 06 816
		78	48	26	51.50 x 29.70	B 90 06 827	B 90 06 828	B 90 06 826

Intermediate ring	Material	Colour							 NEW
			S	M	L	S	M	L	
	TPE	 lava	B 90 02 702	B 90 04 702	B 90 06 702	B 90 02 752	B 90 04 752	B 90 06 752	B 90 06 782
	TPE	 orange	B 90 02 703	B 90 04 703	B 90 06 703	B 90 02 753	B 90 04 753	B 90 06 753	B 90 06 783
	TPE	 green	B 90 02 704	B 90 04 704	B 90 06 704	B 90 02 754	B 90 04 754	B 90 06 754	B 90 06 784
	TPE	 blue	B 90 02 705	B 90 04 705	B 90 06 705	B 90 02 755	B 90 04 755	B 90 06 755	B 90 06 785
	PMMA*2	 black	B 90 02 706	B 90 04 706	B 90 06 706	B 90 02 756	B 90 04 756	B 90 06 756	B 90 06 786
	TPE	 off-white	B 90 02 707	B 90 04 707	B 90 06 707	B 90 02 757	B 90 04 757	B 90 06 757	B 90 06 787
	TPE	 volcano	B 90 02 708	B 90 04 708	B 90 06 708	B 90 02 758	B 90 04 758	B 90 06 758	B 90 06 788
	ABS	 black	B 90 02 709	B 90 04 709	B 90 06 709	B 90 02 759	B 90 04 759	B 90 06 759	B 90 06 789

MINITEC ACCESSORIES

Article	For MINITEC	Version / Application	Part-No.
① Key ring	E (Edge) / D (Drop)	nickel-plated, ø 20.5 mm	A 91 64 001
② Carrying strap „Reflex“	E (Edge) / D (Drop)	silver/black with quick-action lock, approx. 860 mm long	B 91 00 022
③ Carrying strap „Woven“	E (Edge) / D (Drop)	black, with safety closure, approx. 900 mm long	B 91 00 053
④ Hand strap „Woven“	E (Edge) / D (Drop)	grey, with quick-action lock, approx. 200 mm long	B 91 00 044
⑤ Wrist strap	E (Edge, 2 strap loops)	black, elastic belt with velcro, approx. 280 mm long	B 91 00 033
⑥ Strap eyelet	E (Edge size L)	ABS lava, for belts or belt webbing up to 34 x 4 mm, horizontally/vertically use, incl. screws for mounting	B 91 06 108



*1 To achieve one MINITEC, please order:
1 bottom and top part
1 intermediate ring
(assembly kit supplied with case)

2 cases made of PMMA (plexiglass) not comparable to cases made of ABS in terms of mechanical load-bearing capacity

WALLTEC

Enclosure	Type	Outside dim. in mm W H D	Equipment premarked openings for cable entry and outlet	Material	Part-No. light grey RAL 7035
	WALLTEC 166 F	166 160 80	rear	ABS (UL 94 HB)	A 97 30 101
	WALLTEC 166 D	166 160 108	rear	ABS (UL 94 HB)	A 97 31 101
	WALLTEC 213	213 185 90	rear	ABS (UL 94 HB)	A 97 32 101
	WALLTEC 257	257 219 122	rear	ABS (UL 94 HB)	A 97 33 101
	WALLTEC 296	296 260 95	rear	ABS (UL 94 HB)	A 97 34 101
	WALLTEC 363	363 316 134	rear	ABS (UL 94 HB)	A 97 35 101
Enclosure with transparent cover*1	Type	Outside dim. in mm W H D	Equipment premarked openings for cable entry and outlet	Material	Part-No. light grey RAL 7035
	WALLTEC 188 F	188 160 106	rear	PC (UL 94 5V)	A 97 30 112
	WALLTEC 188 D	188 160 134	rear	PC (UL 94 5V)	A 97 31 112
	WALLTEC 235	235 185 119	rear	PC (UL 94 5V)	A 97 32 112
	WALLTEC 280	280 219 156	rear	PC (UL 94 5V)	A 97 33 112
	WALLTEC 320	320 260 129	rear	PC (UL 94 5V)	A 97 34 112
	WALLTEC 390	390 316 167	rear	PC (UL 94 5V)	A 97 35 112

WALLTEC ACCESSORIES

Article	For type	Version / Application	Part-No.
① Front lid	WALLTEC 166 F / D	PC (UL 94 5V), light grey, 166 x 106 x 16 mm, max. dim. keypad 131 x 93 mm	A 91 30 102
	WALLTEC 213	PC (UL 94 5V), light grey, 213 x 125 x 20 mm, max. dim. keypad 179.2 x 112 mm	A 91 32 102
	WALLTEC 257	PC (UL 94 5V), light grey, 257 x 157 x 30 mm, max. dim. keypad 222.4 x 143.3 mm	A 91 33 102
	WALLTEC 296	PC (UL 94 5V), light grey, 296 x 196 x 30 mm, max. dim. keypad 251.6 x 182.4 mm	A 91 34 102
② Front panel	WALLTEC 166 / 188	Al, matt anodised, 158.5 x 98.5 x 1.5 mm	A 91 30 116
	WALLTEC 213 / 235	Al, matt anodised, 205.5 x 117.5 x 1.5 mm	A 91 32 116
	WALLTEC 257 / 280	Al, matt anodised, 250 x 150 x 1.5 mm	A 91 33 116
	WALLTEC 296 / 320	Al, matt anodised, 288 x 188 x 1.5 mm	A 91 34 116
	WALLTEC 363 / 390	Al, matt anodised, 353 x 223 x 1.5 mm	A 91 35 116
③ Mounting plate (screws supplied with enclosure)	WALLTEC 166 / 188	Steel, galvanized, 136 x 133 x 1.5 mm, for mounting of components	A 91 30 127
	WALLTEC 213 / 235	Steel, galvanized, 142 x 200 x 1.5 mm, for mounting of components	A 91 32 127
	WALLTEC 257 / 280	Steel, galvanized, 225 x 175 x 1.5 mm, for mounting of components	A 91 33 127
	WALLTEC 296 / 320	Steel, galvanized, 282 x 215 x 1.5 mm, for mounting of components	A 91 34 127
	WALLTEC 363 / 390	Steel, galvanized, 345 x 258 x 1.5 mm, for mounting of components	A 91 35 127
④ Wall mounting bracket*2	166 F/D, 188 F/D,	PC (UL 94 5V), light grey, set with 2 pcs incl. screws	A 91 00 132
⑤ Fastening element for DIN-Rails*2	213, 235, 257, 280	PC (UL 94 5V), light grey, for DIN EN 60715 TH35, set with 2 pcs (right/left)	A 91 00 142
⑥ Screw 40 x 18*2	with transp. cover	additional fastening for cover closure, 1 pc	A 91 00 156



ART-CASE ADDITIONS

Information on page 12

Article	For ART-CASE with	Version / Application	Part-No.
Wall mounting set NEW	lid (R, O) or base (R, S, O, E)	ABS, black RAL 9005, for the safe and secure wall mounting of the case (machining lid/bases necessary), removal protection device with screw	B 51 11 309
 Enclosures and further accessories see our website / catalogue pages 80-82.			

*1 cover not mounted; lock PA, green, RAL 6016; see assembly instruction on our website www.okw.com*2 see assembly instruction on our website www.okw.com

SMART-CASE

SMART-CASE		Outside dim. in mm			Version / Equipment (dim. in mm)		max. dim. keypad	ABS (UL 94 HB)		black (gland black)	PMMA plexiglass® black*1
		L	W	H	battery compartment	cable gland approx. ø		off-white (cable gland: volcano vers. III-V)	black		
	XS	58	35,6	19	—	—	without recess	A 90 64 107	A 90 64 109	—	A 90 64 209
	M	96	47	24	I 2 x AAA	—	74.60 x 39.85	A 90 66 107	A 90 66 109	—	A 90 66 209
		96	47	24	II 2 x AAA	—		A 90 66 117	A 90 66 119	—	A 90 66 219
		96	47	24	III —	5.0 - 5.9		A 90 66 127	A 90 66 129	A 90 66 329	—
		96	47	24	IV —	4.2 - 5.0		A 90 66 137	A 90 66 139	A 90 66 339	—
		96	47	24	V —	3.4 - 4.2		A 90 66 147	A 90 66 149	A 90 66 349	—
		96	47	24	—	—		A 90 66 317	A 90 66 319	—	A 90 66 419
		96	47	24	—	—		—	—	—	—
	L	140	62.7	30.5	I 2 x AA / 1 x 9 V	—	103.95 x 50.95	A 90 67 107	A 90 67 109	—	A 90 67 209
		140	62.7	30.5	II —	—		A 90 67 117	A 90 67 119	—	A 90 67 219
		140	62.7	30.5	III —	5.0 - 5.9		A 90 67 127	A 90 67 129	A 90 67 329	—
		140	62.7	30.5	IV —	4.2 - 5.0		A 90 67 137	A 90 67 139	A 90 67 339	—
		140	62.7	30.5	V —	3.4 - 4.2		A 90 67 147	A 90 67 149	A 90 67 349	—
	XL	168	74.4	35.4	I 2 x AA / 1 x 9 V	—	110.60 x 61.05	A 90 68 107	A 90 68 109	—	A 90 68 209
		168	74.4	35.4	II —	—		A 90 68 117	A 90 68 119	—	A 90 68 219
		168	74.4	35.4	III —	5.0 - 5.9		A 90 68 127	A 90 68 129	A 90 68 329	—
		168	74.4	35.4	IV —	4.2 - 5.0		A 90 68 137	A 90 68 139	A 90 68 339	—
		168	74.4	35.4	V —	3.4 - 4.2		A 90 68 147	A 90 68 149	A 90 68 349	—

SMART-CASE ACCESSORIES

Article	For SMART-CASE	Version / Application	Part-No.	
① Set of battery clips	M	tin-plated, for 2 x 1.5 V micro cells (AAA)	A 91 66 001	
	L, XL	tin-plated, for 2 x 1.5 V mignon cells (AA)	A 91 90 002	
② Battery contact	M	tin-plated, for a serial connection when using the set of battery clips	A 91 66 002	
③ Battery holder	M	clamps down securely 2 x AAA	A 91 66 003	
④ Plug-in contact	L, XL	for one 9 V flat battery	A 91 60 003	
⑤ Sealing	L	for versions II-V, for a higher protection class (IP 65)	A 91 67 002	
	XL	for versions II-V, for a higher protection class (IP 65)	A 91 68 002	
⑥ Set of strain relief	M, L, XL & station	for strain relief of cable connected applications	A 91 66 004	
⑦ Key ring	XS	nickel-plated, ø 20.5 mm	A 91 64 001	
			off-white	black
⑧ Belt / pocket clip	M, L, XL	PA 6, 2 mounting holes ø 4.2 mm necessary	A 91 67 017	A 91 67 019
⑨ Holding clamp	M, L, XL	up to ø 32 mm, ABS, 2 mounting holes ø 4.2 mm necessary	A 91 67 027	A 91 67 029
⑩ Holder	M	ABS, also suitable for cable connected applications	A 91 66 307	A 91 66 309
	L	ABS, also suitable for cable connected applications	A 91 67 307	A 91 67 309
	XL	ABS, also suitable for cable connected applications	A 91 68 307	A 91 68 309
⑪ Adhesive foil for holder	holder M	double-sided adhesive foil with foam carrier	A 91 66 005	
	holder L	double-sided adhesive foil with foam carrier	A 91 67 005	
	holder XL	double-sided adhesive foil with foam carrier	A 91 68 005	
⑫ Station	M	ABS, desk case application	A 91 66 037	A 91 66 039
	L	ABS, desk case application	A 91 67 037	A 91 67 039
	XL	ABS, desk case application	A 91 68 037	A 91 68 039
⑬ Contacts (bore holes necessary)	M, L, XL	contact pin, gold-plated, < 15 A	A 91 93 030	
	M, L, XL	spring contact, gold-plated, F 0.3 N, travel 1.5 mm, < 3 A	A 91 93 032	



for ring eyelet see
www.okw.com

*1 sizes L & XL only the bottom parts made of PMMA, top part is made of ABS (UL 94 HB); cases made of PMMA (plexiglass®) not comparable to cases made of ABS in terms of mechanical load-bearing capacity

SALES NETWORK

OKW worldwide



A Austria

Ineltro Electronics GmbH
Lamezanstr. 10
1230 Wien
Tel. (1) 610 62-0
E-Mail info@ineltro.at
Web www.ineltro.at

AUS Australia

Soanar Pty Ltd
39 Hewish Road
Croydon, Victoria 3136
Tel. 61 3 9724 0888
E-Mail okw@soanar.com
Web www.soanar.com

B Belgium

Telerex N.V.
Bisschoppenhoflaan 255
2100 Antwerpen
Tel. (03) 3 26 40 00
E-Mail info@telerex-europe.com
Web www.telerex-europe.com

BD Bangladesh

see
Schurter Electronics (India) Pvt. Ltd.,
IND India

BG Bulgaria

K1 Electronics Ltd.
55B, Layosh Koshut Str.
1606 Sofia
Tel. (2) 9 53 15 50
E-Mail office@k1-bg.com
Web www.k1-bg.com

BR Brazil

sob
Schurter + OKW do Brasil
Componentes Eletrônicos Ltda.
Rua Novo Cancioneiro, 93 - Brooklin
São Paulo - SP - CEP 04704-080
Tel. 11 50 90 00 30
E-Mail info@sob-brasil.com
Web www.sob-brasil.com

BY Belarus

Components & Systems Ltd.
M. Tank Street, 2, of. 1
220004 Minsk
Tel. (017) 3 06 32 35
E-Mail hand@composyst.ru
Web www.composyst.ru

CDN Canada

see OKW Enclosures Inc.,
U.S.A.

CH Switzerland

okatron AG
Altgraben 31
4624 Härkingen
Tel. 062 3 98 44 11
E-Mail info@okatron.ch
Web www.okatron.ch

CN China

Phoeni-tech Industry & Trading
(Shanghai) Co. Ltd.
Jiao Zhou Rd. 728
Jiao Zhou Mansion Rm No. 0301
200040 Shanghai CN
Tel. 21 62 98 87 20 / 62 98 61 86
E-Mail phoenitec@online.sh.cn

CZ Czech Republic

okatec spol. s r.o.
Zámecká 193
564 01 Zámberk
Tel. 465 61 80 61
E-Mail info@okatec.cz
Web www.okatec.cz

D Germany

ORCA Gehäusetechnik GmbH
Vertriebsgesellschaft Deutschland Nord
Kreuzbreite 2
31737 Rinteln
Tel. (0 57 51) 92 52 70
E-Mail info@orcanord.de
Web www.orca-gehaeuse.com

ORCA Gehäusetechnik GmbH
Vertriebsgesellschaft Deutschland Süd
Friedrich-List-Str. 7
74722 Buchen
Tel. (0 62 81) 56 23 0
E-Mail info@orca-gehaeuse.com
Web www.orca-gehaeuse.com

okw Kunststofftechnik GmbH
Vertriebsgesellschaft Deutschland Ost
Karlsbader Str. 5
09456 Annaberg-Buchholz
Tel. (0 37 33) 67 69 0
E-Mail info@okw-kunststofftechnik.de
Web www.okw-kunststofftechnik.de

DK Denmark

Thorkild Larsen A/S
Fabriksvangen 17
3550 Slangerup
Tel. 48 18 66 66
E-Mail vg@thorkild-larsen.dk
Web www.thorkild-larsen.dk

E Spain

Cenvalsa
Ulises, n° 104
28043 Madrid
Tel. (91) 7 21 60 12
E-Mail sismecanic@cenval.es
Web www.cenval.es

EST Estonia

Elke Sensor LLC
Elektroni t. 8-60
11316 Tallinn
Tel. 372 655 40 06
E-Mail info@elkesensor.ee
Web www.elkesensor.ee

F France

okatron sas
ZAC Paris Nord 2, B.P. 69038
22, avenue des Nations
95971 Roissy CDG Cedex
Tel. 01 48 63 28 48
E-Mail okatron@okatron.fr
Web www.okatron.fr

okatron sas
Agence Sud-Est
Villa Mercedes - Bât. C
153, route de Vourles
69230 Saint-Genis-Laval
Tel. 04 78 56 80 00

FIN Finland

Noretron Komponentit Oy
PL 22 (Mankkaantie 32)
02631 Espoo
Tel. 010 5 25 80 00
E-Mail komponentit@noretron.fi
Web www.noretron.fi

GR Greece

MAR Electronics
10, Salaminos Str.
54625 Thessaloniki
Tel. (2310) 53 26 58
E-Mail info@marelectronics.gr
Web www.marelectronics.gr

H Hungary

INNOMED Medical zrt.
Szabó József u. 12
1146 Budapest
Tel. 460-9212
E-Mail innomed@innomed.hu
Web www.innomed.hu

I Italy

Alhof di A. Hofmann SPA
Via Melegnano 20
20019 Settimo Milanese MI
Tel. (02) 28 50 08 1
E-Mail alhof@alhof.com
Web www.alhof.com

IL Israel

Ambi-Tech Electronics
20 Ta'as st. „Beit hapa'amon“
industrial area, Kfar-Saba
P.O. Box 50
Kfar-Saba 44425
Tel. 972-9-76 77 500
E-Mail pweiss@netvision.net.il
Web www.pweiss.co.il

IND India

Schurter Electronics (India) Pvt. Ltd.
EPIP Plot# E-59, 60, 61, EPIP Zone, GIDC,
Manjusr - 391 775
Vadodara Savli Road, District-Vadodara
Gujarat
Tel. 91 2667 26 47 53 / 4
E-Mail sales@schurter.co.in
Web www.schurter.co.in

IRL Ireland

see OKW Enclosures Ltd.,
UK United Kingdom

J Japan

Settsu Metal
Industrial Co., Ltd.
4-1-26, Yagumonishi, Moriguchi
Osaka 570-0006
Tel. 06-69 92-23 31
E-Mail eigyou@settsu.co.jp
Web www.settsu.co.jp

KSA Kingdom Saudi Arabia

see
Schurter Electronics (India) Pvt. Ltd.,
IND India

LK Sri Lanka

see
Schurter Electronics (India) Pvt. Ltd.,
IND India

LT Lithuania

JML GROUP UAB
NAUGARDUKO 91-108
03202 Vilnius
Tel. +370 52 13 36 03
E-Mail info@jml-group.lt
Web www.jml-group.lt

MAL Malaysia

see Camwell Industries Pte. Ltd.,
SGP Singapore

N Norway

Freber Elektronik AS
Box 3583
3007 Drammen
Tel. 32 20 88 20
E-Mail mailbox@freber.no
Web www.freber.no

NL Netherlands

Telerex Nederland B.V.
Postbus 6852
4802 HW Breda
Tel. (0 76) 5 78 20 00
E-Mail info@telerex-europe.com
Web www.telerex-europe.com

NZ New Zealand

Soanar (New Zealand) Pty Ltd
16-18 Fisher Crescent
Mt Wellington, Auckland 1060
Tel. 64 9 258 5133
E-Mail okw@soanar.com
Web www.soanar.com

P Portugal

Niposom - J. Nabais LDA
Rua Humberto Cruz, 4
1900-260 Lisboa
Tel. 351-21-844 02 00
E-Mail smsantos.gp@niposom.com
Web www.niposom.pt

PL Poland

LC Elektronik
UL. PULKOWA 58
01-969 Warszawa
Tel. (22) 569 53 00
E-Mail lcel@lcel.com.pl
Web www.lcel.com.pl

RI Indonesia

see Camwell Industries Pte. Ltd.,
SGP Singapore

RO Romania

SC EEE S.A.
Bv. Industriilor Nr. 4
300714 Timisoara
Tel. (0) 256 29 16 61
E-Mail ee@eee.ro
Web www.eee.ro

ROK South Korea

Zoontech Enclosuresystem Co.
4525, Ma-dong
Joongang Circulation Complex
1258, Kurobon-don
Kuro-ku, Seoul
Tel. (82) 2 2060 8125
E-Mail jschoi@zoontech.com
Web www.zoontech.com

RU Russia

EFO Ltd.
Politechnicheskaja, 21
St. Petersburg, 194021
Tel. (8 12) 3 31 09 64
E-Mail eve@efo.ru
Web www.korpusera.ru
www.okw.ru

S Sweden

Swetouch AB
Vasagatan 3
573 31 Tranås
Tel. (0) 140 77 33 80
E-Mail patrik@swetouch.se
Web www.swetouch.se

Elfa AB
Elektronikhöjden 14
17580 Järfälla
Tel. (08) 58 09 41 00
E-Mail order@elfa.se
Web www.elfa.se

SRB Serbia

TAGOR Electronic d.o.o.
Tihomira Brankovica 21
18000 Niš
Tel. 381 18 575 545
E-Mail okw@tagor.rs
Web www.tagor.rs

SGP Singapore

Camwell Industries Pte. Ltd.
59 Ubi Avenue 1
#05-08 Bizlink Centre
Singapore 408938
Tel. (65) 67 41 32 33
E-Mail sales@camwell.com.sg
Web www.camwell.com.sg

SK Slovakian Republic

see okatec spol. s r.o.,
CZ Czech Republic

SLO Slovenia

Wilsonic d.o.o.
Verje 28b
1215 Medvode
Tel. 386-1-3611278
E-Mail sonja@wilsonic.si
Web www.wilsonic.si

TH Thailand

see Camwell Industries Pte. Ltd.,
SGP Singapore

TR Turkey

Spektrum Elektronik
Salih Omurtak Cad No 65 Kosuyolu
34718 Istanbul
Tel. (216) 4 28 45 45
E-Mail contact@spektrumelektronik.com
Web www.spektrumelektronik.com

TW Taiwan

MechaTronix Kaohsiung Co. Ltd.
4F, No. 308, Bade 1st Rd.
Sinsin district, Kaohsiung 800
Tel. +886-7-238-2185
E-Mail annie@mechatronix-asia.com
Web www.mechatronix-asia.com

UA Ukraine

Biakom Ltd.
95-C, Vidradny Prospect
03061 Kiev
Tel./Fax +38 (044) 507-02-03
mob. +38-068-128-7164
E-Mail oxana.novikova@biakom.kiev.ua
Web www.biakom.com

UAE United Arab Emirates

see
Schurter Electronics (India) Pvt. Ltd.,
IND India

UK United Kingdom

OKW Enclosures Ltd.
15 Brunel Way
Segensworth East
Fareham, PO15 5TX
Tel. (0 14 89) 58 38 58
E-Mail sales@okw.co.uk
Web www.okw.co.uk

U.S.A. United States of America

OKW Enclosures Inc.
3000 Old Pond Road
Bridgeville PA 15017
Tel. (800) 9 65 98 72
E-Mail sales@okwenclosures.com
Web www.okwenclosures.com

VN Vietnam

see Camwell Industries Pte. Ltd.,
SGP Singapore

ZA South Africa

Avnet Kopp (Pty) Ltd.
P.O. Box 3853
Rivonia 2128
Tel. (0) 11 8 09 61 00
E-Mail sales@avnet.co.za
Web www.avnet.co.za

Manufacturer

Odenwälder Kunststoffwerke
Gehäusesysteme GmbH
Friedrich-List-Str. 3
74722 Buchen/Germany

Sales Germany

Tel. +49 (0) 62 81 / 4 04-128
Fax +49 (0) 62 81 / 4 04-144
E-Mail InfoOG@okw.com

Sales Export

Tel. +49 (0) 62 81 / 4 04-165
Fax +49 (0) 62 81 / 4 04-123
E-Mail DittmannD@okw.com

