




MICRO SWITCH
FREEPORT ILLINOIS U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH-ENCLOSED

CATALOG LISTING
622EN133-R




WARNING- THIS PRODUCT IS SUBJECT TO THE U.S. INTERNATIONAL TRAFFIC IN ARMS REGULATIONS (ITAR), AND THE EXPORT CONTROL LAWS OF THE UNITED STATES. TRANSFER OF TECHNICAL DATA PERTAINING TO THIS PRODUCT BY ANY MEANS TO A FOREIGN PERSON PER ITAR DEFINITIONS, WHETHER IN THE UNITED STATES OR ABROAD, WITHOUT A PRIOR EXPORT LICENSE OR OTHER APPROVAL FROM THE U.S. DEPARTMENT OF STATE, IS PROHIBITED.



- NOTES**
- 1 - CORROSION RESISTANT STEEL ENCLOSURE
 - 2 - SWITCH SEALED PER MIL-PRF-8805 SYMBOL 4
 - 3 - DEUTSCH RECEPTACLE
 - 4 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .010 OF PLUNGER TRAVEL
 - 5 - ELECTRICAL RATINGS APPLY AS SPECIFIED IN MIL-PRF-8805/43 UP TO 185°F
 - 6 - CIRCUIT DIAGRAM AND CATALOG LISTING ARE SHOWN ON NAMEPLATE
 - 7 - CIRCUIT DIAGRAM - LETTERS ARE ASSOCIATED WITH RECEPTACLE - NUMBERS ARE ASSOCIATED WITH WIRING
 - 8 - CONNECTOR MUST BE PERPENDICULAR WITH CENTERLINE OF BUSHING KEYWAY WITHIN ±6°
 - 9 - ROLLER MUST BE IN-LINE WITH BUSHING KEYWAY WITHIN 2.5° ROLLER PLUNGER CAN BE ROTATED CLOCKWISE OR COUNTER CLOCKWISE TO ALIGN THE KEYWAY WITHIN 2.5°
 - 10 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805

622EN133-R
M
DRAWING NUMBER
9
ISSUE
REVISIONS
A 0047573 PART 4 R J H 15 AUG 80
B 0049806 J A P 25 SEPT 81
C 0052703 D J W 4 FEB 83
D 0057370 M A M 16 MAY 85
E 0064618 J A S 1 NOV 88
F 0073035 D A W 1 JUL 92
G 0075612-8 W E S 16 AUG 93
H 0006802 T C C / A P 30 AUG 04
FO-52851-A
DRAWN
G J W
CHECK
I MAY 80
CHECK
J MAY 80
CHECK
K MAY 80
CHECK
L MAY 80
CHECK
M MAY 80
CHECK
N MAY 80
CHECK
O MAY 80
CHECK
P MAY 80
CHECK
Q MAY 80
CHECK
R MAY 80
CHECK
S MAY 80
CHECK
T MAY 80
CHECK
U MAY 80
CHECK
V MAY 80
CHECK
W MAY 80
CHECK
X MAY 80
CHECK
Y MAY 80
CHECK
Z MAY 80
CHECK
AA MAY 80
CHECK
AB MAY 80
CHECK
AC MAY 80
CHECK
AD MAY 80
CHECK
AE MAY 80
CHECK
AF MAY 80
CHECK
AG MAY 80
CHECK
AH MAY 80
CHECK
AI MAY 80
CHECK
AJ MAY 80
CHECK
AK MAY 80
CHECK
AL MAY 80
CHECK
AM MAY 80
CHECK
AN MAY 80
CHECK
AO MAY 80
CHECK
AP MAY 80
CHECK
AQ MAY 80
CHECK
AR MAY 80
CHECK
AS MAY 80
CHECK
AT MAY 80
CHECK
AU MAY 80
CHECK
AV MAY 80
CHECK
AW MAY 80
CHECK
AX MAY 80
CHECK
AY MAY 80
CHECK
AZ MAY 80
CHECK
BA MAY 80
CHECK
BB MAY 80
CHECK
BC MAY 80
CHECK
BD MAY 80
CHECK
BE MAY 80
CHECK
BF MAY 80
CHECK
BG MAY 80
CHECK
BH MAY 80
CHECK
BI MAY 80
CHECK
BJ MAY 80
CHECK
BK MAY 80
CHECK
BL MAY 80
CHECK
BM MAY 80
CHECK
BN MAY 80
CHECK
BO MAY 80
CHECK
BP MAY 80
CHECK
BQ MAY 80
CHECK
BR MAY 80
CHECK
BS MAY 80
CHECK
BT MAY 80
CHECK
BU MAY 80
CHECK
BV MAY 80
CHECK
BW MAY 80
CHECK
BX MAY 80
CHECK
BY MAY 80
CHECK
BZ MAY 80
CHECK
CA MAY 80
CHECK
CB MAY 80
CHECK
CC MAY 80
CHECK
CD MAY 80
CHECK
CE MAY 80
CHECK
CF MAY 80
CHECK
CG MAY 80
CHECK
CH MAY 80
CHECK
CI MAY 80
CHECK
CJ MAY 80
CHECK
CK MAY 80
CHECK
CL MAY 80
CHECK
CM MAY 80
CHECK
CN MAY 80
CHECK
CO MAY 80
CHECK
CP MAY 80
CHECK
CQ MAY 80
CHECK
CR MAY 80
CHECK
CS MAY 80
CHECK
CT MAY 80
CHECK
CU MAY 80
CHECK
CV MAY 80
CHECK
CW MAY 80
CHECK
CX MAY 80
CHECK
CY MAY 80
CHECK
CZ MAY 80
CHECK
DA MAY 80
CHECK
DB MAY 80
CHECK
DC MAY 80
CHECK
DD MAY 80
CHECK
DE MAY 80
CHECK
DF MAY 80
CHECK
DG MAY 80
CHECK
DH MAY 80
CHECK
DI MAY 80
CHECK
DJ MAY 80
CHECK
DK MAY 80
CHECK
DL MAY 80
CHECK
DM MAY 80
CHECK
DN MAY 80
CHECK
DO MAY 80
CHECK
DP MAY 80
CHECK
DQ MAY 80
CHECK
DR MAY 80
CHECK
DS MAY 80
CHECK
DT MAY 80
CHECK
DU MAY 80
CHECK
DV MAY 80
CHECK
DW MAY 80
CHECK
DX MAY 80
CHECK
DY MAY 80
CHECK
DZ MAY 80
CHECK
EA MAY 80
CHECK
EB MAY 80
CHECK
EC MAY 80
CHECK
ED MAY 80
CHECK
EE MAY 80
CHECK
EF MAY 80
CHECK
EG MAY 80
CHECK
EH MAY 80
CHECK
EI MAY 80
CHECK
EJ MAY 80
CHECK
EK MAY 80
CHECK
EL MAY 80
CHECK
EM MAY 80
CHECK
EN MAY 80
CHECK
EO MAY 80
CHECK
EP MAY 80
CHECK
EQ MAY 80
CHECK
ER MAY 80
CHECK
ES MAY 80
CHECK
ET MAY 80
CHECK
EU MAY 80
CHECK
EV MAY 80
CHECK
EW MAY 80
CHECK
EX MAY 80
CHECK
EY MAY 80
CHECK
EZ MAY 80
CHECK
FA MAY 80
CHECK
FB MAY 80
CHECK
FC MAY 80
CHECK
FD MAY 80
CHECK
FE MAY 80
CHECK
FF MAY 80
CHECK
FG MAY 80
CHECK
FH MAY 80
CHECK
FI MAY 80
CHECK
FJ MAY 80
CHECK
FK MAY 80
CHECK
FL MAY 80
CHECK
FM MAY 80
CHECK
FN MAY 80
CHECK
FO MAY 80
CHECK
FP MAY 80
CHECK
FQ MAY 80
CHECK
FR MAY 80
CHECK
FS MAY 80
CHECK
FT MAY 80
CHECK
FU MAY 80
CHECK
FV MAY 80
CHECK
FW MAY 80
CHECK
FX MAY 80
CHECK
FY MAY 80
CHECK
FZ MAY 80
CHECK
GA MAY 80
CHECK
GB MAY 80
CHECK
GC MAY 80
CHECK
GD MAY 80
CHECK
GE MAY 80
CHECK
GF MAY 80
CHECK
GG MAY 80
CHECK
GH MAY 80
CHECK
GI MAY 80
CHECK
GJ MAY 80
CHECK
GK MAY 80
CHECK
GL MAY 80
CHECK
GM MAY 80
CHECK
GN MAY 80
CHECK
GO MAY 80
CHECK
GP MAY 80
CHECK
GQ MAY 80
CHECK
GR MAY 80
CHECK
GS MAY 80
CHECK
GT MAY 80
CHECK
GU MAY 80
CHECK
GV MAY 80
CHECK
GW MAY 80
CHECK
GX MAY 80
CHECK
GY MAY 80
CHECK
GZ MAY 80
CHECK
HA MAY 80
CHECK
HB MAY 80
CHECK
HC MAY 80
CHECK
HD MAY 80
CHECK
HE MAY 80
CHECK
HF MAY 80
CHECK
HG MAY 80
CHECK
HH MAY 80
CHECK
HI MAY 80
CHECK
HJ MAY 80
CHECK
HK MAY 80
CHECK
HL MAY 80
CHECK
HM MAY 80
CHECK
HN MAY 80
CHECK
HO MAY 80
CHECK
HP MAY 80
CHECK
HQ MAY 80
CHECK
HR MAY 80
CHECK
HS MAY 80
CHECK
HT MAY 80
CHECK
HU MAY 80
CHECK
HV MAY 80
CHECK
HW MAY 80
CHECK
HX MAY 80
CHECK
HY MAY 80
CHECK
HZ MAY 80
CHECK
IA MAY 80
CHECK
IB MAY 80
CHECK
IC MAY 80
CHECK
ID MAY 80
CHECK
IE MAY 80
CHECK
IF MAY 80
CHECK
IG MAY 80
CHECK
IH MAY 80
CHECK
II MAY 80
CHECK
IJ MAY 80
CHECK
IK MAY 80
CHECK
IL MAY 80
CHECK
IM MAY 80
CHECK
IN MAY 80
CHECK
IO MAY 80
CHECK
IP MAY 80
CHECK
IQ MAY 80
CHECK
IR MAY 80
CHECK
IS MAY 80
CHECK
IT MAY 80
CHECK
IU MAY 80
CHECK
IV MAY 80
CHECK
IW MAY 80
CHECK
IX MAY 80
CHECK
IY MAY 80
CHECK
IZ MAY 80
CHECK
JA MAY 80
CHECK
JB MAY 80
CHECK
JC MAY 80
CHECK
JD MAY 80
CHECK
JE MAY 80
CHECK
JF MAY 80
CHECK
JG MAY 80
CHECK
JH MAY 80
CHECK
JI MAY 80
CHECK
JJ MAY 80
CHECK
JK MAY 80
CHECK
JL MAY 80
CHECK
JM MAY 80
CHECK
JN MAY 80
CHECK
JO MAY 80
CHECK
JP MAY 80
CHECK
JQ MAY 80
CHECK
JR MAY 80
CHECK
JS MAY 80
CHECK
JT MAY 80
CHECK
JU MAY 80
CHECK
JV MAY 80
CHECK
JW MAY 80
CHECK
JX MAY 80
CHECK
JY MAY 80
CHECK
JZ MAY 80
CHECK
KA MAY 80
CHECK
KB MAY 80
CHECK
KC MAY 80
CHECK
KD MAY 80
CHECK
KE MAY 80
CHECK
KF MAY 80
CHECK
KG MAY 80
CHECK
KH MAY 80
CHECK
KI MAY 80
CHECK
KJ MAY 80
CHECK
KK MAY 80
CHECK
KL MAY 80
CHECK
KM MAY 80
CHECK
KN MAY 80
CHECK
KO MAY 80
CHECK
KP MAY 80
CHECK
KQ MAY 80
CHECK
KR MAY 80
CHECK
KS MAY 80
CHECK
KT MAY 80
CHECK
KU MAY 80
CHECK
KV MAY 80
CHECK
KW MAY 80
CHECK
KX MAY 80
CHECK
KY MAY 80
CHECK
KZ MAY 80
CHECK
LA MAY 80
CHECK
LB MAY 80
CHECK
LC MAY 80
CHECK
LD MAY 80
CHECK
LE MAY 80
CHECK
LF MAY 80
CHECK
LG MAY 80
CHECK
LH MAY 80
CHECK
LI MAY 80
CHECK
LJ MAY 80
CHECK
LK MAY 80
CHECK
LL MAY 80
CHECK
LM MAY 80
CHECK
LN MAY 80
CHECK
LO MAY 80
CHECK
LP MAY 80
CHECK
LQ MAY 80
CHECK
LR MAY 80
CHECK
LS MAY 80
CHECK
LT MAY 80
CHECK
LU MAY 80
CHECK
LV MAY 80
CHECK
LW MAY 80
CHECK
LX MAY 80
CHECK
LY MAY 80
CHECK
LZ MAY 80
CHECK
MA MAY 80
CHECK
MB MAY 80
CHECK
MC MAY 80
CHECK
MD MAY 80
CHECK
ME MAY 80
CHECK
MF MAY 80
CHECK
MG MAY 80
CHECK
MH MAY 80
CHECK
MI MAY 80
CHECK
MJ MAY 80
CHECK
MK MAY 80
CHECK
ML MAY 80
CHECK
MN MAY 80
CHECK
MO MAY 80
CHECK
MP MAY 80
CHECK
MQ MAY 80
CHECK
MR MAY 80
CHECK
MS MAY 80
CHECK
MT MAY 80
CHECK
MU MAY 80
CHECK
MV MAY 80
CHECK
MW MAY 80
CHECK
MX MAY 80
CHECK
MY MAY 80
CHECK
MZ MAY 80
CHECK
NA MAY 80
CHECK
NB MAY 80
CHECK
NC MAY 80
CHECK
ND MAY 80
CHECK
NE MAY 80
CHECK
NF MAY 80
CHECK
NG MAY 80
CHECK
NH MAY 80
CHECK
NI MAY 80
CHECK
NJ MAY 80
CHECK
NK MAY 80
CHECK
NL MAY 80
CHECK
NM MAY 80
CHECK
NO MAY 80
CHECK
NP MAY 80
CHECK
NQ MAY 80
CHECK
NR MAY 80
CHECK
NS MAY 80
CHECK
NT MAY 80
CHECK
NU MAY 80
CHECK
NV MAY 80
CHECK
NW MAY 80
CHECK
NX MAY 80
CHECK
NY MAY 80
CHECK
NZ MAY 80
CHECK
OA MAY 80
CHECK
OB MAY 80
CHECK
OC MAY 80
CHECK
OD MAY 80
CHECK
OE MAY 80
CHECK
OF MAY 80
CHECK
OG MAY 80
CHECK
OH MAY 80
CHECK
OI MAY 80
CHECK
OJ MAY 80
CHECK
OK MAY 80
CHECK
OL MAY 80
CHECK
OM MAY 80
CHECK
ON MAY 80
CHECK
OO MAY 80
CHECK
OP MAY 80
CHECK
OQ MAY 80
CHECK
OR MAY 80
CHECK
OS MAY 80
CHECK
OT MAY 80
CHECK
OU MAY 80
CHECK
OV MAY 80
CHECK
OW MAY 80
CHECK
OX MAY 80
CHECK
OY MAY 80
CHECK
OZ MAY 80
CHECK
PA MAY 80
CHECK
PB MAY 80
CHECK
PC MAY 80
CHECK
PD MAY 80
CHECK
PE MAY 80
CHECK
PF MAY 80
CHECK
PG MAY 80
CHECK
PH MAY 80
CHECK
PI MAY 80
CHECK
PJ MAY 80
CHECK
PK MAY 80
CHECK
PL MAY 80
CHECK
PM MAY 80
CHECK
PN MAY 80
CHECK
PO MAY 80
CHECK
PP MAY 80
CHECK
PQ MAY 80
CHECK
PR MAY 80
CHECK
PS MAY 80
CHECK
PT MAY 80
CHECK
PU MAY 80
CHECK
PV MAY 80
CHECK
PW MAY 80
CHECK
PX MAY 80
CHECK
PY MAY 80
CHECK
PZ MAY 80
CHECK
QA MAY 80
CHECK
QB MAY 80
CHECK
QC MAY 80
CHECK
QD MAY 80
CHECK
QE MAY 80
CHECK
QF MAY 80
CHECK
QG MAY 80
CHECK
QH MAY 80
CHECK
QI MAY 80
CHECK
QJ MAY 80
CHECK
QK MAY 80
CHECK
QL MAY 80
CHECK
QM MAY 80
CHECK
QN MAY 80
CHECK
QO MAY 80
CHECK
QP MAY 80
CHECK
QQ MAY 80
CHECK
QR MAY 80
CHECK
QS MAY 80
CHECK
QT MAY 80
CHECK
QU MAY 80
CHECK
QV MAY 80
CHECK
QW MAY 80
CHECK
QX MAY 80
CHECK
QY MAY 80
CHECK
QZ MAY 80
CHECK
RA MAY 80
CHECK
RB MAY 80
CHECK
RC MAY 80
CHECK
RD MAY 80
CHECK
RE MAY 80
CHECK
RF MAY 80
CHECK
RG MAY 80
CHECK
RH MAY 80
CHECK
RI MAY 80
CHECK
RJ MAY 80
CHECK
RK MAY 80
CHECK
RL MAY 80
CHECK
RM MAY 80
CHECK
RN MAY 80
CHECK
RO MAY 80
CHECK
RP MAY 80
CHECK
RQ MAY 80
CHECK
RR MAY 80
CHECK
RS MAY 80
CHECK
RT MAY 80
CHECK
RU MAY 80
CHECK
RV MAY 80
CHECK
RW MAY 80
CHECK
RX MAY 80
CHECK
RY MAY 80
CHECK
RZ MAY 80
CHECK
SA MAY 80
CHECK
SB MAY 80
CHECK
SC MAY 80
CHECK
SD MAY 80
CHECK
SE MAY 80
CHECK
SF MAY 80
CHECK
SG MAY 80
CHECK
SH MAY 80
CHECK
SI MAY 80
CHECK
SJ MAY 80
CHECK
SK MAY 80
CHECK
SL MAY 80
CHECK
SM MAY 80
CHECK
SN MAY 80
CHECK
SO MAY 80
CHECK
SP MAY 80
CHECK
SQ MAY 80
CHECK
SR MAY 80
CHECK
SS MAY 80
CHECK
ST MAY 80
CHECK
SU MAY 80
CHECK
SV MAY 80
CHECK
SW MAY 80
CHECK
SX MAY 80
CHECK
SY MAY 80
CHECK
SZ MAY 80
CHECK
TA MAY 80
CHECK
TB MAY 80
CHECK
TC MAY 80
CHECK
TD MAY 80
CHECK
TE MAY 80
CHECK
TF MAY 80
CHECK
TG MAY 80
CHECK
TH MAY 80
CHECK
TI MAY 80
CHECK
TJ MAY 80
CHECK
TK MAY 80
CHECK
TL MAY 80
CHECK
TM MAY 80
CHECK
TN MAY 80
CHECK
TO MAY 80
CHECK
TP MAY 80
CHECK
TQ MAY 80
CHECK
TR MAY 80
CHECK
TS MAY 80
CHECK
TT MAY 80
CHECK
TU MAY 80
CHECK
TV MAY 80
CHECK
TW MAY 80
CHECK
TX MAY 80
CHECK
TY MAY 80
CHECK
TZ MAY 80
CHECK
UA MAY 80
CHECK
UB MAY 80
CHECK
UC MAY 80
CHECK
UD MAY 80
CHECK
UE MAY 80
CHECK
UF MAY 80
CHECK
UG MAY 80
CHECK
UH MAY 80
CHECK
UI MAY 80
CHECK
UJ MAY 80
CHECK
UK MAY 80
CHECK
UL MAY 80
CHECK
UM MAY 80
CHECK
UN MAY 80
CHECK
UO MAY 80
CHECK
UP MAY 80
CHECK
UQ MAY 80
CHECK
UR MAY 80
CHECK
US MAY 80
CHECK
UT MAY 80
CHECK
UU MAY 80
CHECK
UV MAY 80
CHECK
UW MAY 80
CHECK
UX MAY 80
CHECK
UY MAY 80
CHECK
UZ MAY 80
CHECK
VA MAY 80
CHECK
VB MAY 80
CHECK
VC MAY 80
CHECK
VD MAY 80
CHECK
VE MAY 80
CHECK
VF MAY 80
CHECK
VG MAY 80
CHECK
VH MAY 80
CHECK
VI MAY 80
CHECK
VJ MAY 80
CHECK
VK MAY 80
CHECK
VL MAY 80
CHECK
VM MAY 80
CHECK
VN MAY 80
CHECK
VO MAY 80
CHECK
VP MAY 80
CHECK
VQ MAY 80
CHECK
VR MAY 80
CHECK
VS MAY 80
CHECK
VT MAY 80
CHECK
VU MAY 80
CHECK
VV MAY 80
CHECK
VW MAY 80
CHECK
VX MAY 80
CHECK
VY MAY 80
CHECK
VZ MAY 80
CHECK
WA MAY 80
CHECK
WB MAY 80
CHECK
WC MAY 80
CHECK
WD MAY 80
CHECK
WE MAY 80
CHECK
WF MAY 80
CHECK
WG MAY 80
CHECK
WH MAY 80
CHECK
WI MAY 80
CHECK
WJ MAY 80
CHECK
WK MAY 80
CHECK
WL MAY 80
CHECK
WM MAY 80
CHECK
WN MAY 80
CHECK
WO MAY 80
CHECK
WP MAY 80
CHECK
WQ MAY 80
CHECK
WR MAY 80
CHECK
WS MAY 80
CHECK
WT MAY 80
CHECK
WU MAY 80
CHECK
WV MAY 80
CHECK
WW MAY 80
CHECK
WX MAY 80
CHECK
WY MAY 80
CHECK
WZ MAY 80
CHECK
XA MAY 80
CHECK
XB MAY 80
CHECK
XC MAY 80
CHECK
XD MAY 80
CHECK
XE MAY 80
CHECK
XF MAY 80
CHECK
XG MAY 80
CHECK
XH MAY 80
CHECK
XI MAY 80
CHECK
XJ MAY 80
CHECK
XK MAY 80
CHECK
XL MAY 80
CHECK
XM MAY 80
CHECK
XN MAY 80
CHECK
XO MAY 80
CHECK
XP MAY 80
CHECK
XQ MAY 80
CHECK
XR MAY 80
CHECK
XS MAY 80
CHECK
XT MAY 80
CHECK
XU MAY 80
CHECK
XV MAY 80
CHECK
XW MAY 80
CHECK
XX MAY 80
CHECK
XY MAY 80
CHECK
XZ MAY 80
CHECK
YA MAY 80
CHECK
YB MAY 80
CHECK
YC MAY 80
CHECK
YD MAY 80
CHECK
YE MAY 80
CHECK
YF MAY 80
CHECK
YG MAY 80
CHECK
YH MAY 80
CHECK
YI MAY 80
CHECK
YJ MAY 80
CHECK
YK MAY 80
CHECK
YL MAY 80
CHECK
YM MAY 80
CHECK
YN MAY 80
CHECK
YO MAY 80
CHECK
YP MAY 80
CHECK
YQ MAY 80
CHECK
YR MAY 80
CHECK
YS MAY 80
CHECK
YT MAY 80
CHECK
YU MAY 80
CHECK
YV MAY 80
CHECK
YW MAY 80
CHECK
YX MAY 80
CHECK
YY MAY 80
CHECK
YZ MAY 80
CHECK
ZA MAY 80
CHECK
ZB MAY 80
CHECK
ZC MAY 80
CHECK
ZD MAY 80
CHECK
ZE MAY 80
CHECK
ZF MAY 80
CHECK
ZG MAY 80
CHECK
ZH MAY 80
CHECK
ZI MAY 80
CHECK
ZJ MAY 80
CHECK
ZK MAY 80
CHECK
ZL MAY 80
CHECK
ZM MAY 80
CHECK
ZN MAY 80
CHECK
ZO MAY 80
CHECK
ZP MAY 80
CHECK
ZQ MAY 80
CHECK
ZR MAY 80
CHECK
ZS MAY 80
CHECK
ZT MAY 80
CHECK
ZU MAY 80
CHECK
ZV MAY 80
CHECK
ZW MAY 80
CHECK
ZX MAY 80
CHECK
ZY MAY 80
CHECK
ZZ MAY 80
CHECK

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



SCALE FULL		
DO NOT SCALE PRINT		
TOLERANCES		
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE 2		
NO PLACES	DIM. mm	TOL. mm/in
ONE PLACE	X, X	1/64
TWO PLACES	X, XX	0.001
THREE PLACES	X, XXX	0.0001
ANGLES		
	SI METRIC	US CUSTOMARY
DESIGN UNITS	<input type="checkbox"/>	<input checked="" type="checkbox"/>
RAW MATERIAL - COMMERCIAL STANDARD MICRO SWITCH STANDARDS APPLY		
DIMENSIONS ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED		
WEIGHT .15 LB MAX		

CHARACTERISTICS	ELECTRICAL DATA		
OPERATING FORCE----- 6-12 LB	CONTACT ARRANGEMENT		
FULL OVERTRAVEL FORCE-----30 LB MAX	SPDT (2)		
RELEASE FORCE----- 4 LB MIN	LOAD	28 VDC SEA LEVEL	28 VDC 50,000 FT.
PRETRAVEL----- .040 MAX	RES	7	7
DIFFERENTIAL TRAVEL----- .020 MAX	IND	4	2.5
OVERTRAVEL----- .210 MIN	MOTOR	4	
	LAMP		