

Superbright LED Retrofit Lamp Dimmable



Features:

- 15W LED lamp designed as high quality replacement of 85W halogen PAR38 lamps
- Dimmable 20-100%
- 25,000 hours rated life
- Suitable for indoor environments
- Available in 2,700K and 3,000K CCT with 80CRI
- Power factor 0.95
- Reduces energy consumption up to 80%
- Lasts 33 times longer than halogen lamps
- Mercury free
- UV and IR free
- UL File No. : E356190

Specifications:

Lamp Base Type	: Edison Screw / E26
Power Rating	: 15W
Supply Voltage	: 120V
Average Bulb Life	: 25,000h
Power Factor	: 0.95

Application Information

Where does it used

- Art galleries and Museums
- Residential
- Shopping Mall
- Hotels
- Corridors
- Offices
- Meeting Rooms

Applications

- Display Lighting
- Recessed Downlighting
- Tracking Lighting
- Landscape Lighting

Notes


- Operating temperature range between -20°C and +50°C
- Suitable for dimmers or in luminaires controlled by a dimmer
- Not intended for use with emergency light fixtures
- Not for use where exposed to weather
- Not for use in totally enclosed and insulated fixtures

Superbright LED Retrofit Lamp


Dimmable



Light Spot




Beam angle : 25°




Beam angle : 40°

Illumination Intensity Chart (CREE XPE)

Luminous Intensity Distribution Curve



Illuminance at a Distance



All data above are based on CCT 3,000K,15°




Superbright LED Retrofit Lamp

Dimmable



Dimension



Size : Ø122 × H137mm

Part Number Table

Description	LED Colour	CCT	Beam Angle	Typical Lumens (lm)	CRI	Part Number
LED Lamp, E26, 120V	Warm White	3,000K	25°	1,100	80	PAR38-LED120V15W25-3000DIM
	Cool White	6,000K		1,250	70	PAR38-LEDE26120V15W25-6000DIM
	Warm White	3,000K	40°	1,100	80	PAR38-LEDE26120V15W40-3000DIM
	Cool White	6,000K		1,250	70	PAR38-LEDE26120V15W40-6000DIM

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com
 www.farnell.com
 www.newark.com

