MATERIALS & TEMPERATURES

Code	Material	Min	Max
GF	Glass-Filled Nylon	-40°C	+110°C
N	Nylon	-40°C	+80°C
D	Polyester	-40°C	+160°C
P	Polypropylene	-20°C	+80°C
PPS	Polyphenylene Sulphide	-40°C	+220°C

DISCLAIMER: These figures are to be used as GUIDELINES ONLY. Different figures may apply depending upon the application. Samples are readily available for testing to ascertain suitability.