


PHYSICAL DIMENSIONS:

A	3.20 [.126]	+ 0.20 [.008]
B	1.60 [.063]	+ 0.20 [.008]
C	0.80 [.031]	+ 0.20 [.008]
D	0.40 [.016]	+ 0.15 [.006]
D1	0.30 [.012]	+ 0.20 [.008]
E	0.80 [.031]	+ 0.10 [.004]

DA1206B601R-10

UNCONTROLLED DOCUMENT





ELECTRICAL CHARACTERISTICS:

Z @ 100MHz (Ω)	DCR (Ω)	Rated Current
Nominal	600	
Minimum	450	
Maximum	750	200 mA


LINE TO LINE INSULATION RESISTANCE
>100 M Ω AT 75 VOLTS.

NOTES: UNLESS OTHERWISE SPECIFIED

1. TAPED AND REELED per CURRENT EIA SPECIFICATIONS 7" REELS, 3000 PCS/REEL EMBOSSED PLASTIC TAPE.
2. TERMINATION FINISH IS 100% TIN.
3. COMPONENTS SHOULD BE ADEQUATELY PREHEATED BEFORE SOLDERING.




LAND PATTERNS FOR REFLOW SOLDERING



(For wave soldering, add 0.762 (0.030) to this dimension)

RECOMMENDED SOLDERING CONDITIONS



DIMENSIONS ARE IN mm [INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
D	UPDATE COMPANY LOGO	05/20/09	JRK	PROJECT/PART NUMBER:	DA1206B601R-10	REV	D
C	D1 dim chgd from 0.008 ± 0.004 to 0.012 ± 0.008. UPDATE COMPANY LOGO	10/30/07	JRK	PART TYPE:	CO-FIRE	SCALE:	NTS
B	CHANGE DCR, MODIFY NOTE 1 ADD ROHS	11/30/06	JRK	DATE:	03/30/04	SHEET:	2 of 2
A	ORIGINAL DRAFT	03/30/04	TMB	CAD #	DA1206B601R-10-D	TOOL #	-
REV	DESCRIPTION	DATE	INT				