


CORE DIMENSIONS:

A	12.00 [.472]	+	0.33 [.013]
B	7.00 [.276]	+	0.13 [.005]
C	15.00 [.591]	+	0.25 [.010]
D	5.54 [.218]	+	0.20 [.008]
E	4.62 [.182]	+	0.30 [.012]

Weight/1000 5.11 kgs 11.26 lbs.
(Per Pair)



CASE DIMENSIONS:


A	15.00 [.591]	+	0.30 [.012]
B	7.00 [.276]	+	0.20 [.008]
C	18.00 [.709]	+	0.30 [.012]
C1	22.00 [.866]	+	0.38 [.015]
D	15.00 [.591]	+	0.38 [.015]

**UNCONTROLLED
DOCUMENT**

IMPEDANCE (Z)

Frequency	25 MHz	100 MHz	300 MHz
Nominal (REF)	56 Ω	123 Ω	246 Ω
Minimum	- Ω	98 Ω	- Ω

Z vs. FREQUENCY
(REF. ONLY)



FREQUENCY (MHz)

AGILENT E4991A Impedance/Material Analyzer
HP 16092A-Test Fixture

NOTES:

- CASE FLAMMABILITY RATING: UL94 V-0
- CASE MATERIAL: HALOGEN FREE NYLON
- ASSEMBLED PART #: 28A1507-0A2
- CORE PART #: 28A1507-000
- CASE COLOR: BLACK -"0A2"

DIMENSIONS ARE IN mm [INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved. Laird TECHNOLOGIES®				
						PROJECT/PART NUMBER:		REV
				28A1507-0A2		A	FERRITE SNAP-ON	TMB
				DATE:		SCALE:	MATERIAL:	
				10/21/08		NTS	NiZn Ferrite	
				CAD #		TOOL #		
				28A1507-0A2-A		—		
A	ORIGINAL DRAFT	10/21/08	TMB					
REV	DESCRIPTION	DATE	INT					