

QUINT-BAT/24DC/12AH


Order No.: 2866365



<http://eshop.phoenixcontact.co.uk/phoenix/treeViewClick.do?UID=2866365>

Rechargeable battery module, lead AGM, VRLA technology, 24 V DC, 12 Ah. Connection via male cable lug, 14 mm.



Commercial data	
EAN	 4 017918 959760
Pack	1
Customs tariff	85072098
Country of Origin	CN
Catalog page information	Page 591 (IF-2009)

Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

Technical data	
Input data	
Nominal input voltage	24 V DC
Output data	
Nominal output voltage	24 V DC
Output current	max. 50 A
Connection in parallel	Yes, for increasing the buffer period
Connection in series	No
Output fuse	2x 25 A

General data

Disposal	Used batteries must not be thrown away with household waste, they should instead be disposed of in accordance with applicable national regulations. They can also be returned to Phoenix Contact or the manufacturer.
Width	231 mm
Height	156 mm
Depth	110 mm
Net weight	9 kg
Memory medium	battery 12 Ah
Degree of protection	IP20
Protection class	III
Ambient temperature (operation)	0 °C ... 40 °C
Ambient temperature (storage/transport)	0 °C ... 40 °C
Shipbuilding approval	Germanischer Lloyd (EMC 2), ABS

Certificates



Certification GL

Accessories


Item	Designation	Description
Fuse		
0913757	SI FORM C 25 A DIN 72581	Flat-type plug-in fuse, type C, color code: white, nominal current: 25 A

General

2866857	QUINT-ADAPTER/4	Assembly adapter for QUINT-BAT/24DC... on 35mm rail
---------	-----------------	---

Drawings

Block diagram



Address

PHOENIX CONTACT Ltd
Halesfield 13
Telford / Shropshire / TF7 4PG,England
Phone 01952 681 700
Fax 01952 681 799
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.
Technical modifications reserved;