Permatex Europe Unit 3, Express Park, Shipton Way, Northampton Road, Rushden, Northamptonshire NN10 6GK UK

Ph: 0870 4589545

SAFETY DATA SHEET according to REACH regulation 1907/2006

1. IDENTIFICATION OF THE PREPARATION

Identification of the **ULTRA BLACK GASKET MAKER 3.350Z**

preparation:

Item No: 82180

Recommended use: Silicone elastomer

2. HAZARDS IDENTIFICATION

Xn - Harmful Classification:

Most Important Hazards: Suspect cancer hazard - risk of cancer depends on duration and level of

> exposure. May cause allergic skin reaction. When this product is exposed to moisture, butanone oxime may be formed. When produced during curing, may cause irritation to eyes, nose and throat. Overexposure may cause eye

and skin redness. Harmful to aquatic organisms, may cause long-term

adverse effects in the aquatic environment.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	Weight%	EC Number	EU Classification
POLY (DIMETHYLSILOXANE), HYDROXY TERMINATED 70131-67-8	20-40	Not determined	None
CALCIUM CARBONATE 471-34-1	20-30	207-439-9	None
LIMESTONE 1317-65-3	15-25	215-279-6	None
SYNTHETIC ISOPARAFFINIC HYDROCARON 64742-47-8	<7	265-149-8	F:R10, Xn:R65, Xi:R38, N:R51/53
VINYL OXIMINOSILANE 2224-33-1	<5	218-747-8	None
STEARIC ACID 57-11-4	<2	200-313-4	None
2-BUTANONE OXIME 96-29-7	0.5-2.0	202-496-6	Carc.3:R40 Xn:R21 Xi:R41,43

4. FIRST-AID MEASURES

General advice: If you feel unwell, seek medical advice (show the label where possible). Inhalation:

Move to fresh air in case of accidental inhalation of vapours. If symptoms

persist, call a physician.

Wipe off material with paper towel or cloth. Wash off with soap and water. If **Skin Contact:**

skin irritation persists, call a physician.

Eye Contact: In the case of contact with eyes, rinse immediately with plenty of water and

seek medical advice.

Product Name: ULTRA BLACK GASKET MAKER <u>Item No:</u> 82180

3.35OZ

4. FIRST-AID MEASURES

Ingestion: Rinse mouth. If swallowed, seek medical advice immediately and show this

container or label.

Protection of first-aiders: Use personal protective equipment. Avoid contact with skin, eyes and

clothing.

Notes to Physician: Treatment should be directed at preventing absorption, administering to

symptoms (if they occur), and providing supportive therapy

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media: Carbon dioxide (CO2), Dry chemical, foam

Extinguishing media which must not be used for safety

None reasonably foreseeable.

reasons:

Special instructions for Thermal decomposition can lead to release of irritating gases and vapours.

protection and hygiene:

Special protective equipment Use personal protective equipment. Avoid contact with eyes.

for firefighters:

6. ACCIDENTAL RELEASE MEASURES

Personal Precautions: For additional information on processing see sections 7, 8 and 11 of this

safety data sheet.

Environmental Precautions: Do not flush into surface water or sanitary sewer system.

Cleanup: Scrape up. Absorb spill with inert material (e.g. dry sand or earth), then place

in a chemical waste container. Slippery, can cause falls if walked on.

7. HANDLING AND STORAGE

Handling precautions: Avoid breathing vapors or mists. Avoid contact with the skin and the eyes.

Wash hands before breaks and immediately after handling the product.

Storage: Store in cool place. Keep containers dry and tightly closed to avoid moisture

absorption and contamination.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Component	ACGIH; TLV-TWA	German MAK; TWA	UK WEL; TWA	Finnish OEL; HTP
POLY (DIMETHYLSILOXANE), HYDROXY TERMINATED 70131-67-8	Not listed	Not listed	Not listed	Not listed
CALCIUM CARBONATE 471-34-1	10 mg/m ³	Not listed	Not listed	Not listed
LIMESTONE 1317-65-3	Not listed	Not listed	10 mg/m ³	Not listed
SYNTHETIC ISOPARAFFINIC HYDROCARON 64742-47-8	Not listed	Not listed	Not listed	Not listed
VINYL OXIMINOSILANE 2224-33-1	Not listed	Not listed	Not listed	Not listed
STEARIC ACID 57-11-4	Not listed	Not listed	Not listed	Not listed
2-BUTANONE OXIME 96-29-7	Not listed	Not listed	Not listed	Not listed

Ventilation: Provide adequate ventilation .

Respiratory Protection: In case of insufficient ventilation, wear suitable respiratory equipment.

Product Name: ULTRA BLACK GASKET MAKER Item No: 82180

3.35OZ

Skin: Neoprene or nitrile gloves recommended.

Eyes: Safety glasses

Hygiene Measures: When using, do not eat, drink or smoke.

9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance: Black paste

Odor: Mild

pH: Does not apply

Boiling point/range: Not applicable polymerization

Melting point: Not determined **Flash point:** >95°C (200°F).

Risk of explosion: None reasonably foreseeable.

Vapor pressure: <5 mm Hg Density: 1.44

Solubility in water: polymerization
Partition coefficient (n- Not determined

octanol/water):

Vapor density: >1 (Air = 1)
Evaporation Rate: Not determined

VOC Content(%): <4%

10. STABILITY/REACTIVITY

Stability: Stable under normal conditions.

Conditions to Avoid: Exposure to moisture.

Materials to avoid: Polymerization can occur, Strong oxidizing agents, Water, Acids

Hazardous decomposition Ethyl methyl ketone, methyl ethyl ketoxime

products: , formaldehyde, nitrogen oxides (NOx), Carbon oxides

11. TOXICOLOGICAL INFORMATION

Component	Weight%	LD50/oral/rat	LC50/inhalation/rat
POLY (DIMETHYLSILOXANE), HYDROXY TERMINATED 70131-67-8	20-40	>40,000 mg/kg	>535 mg/l
CALCIUM CARBONATE 471-34-1	20-30	6450 mg/kg	
LIMESTONE 1317-65-3	15-25	>5000 mg/kg	
SYNTHETIC ISOPARAFFINIC HYDROCARON 64742-47-8	<7	>5000 mg/kg	>5.2 mg/L/4H
2-BUTANONE OXIME 96-29-7	0.5-2.0	930 mg/kg	20 mg/L/4H

Local Effects

Skin Irritation: May cause skin irritation and/or dermatitis. May cause allergic skin reaction.

Eye Irritation: Irritating, but will not permanently injure eye tissue

Inhalation: May cause irritation of the mucous membranes. Exposure to decomposition

products may be a hazard to health.

Ingestion: Irritating to mouth, throat and stomach.

Sensitization: May cause sensitization of susceptible persons by skin contact.

Chronic toxicity: None reasonably foreseeable

Specific Effects

Carcinogenic effects: May form formaldehyde at high temperatures.

Mutagenic effects: None reasonably foreseeable.

Reproductive toxicity: None reasonably foreseeable

Target Organ Effects: Eyes, Skin, Respiratory System, Gastrointestinal Tract

Product Name: ULTRA BLACK GASKET MAKER <u>Item No:</u> 82180

3.35OZ

12. ECOLOGICAL INFORMATION

Ecotoxicity: Harmful to aquatic organisms, may cause long-term adverse effects in the

aquatic environment.

13. DISPOSAL CONSIDERATIONS

Waste from Residues: According to the European Waste Catalogue, Waste Codes are not product

specific, but application specific. Waste codes should be assigned by the

user based on the application for which the product was used.

RoHS/WEEE: This product is in compliance with EU Directive 2002/95/EC Restriction of the

Use of Certain Hazardous Substances in Electrical and Electronic Equipment (RoHS) and EU Directive 2002/96/EC Restriction on waste electrical and

electronic equipment (WEEE).

14. TRANSPORT INFORMATION

IATA

Proper Shipping Name: Not regulated Not applicable UN/ID No: Not applicable

IMDG

Proper shipping name: Not regulated Not applicable UN/ID No: Not applicable

Marine Pollutant: None

ADR/RID

Proper Shipping Name: Not regulated Hazard Class: Not applicable

UN/ID No: None

15. REGULATORY INFORMATION

This product is classified in accordance with Annex VI to Directive 67/548/EEC

Indication of Danger:

Xn - Harmful

Names of the ingredients given on the warning label:

2-butanone oxime

R -phrase(s):

R40 - Limited evidence of a carcinogenic effect

R43 - May cause sensitization by skin contact

R52/53 - Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment

S -phrase(s):

S 2 - Keep out of the reach of children

S24/25 - Avoid contact with skin and eyes

S36/37 - Wear suitable protective clothing and gloves

S61 - Avoid release to the environment. Refer to special instructions/safety data sheets

Product Name: ULTRA BLACK GASKET MAKER <u>Item No:</u> 82180

3.35OZ

16. OTHER INFORMATION

Risk Phrases mentioned in Section 2:

R10 - Flammable.

R21 -Harmful in contact with skin.

R38 - Irritating to skin.

R40 - Limited evidence of a carcinogenic effect

R41 - Risk of serious damage to eyes.

R43 - May cause sensitization by skin contact.

R65 - Harmful: may cause lung damage if swallowed.

R51/53 - Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment

Prepared By: Denise Boyd, Manager- Revision Date: March 24, 2009

Environmental, Health & Safety

Company: Permatex. Inc. 10 Columbus Revision Number: 2

Blvd. Hartford, CT USA 06106

Telephone: 877-376-2839