



#### Features:

- For Surface Mounted Applications
- Low Profile Package
- Built-In Strain Relief
- Metal Silicon Junction, Majority Carrier Conduction
- High Surge Capability
- Low Power Loss, High Efficiency
- For Use in Low Voltage High Frequency Inverters, Free Wheeling and Polarity Protection Applications
- Guardring for Over Voltage Protection
- High Temperature Soldering Guaranteed: 250°C/10 Seconds at Terminals

#### **Mechanical Data**

- Case: JEDEC DO-214AC, Molded Plastic over Passivated Chip
- Terminals: Solder Plated, Solderable per MIL-STD-750, Method 2026
- Polarity: Colour Band Denotes Cathode End
- Weight: 0.002oz, 0.064g

#### **Maximum Ratings and Thermal Characteristics**

Ratings at 25°C ambient temperature unless otherwise specified

Characteristic		B340A-13-F	B360A-13-F	Units
Maximum repetitive peak reverse voltage	VRRM	40	60	V
Maximum RMS voltage	VRWS	28	42	V
Maximum DC blocking voltage	V DC	40	60	V
Maximum average forward rectified current at T∟ See Fig. 1. (Note 2)	lf(AV)	3		Α
Peak forward surge current 8.3ms single half-sine-wave	İFSM	100		А
Maximum instantaneous forward voltage at 3A (Note 1)	VF	0.5	0.7	V
Maximum DC reverse current T <sub>A</sub> =25°C at rated DC blocking voltage T <sub>A</sub> =100°C (Note 1)	lr	0.5 20		mA
Typical thermal resistance (Note 2)	Røja Røjl	_	0 0	°C/W
Operating junction and storage temperature range	TJ, TSTG	-65 to	+125	°C

- (1) Pulse test: 300µS pulse width,1% duty cycle.
- (2) PCB mounted with 0.55" × 0.55" (14 × 14mm<sup>2</sup>) copper pad areas.

www.element14.com www.farnell.com www.newark.com






#### FIG.1 - FORWARD DERATING CURVE

### AVERAGE FORWARD RECTIFIED B320A-B340A Resistive or **CURRENT, AMPERES** AMBIENT TEMPERATURE °C

#### FIG.2- PEAK FORWARD SURGE CURRENT


PEAK FORWARD SURGE **CURRENT, AMPERES** 




NUMBER OF CYCLES AT 60Hz

#### FIG.3 - TYPICAL FORWARD CHARACTERISTICS

**INSTANTANEOUS FORWARD CURRENT, AMPERES** 



**NSTANTANEOUS REVERSE CURRENT, MILLIAMPERES** 



PERCENT OF RATED PEAK REVERSE VOLTAGE, %


www.element14.com www.farnell.com www.newark.com






#### FIG.5-TYPICAL JUNCTION CAPACITANCE

#### FIG.6- TYPICAL TRANSIENT THERMAL IMPEDANCE




TRANSIENT THERMAL IMPEDANCE °C/W



REVERSE VOLTAGE, VOLTS

PULSE DURATION, SEC

### **Package Outline Dimensions**




DO-214AC(SMA)				
Dim.	Min.	Max.		
А	4.25	4.65		
В	2.4	2.8		
С	1.85	2.15		
D	4.85	5.35		
Е	0.1	0.3		
F	0.9	1.5		
G	0.2 Max.			
Н	1.9	2.3		
Ī	1.35	1.65		

Dimensions : Millimetres



#### **Soldering Footprint**



**Dimensions: Millimetres** 

#### **Package Information**

Device	Package	Shipping
B340A-13-F & B360A-13-F	DO-214AC(SMA)	5,000 / Tape & Reel

#### **Part Number Table**

Description	Part Number
Schottky Barrier Rectifier	B340A-13-F
	B360A-13-F

Important Notice: This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com www.farnell.com www.newark.com

