


PI Series

Short and Long Actuator Piono Key



Features:

- SPST with low contact resistance.
- Down for off.
- Vapour phase solderable, IR reflow solderable.
- Insert moulding of terminals and ultrasonic welding.
- Fully sealed construction permits washing with freon, alcohol, water and steam.
- Double contacts for high reliability.



Dimensions : Millimetres (Inches)

Style:

This specification describes "WASHABLE OF DUAL IN-LINE PACKAGE SWITCHES", mainly used as signal switch of electric devices, with the general requirements off mechanical and electrical characteristics.

Operating temperature : -20°C to +70°C.

Storage temperature range : -40°C to +85°C.

Current Range:


Non-switching : 100mA, 50V dc.

Switching : 25mA, 24V dc.

Type of Actuation : Actuated by sliding.



Test Sequence

Description	Test Conditions	Requirements
Electric Performance:		
Visual Examination	By visual examination check without any out pressure and testing.	There shall be no defects that affect the serviceability of the product.
Contact Resistance	1. To be measured between the two terminals associated with each switch pole. 2. Measurements shall be made with a 1KHz shall current contact resistance meter.	50mΩ maximum (initial).
Insulation Resistance	500V dc, 1 minute ±5 seconds.	100MΩ minimum.
Dielectric Withstanding Voltage	300V ac (50Hz or 60Hz) shall be applied between all the adjacent terminals and between the terminal and the frame for 1 minute.	There shall be no breakdown or flashover.
Capacitance	1MHz ±10kHz.	5pF maximum.
Mechanical Performance:		
Operation Force	Applied in the direction of operation. ON → OFF OFF → ON 	800gf maximum.
Stop Strength	A static load of PI: Short actuator: 1kgf, Long actuator: 1kgf is applied in the operating direction and pulling direction, operated for a period of 15 seconds.	There shall be no sign of damage mechanically.
Soldering Heat Resistance	1. Soldering temperature: P.C.Board Terminal PI 260°C ±5°C 5 ±1 seconds.	As show in item 2 to 6.
	2. Duration of solder immersion: 5 ±1 seconds.	
	3. Frequency of solder process: 2 times maximum. (PCB is 1.6mm in thickness).	
Vibration	Shall be vibrated in accordance with Method 201A of MIL-STD-202F 1.Frequency : 10-55-10Hz 1 minute/cycle 2.Direction : 3 vertical directions including the direction of operation. 3.Test time : 2 hours each direction.	As show in item 2 to 6.
Shock	Shall be shocked in accordance with Method 213B Condition A MIL-STD-202F 1.Acceleration : 50G. 2.Action time : 11 ±1m seconds. 3.Testing direction : 6 sides. 4.Test cycle : 3 times in each direction.	As show in item 2 to 6.
Solderability	1.PI soldering temperature : 230 ±5°C. 2.Flux : 5 - 10 seconds. 3.Duration of solder immersion : 3 ±0.5 seconds.	No anti-soldering and the coverage of dipping into solder must more than 75% was requested.

Description	Test Conditions	Requirements
Mechanical Performance:		
Seal (Washable)	The switch is placed at a depth of 5cm in fluorocarbon FC-40 for 1 minute 50°C.	1. Visually monitor the successive bubbling distance within 25mm. 2. As shown in item 2 to 6.
Seal Characteristics : (It is not necessary to apply this kind of test for non-washable series). 1. Do not wash immediately after soldering, do it after returning the switches back to thermal temperature. 2. Do not apply external force to the switch during washing. 3. The switch cannot be used where subject to direct contact with water (except for cleaning processing).		
Durability:		
Operation Life	Measurements shall be made following the test set forth below: 1. 25mA, 24V dc resistive load. 2. Rate of operation : 15 to 20 cycles/minute. 3. Cycle of operation : 200 cycles.	1. As shown in item 3 and 4. 2. Contact resistance : 50mΩ maximum (final-after test).
Weather Proof:		
Resistance Low Temperature	Following the test set forth below the sample shall be left in normal temperature and humidity conditions for an hour before measurements are made : 1. Temperature : -40 ±3°C 2. Time : 96 hours	As show in item 2 to 6.
Resistance High Temperature	Following the test set forth below the sample shall be left in normal temperature and humidity conditions for an hour before measurements are made : 1. Temperature : 85 ±2°C 2. Time : 96 hours	1. As show in item 3 to 6. 2. Contact resistance : 50mΩ maximum (final-after test).
Resistance Humidity	Following the test set forth below the sample shall be left in normal temperature and humidity conditions for an hour before measurements are made : 1. Temperature : 40 ±2°C. 2. Relative Humidity : 90 to 95%. 3. Time : 96 hours.	1. As show in item 4 to 6 2. Contact resistance : 50mΩ maximum (final-after test). 3. Insulation Resistance : 100mΩ minimum.

Part Numbers

Number of Ways	Width (B)	Type	Part Number
4	12.45	Piano Key - Long Actuator	PI041900
8	22.61		PI081900
10	27.69		PI101900
4	12.45	Piano Key - Short Actuator	PI040900
8	22.61		PI080900
10	27.69		PI100900

Dimensions : Millimetres

PI Series

Short and Long Actuator Piono Key



Notes:

International Sales Offices:



AUSTRALIA – Farnell InOne
Tel No: ++ 61 2 9645 8888
Fax No: ++ 61 2 9644 7898



FINLAND – Farnell InOne
Tel No: ++ 358 9 560 7780
Fax No: ++ 358 9 345 5411



NETHERLANDS – Farnell InOne
Tel No: ++ 31 30 241 7373
Fax No: ++ 31 30 241 7333



SWITZERLAND – Farnell InOne
Tel No: ++ 41 1 204 64 64
Fax No: ++ 41 1 204 64 54



AUSTRIA – Farnell InOne
Tel No: ++ 43 662 2180 680
Fax No: ++ 43 662 2180 670



FRANCE – Farnell InOne
Tel No: ++ 33 474 68 99 99
Fax No: ++ 33 474 68 99 90



NEW ZEALAND – Farnell InOne
Tel No: ++ 64 9 357 0646
Fax No: ++ 64 9 357 0656



UK – Farnell InOne
Tel No: ++ 44 8701 200 200
Fax No: ++ 44 8701 200 201



BELGIUM – Farnell InOne
Tel No: ++ 32 3 475 2810
Fax No: ++ 32 3 227 3648



GERMANY – Farnell InOne
Tel No: ++ 49 89 61 39 39 39
Fax No: ++ 49 89 613 59 01



NORWAY – Farnell InOne
Tel No: ++ 45 44 53 66 66
Fax No: ++ 45 44 53 66 02



UK – BuckHickman InOne
++ 44 8450 510 150
++ 44 8450 510 130



BRAZIL – Farnell-Newark InOne
Tel No: ++ 55 11 4066 9400
Fax No: ++ 55 11 4066 9410



HONG KONG – Farnell-Newark InOne
Tel No: ++ 852 2268 9888
Fax No: ++ 852 2268 9899



PORTUGAL – Farnell InOne
Tel No: ++ 34 93 475 8804
Fax No: ++ 34 93 474 5288



UK – CPC
++ 44 8701 202 530
++ 44 8701 202 531



CHINA – Farnell-Newark InOne
Tel No: ++86 10 6238 5152
Fax No: ++86 10 6238 5022



IRELAND – Farnell InOne
Tel No: ++ 353 1 830 9277
Fax No: ++ 353 1 830 9016



SINGAPORE – Farnell-Newark InOne
Tel No: ++ 65 6788 0200
Fax No: ++ 65 6788 0300



EXPORT – Farnell InOne
Tel No: ++ 44 8701 200 208
Fax No: ++ 44 8701 200 209

For enquiries from all other markets



DENMARK – Farnell InOne
Tel No: ++ 45 44 53 66 44
Fax No: ++ 45 44 53 66 06



ITALY – Farnell InOne
Tel No: ++ 39 02 93 995 200
Fax No: ++ 39 02 93 995 300



SPAIN – Farnell InOne
Tel No: ++ 34 93 475 8805
Fax No: ++ 34 93 474 5107



ESTONIA – Farnell InOne
Tel No: ++ 358 9 560 7780
Fax No: ++ 358 9 345 5411



MALAYSIA – Farnell-Newark InOne
Tel No: ++ 60 3 7873 8000
Fax No: ++ 60 3 7873 7000



SWEDEN – Farnell InOne
Tel No: ++ 46 8 730 50 00
Fax No: ++ 46 8 83 52 62

<http://www.farnellinone.com>

<http://www.buckhickmaninone.com>

<http://www.cpc.co.uk>

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2004.

