

5V 2A (2000mA) switching power supply - UL Listed -

ID: 276



Description

Need a lot of 5V power? This switching supply gives a clean regulated 5V output at up to 2000mA. 110 or 240 input, so it works in any country. The plugs are "US 2-prong" style so you may need a plug adapter, but you can pick one up at any hardware store for a \$1 or so.

This cable terminates with a 'standard' 5.5mm OD, 2.1mm ID positive tip connector and will match with our **2.1mm extension cord**, **female terminal block adapter**, **breadboard-friendly DC jack**, etc.

This adapter is great for use with **YBox/Propeller projects**, **Chumby Hacker boards** (using a **2.1mm to 1.7mm adapter**), **RGB LED pixels** or **addressable LED strip**, etc. Its not good for powering an Arduino thru the DC jack as it requires at least 7.5V - check out our 9V adapter instead!

This particular adapter is very nice, much better than the 'PSP charger' we got before, with better stability and less drooping at high currents. It's even UL listed!

Technical Details



- 73mm x 43mm x 27mm (2.9in x 1.6in x 1.1in)
- Cable Length: 1.83/72in (5')
- Cable Diameter: 3.5mm (0.125in)

- Plug type: 5.5mm OD / 2.1mm ID 'coaxial' DC plug
- Input: 110V-220V AC
- Output: ~5V DC up to 2A