



Material Safety Data Sheet

Copyright, 2006, 3M Company. All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

SECTION 1: PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME: 3M(TM) Scotch-Weld(TM) Instant Adhesive CA-40H

MANUFACTURER: 3M

DIVISION: Industrial Adhesives and Tapes Division

ADDRESS: 3M Center
St. Paul, MN 55144-1000

EMERGENCY PHONE: 1-800-364-3577 or (651) 737-6501 (24 hours)

Issue Date: 11/20/2006

Supersedes Date: 07/30/2004

Document Group: 10-2990-9

Product Use:

Intended Use: Structural Strength Instant Adhesive
Specific Use: Cyanoacrylate Adhesive

Formerly known as 3M(TM) Pronto(TM) Instant Adhesive CA-40H

SECTION 2: INGREDIENTS

<u>Ingredient</u>	<u>C.A.S. No.</u>	<u>% by Wt</u>
ethyl cyanoacrylate	7085-85-0	93 - 100
poly(methyl methacrylate)	9011-14-7	< 5
hydroquinone	123-31-9	< 0.2

SECTION 3: HAZARDS IDENTIFICATION

3.1 EMERGENCY OVERVIEW

Specific Physical Form: Liquid

Odor, Color, Grade: clear, colorless, sharp irritating odor

General Physical Form: Liquid

Immediate health, physical, and environmental hazards: Combustible liquid and vapor. Closed containers exposed to heat from fire may build pressure and explode. Vapors may travel long distances along the ground or floor to an ignition source and flash back. Hazardous polymerization may occur. May cause severe eye irritation. May cause allergic skin reaction. May bond tissue rapidly.

3.2 POTENTIAL HEALTH EFFECTS

Eye Contact:

Severe Eye Irritation: Signs/symptoms may include significant redness, swelling, pain, tearing, cloudy appearance of the cornea, and impaired vision.

Bonds eyelids rapidly.

Skin Contact:

Moderate Skin Irritation: Signs/symptoms may include localized redness, swelling, itching, and dryness.

Bonds skin rapidly.

Prolonged or repeated exposure may cause:

Allergic Skin Reaction (non-photo induced): Signs/symptoms may include redness, swelling, blistering, and itching.

Inhalation:

Upper Respiratory Tract Irritation: Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.

Ingestion:

Gastrointestinal Irritation: Signs/symptoms may include abdominal pain, nausea, diarrhea and vomiting.

SECTION 4: FIRST AID MEASURES

4.1 FIRST AID PROCEDURES

The following first aid recommendations are based on an assumption that appropriate personal and industrial hygiene practices are followed.

Eye Contact: Immediately flush eyes with large amounts of water for at least 15 minutes. Get immediate medical attention. DO NOT force eyelids open.

Skin Contact: FOR SKIN BONDS: Quickly soak in warm water and avoid use of excessive force to free bonded area. If unable to free bonded area, or if lips or mouth are bonded, get medical attention. If irritation persists, get medical attention.

Inhalation: Remove person to fresh air. If signs/symptoms develop, get medical attention.

If Swallowed: Do not induce vomiting. Give victim two glasses of water. Never give anything by mouth to an unconscious person. Get immediate medical attention.

SECTION 5: FIRE FIGHTING MEASURES

5.1 FLAMMABLE PROPERTIES

Autoignition temperature

No Data Available

Flash Point

176 °F [Test Method: Tagliabue Closed Cup]

Flammable Limits - LEL

No Data Available

Flammable Limits - UEL

No Data Available

5.2 EXTINGUISHING MEDIA

Use fire extinguishers with class B extinguishing agents (e.g., dry chemical, carbon dioxide).

5.3 PROTECTION OF FIRE FIGHTERS

Special Fire Fighting Procedures: Water may not effectively extinguish fire; however, it should be used to keep fire-exposed containers and surfaces cool and prevent explosive rupture. Wear full protective equipment (Bunker Gear) and a self-contained breathing apparatus (SCBA).

Unusual Fire and Explosion Hazards: Combustible liquid and vapor. Closed containers exposed to heat from fire may build pressure and explode. Vapors may travel long distances along the ground or floor to an ignition source and flash back.

Note: See STABILITY AND REACTIVITY (SECTION 10) for hazardous combustion and thermal decomposition information.

SECTION 6: ACCIDENTAL RELEASE MEASURES

Accidental Release Measures: Evacuate unprotected and untrained personnel from hazard area. The spill should be cleaned up by qualified personnel. Ventilate the area with fresh air. For large spill, or spills in confined spaces, provide mechanical ventilation to disperse or exhaust vapors, in accordance with good industrial hygiene practice. Warning! A motor could be an ignition source and could cause flammable gases or vapors in the spill area to burn or explode. Contain spill. For larger spills, cover drains and build dikes to prevent entry into sewer systems or bodies of water. Working from around the edges of the spill inward, cover with bentonite, vermiculite, or commercially available inorganic absorbent material. Mix in sufficient absorbent until it appears dry. Collect as much of the spilled material as possible. Collect as much of the spilled material as possible using non-sparking tools. Place in a closed container approved for transportation by appropriate authorities. DO NOT wipe spill or residue with cleanup materials containing cotton.

In the event of a release of this material, the user should determine if the release qualifies as reportable according to local, state, and federal regulations.

SECTION 7: HANDLING AND STORAGE

7.1 HANDLING

Keep out of the reach of children. Avoid contact with oxidizing agents. Avoid eye contact. Avoid eye contact with vapors, mists, or spray. Avoid breathing of vapors, mists or spray. Do not eat, drink or smoke when using this product. Wash exposed areas thoroughly with soap and water. Keep away from heat, sparks, open flame, pilot lights and other sources of ignition.

7.2 STORAGE

Store away from acids. Store away from heat. Store out of direct sunlight. Store away from flammable and combustible materials. Store away from oxidizing agents.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1 ENGINEERING CONTROLS

Use with appropriate local exhaust ventilation. Use general dilution ventilation and/or local exhaust ventilation to control airborne exposures to below Occupational Exposure Limits and/or control mist, vapor, or spray. If ventilation is not adequate, use respiratory protection equipment.

8.2 PERSONAL PROTECTIVE EQUIPMENT (PPE)

8.2.1 Eye/Face Protection

Avoid eye contact with vapors, mists, or spray.

The following eye protection(s) are recommended: Safety Glasses with side shields, Indirect Vented Goggles.

8.2.2 Skin Protection

Avoid skin contact.

Select and use gloves and/or protective clothing to prevent skin contact based on the results of an exposure assessment. Consult with your glove and/or protective clothing manufacturer for selection of appropriate compatible materials.

Gloves made from the following material(s) are recommended: Butyl Rubber, Polyvinyl Alcohol (PVA), Polyethylene/Ethylene Vinyl Alcohol. The following protective clothing material(s) are recommended: Apron - Polyethylene ethylene vinyl alcohol. DO NOT wear cotton gloves.

8.2.3 Respiratory Protection

Avoid breathing of vapors, mists or spray.

Select one of the following NIOSH approved respirators based on airborne concentration of contaminants and in accordance with OSHA regulations: Half facepiece air-purifying respirator with organic vapor cartridges. Consult the current 3M Respiratory Selection Guide for additional information or call 1-800-243-4630 for 3M technical assistance.

8.2.4 Prevention of Swallowing

Do not eat, drink or smoke when using this product. Wash exposed areas thoroughly with soap and water.

8.3 EXPOSURE GUIDELINES

<u>Ingredient</u>	<u>Authority</u>	<u>Type</u>	<u>Limit</u>	<u>Additional Information</u>
ethyl cyanoacrylate	ACGIH	TWA	0.2 ppm	
hydroquinone	ACGIH	TWA	2 mg/m3	Table A3
hydroquinone	CMRG	STEL	4 mg/m3	
hydroquinone	OSHA	TWA	2 mg/m3	Table Z-1

SOURCE OF EXPOSURE LIMIT DATA:

ACGIH: American Conference of Governmental Industrial Hygienists

CMRG: Chemical Manufacturer Recommended Guideline

OSHA: Occupational Safety and Health Administration

AIHA: American Industrial Hygiene Association Workplace Environmental Exposure Level (WEEL)

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

Specific Physical Form:

Liquid

Odor, Color, Grade:

clear, colorless, sharp irritating odor

General Physical Form:

Liquid

Autoignition temperature

No Data Available

Flash Point

176 °F [*Test Method:* Tagliabue Closed Cup]

Flammable Limits - LEL

No Data Available

Flammable Limits - UEL

No Data Available

Boiling point	131 °F [@ 2 mmHg]
Density	1.05 g/ml [Ref Std: WATER=1]
Vapor Density	4.5 [Ref Std: AIR=1]
Vapor Pressure	0.05 mmHg [@ 20 °C]
Specific Gravity	1.05 [Ref Std: WATER=1]
pH	Not Applicable
Solubility in Water	Nil
Evaporation rate	Negligible
Hazardous Air Pollutants	0 g/l
Volatile Organic Compounds	0 % weight
Kow - Oct/Water partition coef	No Data Available
Percent volatile	0.00 % weight
VOC Less H2O & Exempt Solvents	0 g/l
Viscosity	400.0 - 600.0 centipoise

SECTION 10: STABILITY AND REACTIVITY

Stability: Stable.

Materials and Conditions to Avoid: Strong bases; Amines

Hazardous Polymerization: Hazardous polymerization may occur. Additional Information: May occur in large quantities only.

Hazardous Decomposition or By-Products

<u>Substance</u>	<u>Condition</u>
Carbon monoxide	During Combustion
Carbon dioxide	During Combustion
Oxides of Nitrogen	During Combustion

SECTION 11: TOXICOLOGICAL INFORMATION

Please contact the address listed on the first page of the MSDS for Toxicological Information on this material and/or its components.

SECTION 12: ECOLOGICAL INFORMATION

ECOTOXICOLOGICAL INFORMATION

Not determined.

CHEMICAL FATE INFORMATION

Not determined.

SECTION 13: DISPOSAL CONSIDERATIONS

Waste Disposal Method: Reclaim if feasible. Dispose of completely cured (or polymerized) wastes in a sanitary landfill. Incinerate in an industrial or commercial facility. As a disposal alternative, dispose of waste product in a facility permitted to accept chemical waste.

Since regulations vary, consult applicable regulations or authorities before disposal.

SECTION 14: TRANSPORT INFORMATION

ID Number(s):
62-3829-0330-0, 62-3829-0335-9, 62-3829-3830-6

Please contact the emergency numbers listed on the first page of the MSDS for Transportation Information for this material.

SECTION 15: REGULATORY INFORMATION

US FEDERAL REGULATIONS

Contact 3M for more information.

311/312 Hazard Categories:

Fire Hazard - No Pressure Hazard - No Reactivity Hazard - No Immediate Hazard - Yes Delayed Hazard - No

STATE REGULATIONS

Contact 3M for more information.

CHEMICAL INVENTORIES

The components of this product are in compliance with the chemical notification requirements of TSCA.

All applicable chemical ingredients in this material are listed on the European Inventory of Existing Chemical Substances (EINECS), or are exempt polymers whose monomers are listed on EINECS.

Contact 3M for more information.

INTERNATIONAL REGULATIONS

Contact 3M for more information.

This MSDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

SECTION 16: OTHER INFORMATION

NFPA Hazard Classification

Health: 2 **Flammability:** 2 **Reactivity:** 1 **Special Hazards:** None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

Revision Changes:

Section 1: Division name was modified.

Copyright was modified.

Section 3: Immediate physical hazard(s) was modified.

Section 3: Potential effects from eye contact was modified.

Section 3: Potential effects from skin contact information was modified.

Section 5: Unusual fire and explosion hazard information was modified.

Section 6: Release measures information was modified.

Section 7: Handling information was modified.

Section 7: Storage information was modified.

Section 8: Engineering controls information was modified.

Section 15: Inventories information was modified.

Section 9: Property description for optional properties was modified.

DISCLAIMER: The information in this Material Safety Data Sheet (MSDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the MSDS available directly from 3M.

3M MSDSs are available at www.3M.com

3M TRANSPORTATION CLASSIFICATION REPORT

DATE: 08/29/06

3M ID NUMBER: 62-3829-0330-0

PRODUCT DESC: 3M(TM) SCOTCH-WELDTM INSTANT ADHESIVE CA 40H 1 OZ BOTTLE

PROTECTIVE SERVICE DURING TRANSIT: PROTECTIVE SERVICE NOT REQUIRED

NMFC DESCRIPTION: ADHESIVES,NOI,IN DRUMS OR INNER CONTAINERS O/T COLLAPSIBLE
TUBES OR GLASS

NMFC ITEM NUMBER: 004620 SUB: 05 CLASS: 60.0

AGENCY: DOTG - DEPARTMENT OF TRANSPORTATION - GROUND (UNITED STATES)

NOT HAZARDOUS

AGENCY: DOTW - DEPARTMENT OF TRANSPORTATION - VESSEL (UNITED STATES)

NOT HAZARDOUS

AGENCY: IATA - INTERNATIONAL AIR TRANSPORT ASSOCIATION (UNITED NATIONS)

NOT HAZARDOUS

AGENCY: IMO - INTERNATIONAL MARITIME ORGANIZATION (UNITED NATIONS)

NOT HAZARDOUS

These transportation classifications are provided as a customer service. AS THE SHIPPER YOU REMAIN RESPONSIBLE FOR COMPLYING WITH ALL THE APPLICABLE LAWS AND REGULATIONS, INCLUDING PROPER TRANSPORTATION CLASSIFICATION AND PACKAGING. 3M's transportation classifications are based on product formulation, packaging, 3M policies and 3M's understanding of applicable current regulations. 3M does not guarantee the accuracy of this classification information.

This information applies only to transportation classification and NOT THE PACKAGING, LABELING, OR MARKING REQUIREMENTS. The original 3M package is certified for U.S. ground shipment only. If you are shipping by air or ocean, the package may not meet applicable regulatory requirements.
