

Data Sheet

Type Number 4074
Designation IEC 10 LR 54
System Manganese Dioxide /
 Zinc / KOH - Electrolyte

Nominal Voltage 1.5 V
Typical Capacity C 45 mAh
 Load 110 kOhm, at 20°C down to 1.1 V

Weight (approx.) 14 g
Volume 6,63 ccm
Coding..... Manufacturing Month/Year by
 Letter Code


Temperature Ranges min max.
 Storage -10°C 65 °C
 Discharge -10°C 65°C

Dimensions min max.
 Diameter ... 14 16
 Height (A/B) 33 35
 Shoulder Diameter [L]..... 7
 Shoulder Height [M]..... 1,3

Segment Electronic

Main Applications Watch
 Photo
 Electronic

Typical Capacities (at 20°C)



Discharge Type	Load	End Voltage:	11 V
Continuous 24h/d, 7d/w Current [μ A]:	110000 Ω 136	Time: Capacity [mAh]: Energy [MWh]:	380 h 45 630

All Data contained herein is for single cells

For battery applications, performance data may vary from single cell data, depending on specific battery configuration

VARTA Microbattery GmbH, Daimlerstr. 1, D-73479 Ellwangen/Jagst
 Tel.: (+49) 7961/921-0, Telefax: (+49) 7961/921-553

Subject to change without prior notice!
 Date of issue: 16.09.2003