



## Tenma 72-9485

### Special Functions

Basic Functions	Range	Best Accuracy
DC Voltage	400mV/4V/40V/400V/600V	$\pm(0.8\%+1)$
AC Voltage	400mV/4V/40V/400V/600V	$\pm(1.2\%+5)$
DC Current	40A/1000A	$\pm(1.5\%+8)$
AC Current	40A/1000A	$\pm(2\%+8)$
Resistance	400 $\Omega$ / 4k $\Omega$ / 40k $\Omega$ / 400k $\Omega$ / 4M $\Omega$ / 40M $\Omega$	$\pm(1\%+2)$
Frequency	4kHz/40kHz/400kHz/4MHz/40MHz	$\pm(0.1\%+3)$

### Features

Auto Ranging		✓
Diode		✓
Continuity Buzzer		✓
True RMS	AC Voltage	✓
Surge Current	AC Current	✓
Peak Max / Peak Min Mode		✓
Data Hold		✓
Sleep Mode		✓
Display Backlight		✓
Full Icon Display		✓
Low Battery Display		✓
Input Impedance for AC Voltage Measurement	Around 10M $\Omega$	✓
Max. Display	4000	✓
Analogue Bar Graph		✓

### GENERAL CHARACTERISTICS

Power	9V Alkaline Battery (1604A or 6LF22)
LCD Size	47 x 30mm
Product Color	Orange and Grey
Product Net Weight	533g
Product Size	286 x 105 x 45mm
Standard Accessories	Test Lead, Alkaline Battery, English Manual, Tool Box
Standard Individual Packing	Gift Box
Standard Carton Dimensions	480 x 372 x 315mm (0.056 CBM Per Standard Carton)
Standard Carton Gross Weight	11kg