



fitted with

- work equipment**
- connected load**
- power consumption**
- system of protection**
- class of protection**
- technology**
- usage**
- luminaire body**
- material
- colour
- lamp cover**
- tubular sections**
- material
- colour
- balance of articulation joints**
- weight (net)**
- mains lead**

- fastening**
- lens; dimensions**
- lens; diopters**
- add-on lens; dimensions**

- 1 x circular fluorescent lamp T29-R 22W/840 G10q
- light colour neutral white, 4000 K, Color Rendering Index (CRI)=80
- Energy efficiency category A
- conventional ballast
- 230 V/ 50 Hz
- approx. 31 W
- IP 20
- II
- switchable
- switch

- plastic
- light grey
- polycarbonate, white opal

- plastic
- light grey
- spring
- approx. 3.1 kg
- approx. 2.9 m; mains plug
- CEE 7/XVI
- table clamp (accessory), wall bracket (accessory)
- Ø 120 mm
- 4
- not available



CEE 7/XVI

illuminance

measuring conditions: d=15cm

E_{min}: 850 lx
E_m: 2112 lx

